
Indoor Wall Mount Racks


A BELDEN BRAND

Adjustable Depth Wall Mount Racks

The PPC adjustable racks provide a robust and configurable solution for indoor equipment. These rack systems can be mounted with a 12” depth, and can be extended to 24” deep at one inch intervals. With configurable depth, the PPC adjustable rack system can be used in a wide variety of installations, even those with limited space available.



16RU



24RU



8/16/24RU Configurable Rack

Features

- Extendable depth from 12” to 24” at 1” increments
- Standard 19” rack spacing with 12-24 threaded holes
- Simple assembly with only Phillips screw driver and 7/16” wrench
- Stability offered by angled supports that bolt directly into the frame, ensuring strength without protruding beyond the structure
- Durable powder coat finish
- Equipment mounting hardware included

Ordering Information

Part Number	Description	Rack Units	Rack Width	H x W x D (mm)	H x W x D (in)
2310-049-016-001	KIT INDOOR RACK WALL MOUNT, 16 RU	16RU	19”	823 x 607 x 305-610	32.4 x 23.9 x 12-24
2310-049-024-001	KIT INDOOR RACK WALL MOUNT, 24 RU	24RU	19”	1180 x 607 x 305-610	46.4 x 23.9 x 12-24
2310-049-0824-001	KIT INDOOR RACK WALL MOUNT,8RU,16RU,24RU	8/16/24RU	19”	467 / 823 / 1199 x 607 x 305-610	18.4 / 32.4 / 48.2 x 23.9 x 12-24

Indoor Wall Mount Racks

A BELDEN BRAND

Horizontal Wall Mount Racks with Optional Dust Cover

The PPC horizontal rack with dust cover is the ideal choice for limited space applications, and where dust and debris are a concern. The wall mount rack includes a fold down dust cover, which protects the upward facing ports or network equipment from dust and debris. This wall mount rack allows for a lower profile from the wall due to the vertical orientation of equipment, while allowing ample airflow for any active components installed.





Features

- Fold up cover to prevent dust and debris
- Cover allows for 4” clearance from face of equipment
- 19” 3RU or 6RU rack for vertically mounted equipment
- Cover can lock in place at open or closed position
- Durable powder coat finish
- Wall-mount hardware included

Ordering Information

Part Number	Description	Rack Units	Rack Width	H x W x D (mm)	H x W x D (in)
2310-049-H06-001	6RU Horizontal Rack(w/o Cover)	6RU	19”	152 x 516 x 373	6.0 x 20.3 x 14.7
2310-049-H06-002	6RU Horizontal Rack with Cover	6RU	19”	257 x 561 x 381	10.1 x 22.1 x 15.0
2310-049-H06-CVR	Dust cover for 6RU Horizontal Rack	n/a	n/a	180 x 561 x 376	7.1 x 22.1 x 14.8
2310-049-H03-001	3RU Horizontal Rack(w/o Cover)	3RU	19”	152 x 516 x 239	6.0 x 20.3 x 9.4
2310-049-H03-002	3RU Horizontal Rack with Cover	3RU	19”	257 x 561 x 246	10.1 x 22.1 x 9.7
2310-049-H03-CVR	Dust cover for 3RU Horizontal Rack	n/a	n/a	180 x 561 x 241	7.1 x 22.1 x 9.5

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200

Indoor Wall Mount Racks

A BELDEN BRAND

Open Face 6RU Wall Rack

The PPC 6U Open Face Wall Mount Rack is a cost effective product for rack mount equipment up to 17” deep. The wall mount rack can support up to 100lbs of equipment, and has multiple velcro slots at each RU for cable management.



Features

- 6RU 19” equipment mounting
- 100lb weight capacity
- 17” Deep
- Wall mount with keyhole slots at 16” center
- Tie wrap and velcro slots for wire management
- Includes lag screws and #12-24 equipment mounting hardware
- 12-Gauge (.105 thick) carbon steel construction
- Gloss black powder coat paint

Ordering Information

Part Number	Description	Rack Units	Rack Width	H x W x D (mm)	H x W x D (in)
2310-049-006-001	RACK WALL MNT 19" 6RU OPEN FACE	6RU	19”	267 x 489 x 435	10.5 x 19.25 x 17.12

r1_03262026

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200