Outdoor PPC QuikPass™ Box

Features & Benefits

- Compact size
- IP67, UV stabilized
- Easy to install
- Versatile applications
- Available with SC / LC adapter or for direct splicing
- Expands the PPC QuikPass solution to outdoor deployments
- Available in black or brown colors



Overview

The Outdoor QuikPass™ box is a compact, slim profile termination box for various FTTx applications. This weather-resistant version of the PPC QuikPass™ Fiber Entry Box is used in combination with the Miniflex QuikPass™ Distribution Cable and connects MDUs from the outside, running distribution cable on the exterior and drilling through a pre-terminated drop cable into the apartment.

After window-cutting the distribution cable, the individual fibers can be pulled back and coiled into the box for splicing or termination (up to 10 ft or 3 m). The hinged splice tray can be removed, ensuring easier splicing operations in the field when working at height or in confined spaces.

Mechanical Data

Dimensions (H x W x D)	Material
158 × 56 × 26mm (6.2 x 2.2 x 1in)	Polypropylene UV stabilized

Cable entries	IP Rating	Capacity
2 × 8mm or 10mm – Distribution Cable 2 x 2.2mm or 3mm – Drop Cable	IP 67	1x SC/APC or LC/APC adapter 2x splice protectors

Environmental Data

Operation temperature	Storage temperature
-40°C to 70°C (-40 to 158°F)	-40°C to 70°C (-40 to 158°F)

Outdoor PPC QuikPass™ Box

Ordering Information

Example OQB- | L | A | N | N | 1 | H | - | B | R | N |
1 2 3 4

1 Adapters Type

SA = SC Simplex APC Green
SU = SC Simplex UPC Blue
LA = LC Duplex APC Green
LU = LC Duplex UPC Blue
NN = No Adapters

2 Pigtails Type

A1 = APC 657.A1
A2 = APC 657.A2
B3 = APC 657.B3
NN = No Pigtails

3 Splice Protector Type

1H = Heath Shrink
1C = ANT Crimp

4 Color

BRN = Brown
BLK = Black



Belden
www.belden.com

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200
www.ppc-online.com