
Hardened Fiber Splice Box
Installation Instructions


A BELDEN BRAND

Hardened Fiber Splice Box– HFSB-XXXXXX | Installation

1. To open, squeeze the sides of the base and pull the cover up and off.
2. Splice the supplied fiber pigtails onto the fiber cable.
3. Fibers can enter the box from the back corner, parallel to the side or parallel to the back (see **RED** arrows below) and can be routed clockwise or counter-clockwise inside the box.
4. Zip ties may be used to secure the fibers at the box entry.
5. A zip tie may also be used to attach the base and cover together through two holes at the back.
6. The box may be mounted on an LGX bracket or with screws through the holes in the base floor.
7. To close, place the tab at the rear of the cover into the slot at the rear of the base. Squeeze the sides of the base and snap the cover tabs into the base.



Example Fiber Installation



r1_04022026

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200