
FutureLink® Patch Only LGX Enclosures

A BELDEN BRAND

Features & Benefits

- Lightweight, compact footprint for indoor and outdoor use
- Bracket holds 1 to 3 each 12-port LGX Bulkhead Adapter Panels
- Stackable features and pass-thru ports allow integration with other SFIT/SNID terminals
- Doors with push-to-latch, locking hasp & 216-tool security bolt
- Cable ports equipped with flat rubber grommets
- Molded-in feet for easy wall mounting; pole-mount kit also available
- Compatible with all SFIT Nozzles




c UL us


Overview

The family of PPC FutureLink® enclosures offer a flexible and cost-effective solution for fiber network deployments. SFIT (Stackable Fiber Interface Terminal) Patch Only LGX Enclosures are ideal for use with pre-terminated cables. Their compact footprint and intuitive cable routing makes them the right choice for network deployments where wall space is critical. These Patch Only enclosures range from 12-port to 36-port for use inside IDF closets or on the outside wall of small multi-dwelling units (MDUs) as a demarcation point. They can be stacked onto other SFIT/SNID terminals for added capacity and capability.

Technical Data

Materials	Safety	Performance
UL 94V-0 (indoor) and UL 94-5VA (outdoor) Light Gray Flame Retardant PBT/PC Blend	UL1863	Designed to meet: GR-049-CORE, GR-2898-CORE, GR-3125-CORE





These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents


6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200

FutureLink® Patch Only LGX Enclosures


A BELDEN BRAND

Ordering Information


Part Number	Description
SFIT-FL00CNN-LGX	Patch Only (empty) Enclosure for 1-3 LGX modules, U-shape lay-in grommets and double-stack rubber grommets. Can add onto existing SFIT enclosures (10 in W x 9 in H x 5 in D).
SFIT-FL12AXNN-01	Patch only 12-port SC-APC with one 12-port LGX Bulkhead Adapter Plate (room for 3), cable tie down posts, three flat rubber grommets (10 in W x 9 in H x 5 in D).
SFIT-FL12AXNN-02	Patch only 24-port SC-APC with two 12-port LGX Bulkhead Adapter Plates (room for 3), cable tie down posts, three flat rubber grommets (10 in W x 9 in H x 5 in D).
SFIT-FL36AXNN-03	Patch only 36-port SC-APC with three 12-port LGX Bulkhead Adapter Plates, cable tie down posts, three flat rubber grommets (10 in W x 9 in H x 5 in D).
SFIT-FT36AXNN-03	Patch Only 36-port SC-APC with three 12-port LGX Bulkhead Adapter Plates, tall slack storage, U-shape lay-in grommets, single tie down ground lug (10 in W x 18 in H x 5 in D).
UCS-FS00CNN-003	Patch Only Empty Enclosure for 1-9 short (3.5-inch) LGX modules, slack storage, two 1.2-inch Closed Cap ports, two Rubber Cone Grommet ports (14 in W x 14 in H x 8 in D).
UCS-FD00CNN-003	Patch Only Empty Enclosure for 1-9 short (3.5-inch) LGX modules, tall slack storage, two 1.2- inch Closed Cap ports, two Rubber Cone Grommet ports (14 in W x 30 in H x 8 in D).
W5-10018	12-port LGX Bulkhead Adapter Plate (empty) for Flangeless SC Simplex or LC Duplex Adapters
SFIT-LGX-12SC-BK	12-port LGX Panel SC Generic 12xSC Simplex Black
SFIT-LGX-12SC-BL	12-port LGX Panel SC-UPC 12xSC Simplex Blue
SFIT-LGX-12SC-GN	12-port LGX Panel SC-APC 12xSC Simplex Green
SFIT-LGX-12LD-BL	24-port LGX Panel LC-UPC 12xLC Duplex Blue
SFIT-LGX-12LD-GN	24-port LGX Panel LC-APC 12x LC Duplex Green




W5-10018




SFIT-LGX-12SC-BK




SFIT-LGX-12SC-BL



SFIT-LGX-12SC-GN



SFIT-LGX-12LD-BL



SFIT-LGX-12LD-GN

r3_04092026

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200
www.ppc-online.com