
Hardline Legacy
3-Piece Splice Connector

A BELDEN BRAND




Mechanical Specifications

Connector	Hex Size	CC Trim Length (A)	Connector Length (B)	Cable Retention
	(inches)	*(inches)*	*(inches)*	*(lbs)*
TPS412NE	1	1	5.78	350
TPS412P1	1	1	5.78	500
TPS412P3	1	1	5.78	350
TPS500NE	1	1	5.78	500
TPS500P1	1	1	5.78	500
TPS750P1	1 1/4	1	5.58	575
TPS1000P3	1 3/4	1	6.57	500

Preparation & Installation Tools

Two (2) adjustable wrenches
Linemen's pliers or other appropriate cutters
Appropriate cable preparation tools



Electrical Specifications

Bandwidth	0MHz to 1.794 GHz
Impedance	75 Ohms (nominal)
Return Loss	-25 dB to 1.794 GHz
Insertion Loss	-0.25 dB to 1.794 GHz
Operating Voltage	90 V (at 60 Hz continuous AC)
Operating Current Rating	20 Amps (at 60 Hz continuous AC)
Operating Temperature	-40°F to + 140°F (-40°C to 60°C)

Meets or Exceeds all SCTE Specifications

r3_12162025

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200
www.ppc-online.com