

## RVUTIK01 Connectivity Accessories - REVConnect Installation Tool Case



For more Information  
please call

1-800-Belden1

### General Description:

REVConnect Installation Tool Case

### Usage (Overall)

Suitable Applications: To Install REVConnect products

### Physical Characteristics (Connectivity)

#### Dimensions

Dimensions:

Height (in.)	Width (in.)	Length (in.)
13.500	10.000	2.500

#### Color

Color: Blue

#### Weight

Weight: 2.530 lbs.

#### Included Parts

Included Parts: REVConn Univ Termination Tool, REVConn Core Pack (50), Scissors, Pen Marker, REVConn Univ Tool Blades, REVCon Univ Tool Belt Clip, REVConn Termination STP and UTP Installation Guides

#### Packaging

Packaging: Individually packaged in a plastic bag, shipped in cardboard box

### Mechanical Characteristics (Connectivity)

Storage Temperature Range: -40°C To +60°C

Installation Temperature Range: -10°C To +50°C

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

#### Suitability

Suitability - Indoor: Yes - Indoor

### Notes (Overall)

#### Product Family

Part Number List:

Accessory	Part Number
Termination Tool	RVUTT01
Cable Preparation Tool	RVUCT01
Belt Clip	RVUTC01
Spare Blades	RVUTB01
Installation Tool Case	RVUTIK01
Carrying Tool Case	RVUTCC01
REVConnect Cores 50 Pack	RVUCOEW-B50

## RVUTIK01 Connectivity Accessories - REVConnect Installation Tool Case

### Physical Properties (Overall)

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0    Revision Date: 10-18-2017

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.