

Belden Recommended Cable Glands for Basic Instrumentation

Cable Part Number	AWG	Construction Description	Cable OD (Inches)	Thread Size (NPT)	Min Cable OD (Inches)	Max Cable OD (Inches)	Belden Part Number
31P1601	16 AWG	1 PR OS Foil PLTC /ITC	0.26	3/4"	0.26	0.55	BTC075A0551RA
31T1601	16 AWG	1 TR Foil PLTC/ITC	0.27	3/4"	0.26	0.55	BTC075A0551RA
32P1602	16 AWG	2 PR IS/OS Foil PLTC/ITC	0.45	3/4"	0.26	0.55	BTC075A0551RA
32P1802	18 AWG	2 PR IS/OS PLTC	0.40	3/4"	0.26	0.55	BTC075A0551RA
61P1601	16 AWG	1 Pr OS	0.30	3/4"	0.26	0.55	BTC075A0551RA
61T1601	16 AWG	1 PR OS TC	0.31	3/4"	0.26	0.55	BTC075A0551RA
62P1402	14 AWG	2 PR TC-ER	0.56	3/4"	0.26	0.55	BTC075A0551RA
62P1602	16 AWG	2 PR IS/OS TC-ER	0.48	3/4"	0.26	0.55	BTC075A0551RA
62P1604	16 AWG	4 PR IS/OS TC-ER	0.59	3/4"	0.26	0.55	BTC075A0551RA
62P1606	16 AWG	6 PR IS/OS TC-ER	0.68	3/4"	0.26	0.55	BTC075A0551RA
62P1608	16 AWG	8 PR IS/OS TC-ER	0.75	3/4"	0.26	0.55	BTC075A0551RA
62P1612	16 AWG	12 PR OS TC-ER	0.94	1"	0.67	1.04	BTC100A1041RA
62P1616	16 AWG	16 PR IS/OS TC	1.03	1"	0.67	1.04	BTC100A1041RA
62P1624	16 AWG	24 PR IS/OS TC-ER	1.24	1 1/4"	0.93	1.27	BTC125A1271RA
62P1636	16 AWG	6 PR IS/OS TC	1.47	1 1/2"	1.22	1.5	BTC150A1501RA
62P1802	18 AWG	2 PR OS TC-ER	0.43	3/4"	0.26	0.55	BTC075A0551RA
62P1804	18 AWG	4 PR OS TC-ER	0.50	3/4"	0.26	0.55	BTC075A0551RA
62P1808	18 AWG	8 PR OS TC-ER	0.67	3/4"	0.26	0.55	BTC075A0551RA
62P1812	18 AWG	12 PR IS/OS TC-ER	0.80	1"	0.67	1.04	BTC100A1041RA
62P1824	18 AWG	24 PR OS TC-ER	1.14	1 1/4"	0.93	1.27	BTC125A1271RA
62T1612	16 AWG	12 TR OS TC-ER	1.06	1 1/4"	0.93	1.27	BTC125A1271RA
83950	20 AWG	1 PR PLTC	0.15	3/4"	0.26	0.55	BTC075A0551RA