

**FCSX12SBFT Faceplates and Panels - FX ECX Splice Field-Term Cassette**

**Preview Document. Not Live Data.**

For more Information  
please call

1-800-Belden1



**Description**

FX ECX CASSETTE, OS2/APC 12 PORTS FIELD-TERM SC SIMPLEX, GREEN ADAPTERS

**Usage (Overall):**

Suitable Applications	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
Related Parts	FX ECX Panels, Belden Splice Sleeves (see notes)

**Physical Characteristics (Connectivity):**

**Capacity:**

Max. Capacity	24 Fibers, 12 SC Simplex/APC Ports
---------------	------------------------------------

**Access:**

Front Connection	Static
------------------	--------

**Dimensions:**

Dimensions

Height (in.)	Width (in.)	Length (in.)
1.300	6.340	8.740

**Materials:**

Materials

Description	Type	Material	Color
Adapter Sleeve		Zirconia-Ceramic	
Front Connector Body	SC-Simplex/APC	Plastic - UL94V-0	Green
Cassette assy		Plastic - UL94V-0	Black

**Weight:**

Weight:	0.280 lbs.
---------	------------

**Included Parts:**

Included Parts	250um pigtailed, splice sleeves and cable ties
----------------	--

**Packaging:**

**FCSX12SBFT Faceplates and Panels - FX ECX Splice Field-Term Cassette**

Packaging Individually packaged in a plastic shell, Shipped in cardboard box (12/box)

**Mechanical Characteristics (Connectivity):**

Storage Temperature Range -10°C To +75°C  
Operating Temperature Range -10°C To +60°C

**Applicable Specifications and Agency Compliance (Overall):**

**Applicable Standards & Environmental Programs:**

EU Directive 2011/65/EU (ROHS II) Yes  
EU RoHS Compliance Date (mm/dd/yyyy) 01/01/2013  
MII Order #39 (China RoHS) EUP 50

**Suitability:**

Suitability - Indoor Yes

**Transmission Characteristics (Connectivity):**

**Notes (Overall):**

Notes Splice holder is included.  
  
Splice holder compatible with Belden splice sleeves part numbers (Post-Shrink Diameter): FXFUHS900AB25(2.5mm), FXFUHS9T2CB25 (2.0mm), FXFUHS250DB25 (1.5mm) and FXFUHSRIBEB12 (oval 4.1mm x 4.6mm)  
  
For additional information about this product, please contact our Technical Support group (ibdn.ts@belden.com) or your local sales representative.

**Product Family:**

Revision Number: 0 Revision Date: 01-01-1900

© 2023 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.  
Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.  
All sales of Belden products are subject to Belden's standard terms and conditions of sale.