

Belden Recommended Cable Glands for Series 9000

Cable Part Number	AWG	Construction Description	Cable OD (Inches)	Thread Size (NPT)	Min Cable OD (Inches)	Max Cable OD (Inches)	Belden Part Number
9314	14 AWG	1 PR OS PLTC	0.33	3/4"	0.26	0.55	BTC075A0551RA
9316	16 AWG	1 PR OS PLTC	0.27	3/4"	0.26	0.55	BTC075A0551RA
9318	18 AWG	1 PR OS PLTC	0.24	3/4"	0.26	0.55	BTC075A0551RA
9328	22 AWG	2 PR PLTC	0.32	3/4"	0.26	0.55	BTC075A0551RA
9329	22 AWG	3 PR PLTC	0.34	3/4"	0.26	0.55	BTC075A0551RA
9341	18 AWG	1 PR OS	0.27	3/4"	0.26	0.55	BTC075A0551RA
9342	16 AWG	1 PR OS	0.29	3/4"	0.26	0.55	BTC075A0551RA
9365	18 AWG	1 TRI OS PLTC	0.27	3/4"	0.26	0.55	BTC075A0551RA
9366	16 AWG	1 TRI OS PLTC	0.31	3/4"	0.26	0.55	BTC075A0551RA
9368	18 AWG	2 PR PLTC	0.43	3/4"	0.26	0.55	BTC075A0551RA
9369	18 AWG	3 PR PLTC	0.46	3/4"	0.26	0.55	BTC075A0551RA
9410	16 AWG	1 PR PLTC	0.26	3/4"	0.26	0.55	BTC075A0551RA
9491	22 AWG	1 TRI PLTC	0.21	3/4"	0.26	0.55	BTC075A0551RA
9493	18 AWG	1 TRI PLTC	0.27	3/4"	0.26	0.55	BTC075A0551RA
9513	22 AWG	3 PR OS PLTC	0.33	3/4"	0.26	0.55	BTC075A0551RA
9516	22 AWG	6 PR OS PLTC	0.42	3/4"	0.26	0.55	BTC075A0551RA
9553	18 AWG	3 PR OS PLTC	0.44	3/4"	0.26	0.55	BTC075A0551RA
9411	14 AWG	1 PR PLTC	0.32	3/4"	0.26	0.55	BTC075A0551RA