


Product Bulletin PB00185







## Provide reliable, multi-gigabit network performance, eliminate slow network speeds and maximize uptime


- Reduce installation time and costs through direct-connect termination (MPTL) to any endpoint device using the REVConnect Plug or FlexPlug
- Speed up deployment using the smallest and lightest horizontal Category 6A cable available and maximize the number of cables within a conduit

# The Industry's Smallest-Diameter Category 6A Cable Designed for Smart Building Applications and Optimized for In-Building Wireless Networks

Combining the Category 6A performance you need with the Belden quality and reliability you expect, 10GXW Cables are the lightest, easiest-to-deploy solution available, eliminating slow speeds and maximizing uptime for smart building networks. For fast and easy termination, combine 10GXW with Belden's REVConnect® Connectivity Line. These solutions are designed to work together to create a reliable, end-to-end wireless infrastructure.



## **FEATURES**



- Designed for seamless termination with the innovative REVConnect Connectivity Line
- EquiBlock<sup>™</sup> technology enables consistent, small cable diameters (0.250" CMP / 0.260" CMR) and eliminates hotspots



## **KEY APPLICATIONS**

- In-building Wi-Fi
  - Wi-Fi 6 (802.11ax)
  - -802.11ac
- In-building small cells
- 100W Type 4 PoE

For more information, visit **www.belden.com/10gx-cable** 

## **Ordering Information**

### 10GXW Cables, 0.250" OD, UTP, Plenum-CMP

Description	Belden Part Number								
Length	Red	Orange	Yellow	Green	Blue	Gray	White	Black	
1000 ft (305 m)	10GXW13 0021000	10GXW13 0031000	10GXW13 0041000	10GXW13 0051000	10GXW13 D151000	10GXW13 0081000	10GXW13 0091000	10GXW13 0101000	

### 10GXW Cables, 0.260" OD, UTP, Riser-CMR

	Description	Belden Part Number								
	Length	Red	Orange	Yellow	Green	Blue	Gray	White	Black	
Ī	1000 ft (305 m)	10GXW12 0021000	10GXW12 0031000	10GXW12 0041000	10GXW12 0051000	10GXW12 0061000	10GXW12 0081000	10GXW12 0091000	10GXW12 0101000	

# Reduce Installation Time and Costs by Combining with the REVConnect Connectivity Line



#### RELIABLE

REVConnect features a highly reliable termination for a secure, gas-tight connection that is proven to reduce rework at all category levels.

#### EASY

REVConnect's universal wiring manager supports all UTP and STP CAT 5e, CAT 6 and CAT 6A cables with a single tool that covers all steps of the termination process, including cable preparation.

#### **VERSATILE**

The same universal core can terminate a jack or a plug. This means that field-terminable plugs, which support CAT 6A and high PoE performance, can be terminated as quickly and easily as a jack.





For access to additional resources, visit www.belden.com/REVConnect

