
Hardline
Right Angle Adapter


A BELDEN BRAND



Mechanical Specifications (CP90 Family - Right Angle Adapter)					
Connector	**Connector Length (A)**	**Thread Size**	**Hex Size (B)**	**Hex Size (C)**	**Pin Trim Length**
	(inches)		*(inches)*	*(inches)*	*(inches)*
CP90	1.1	5/8-24 UNEF	3/4	1	9/16
CP903	2.1	5/8-24 UNEF	3/4	1	9/16
CP904.5	3.6	5/8-24 UNEF	3/4	1	9/16

Electrical Specifications	
Bandwidth	0 MHz to 1.794 GHz
Impedance	75 Ohms (nominal)
Return Loss	-30 dB to 1 GHz -25 dB to 1.218 GHz -20 dB to 1.794 GHz
Insertion Loss	-0.25 dB to 1.794 GHz
Operating Voltage	90 V (at 60 Hz continuous AC)
Operating Current Rating	20 Amps (at 60 Hz continuous AC)
Operating Temperature	-40°F to 140°F (-40°C to 60°C)

Meets or Exceeds all SCTE Specifications



Preparation & Installation Tools
Two (2) adjustable wrenches
Linemen's pliers or other appropriate cutters
Appropriate cable preparation tools

r2_12162025

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200
www.ppc-online.com