

Hardline
Splice Block | CSPB

A BELDEN BRAND





Mechanical Specifications

Connector	Height (A)	Width (B)	Port Spacing (C)	Hex Size (D)	Thickness (E)	Thread Size (F)
	(in)	*(in)*	*(in)*	*(in)*	*(in)*	*(in)*
CSPB	1.25	3.25	1.75	.75	0.75	5/8-24 UNEF-2B


Electrical Specifications

Bandwidth	0 MHz to 1.218 GHz
Impedance	75 Ohms
Return Loss	-25 dB to 1.218 GHz
Insertion Loss	-0.25 db to 1.218 GHz
Operating Voltage	90 V (at 60 Hz continuous AC)
Operating Current Rating	20 Amps (at 60 Hz continuous AC)
Operating Temperature	-40°F to + 140°F (-40°C to 60°C)

Meets or Exceeds all SCTE Specifications

Preparation & Installation Tools

Two (2) adjustable wrenches
Linemen's pliers or other appropriate cutters
Appropriate cable preparation tools



r6_12152025

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200
www.ppc-online.com