Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

AX101852 Modular Connectors - Termination Station

		For more Information please call		
		1-800-Belden1		
General Description:				
Termination Station				
Usage (Overall)				
Suitable Applications:	Terminate 10GX, CAT6+, Cat5E MDVO and Keycor	Terminate 10GX, CAT6+, Cat5E MDVO and Keyconnect Style Module, Mediaflex Gigaflex Inserts		
Related Parts:	10GX, CAT6+, Cat5E MDVO and Keyconnect Style	Module, Mediaflex Gigaflex Inserts		
Physical Characteristics (Connectivity)				
Dimensions Dimensions: Height (in.) Width (in.) Depth (in.) 2.500 5.600 7.000				
Materials Materials:				
Description Material Termination Station Plastic - UL940V-0				
Color				
Color:	Black			
Weight				
Weight:	0.100 lbs.			
Packaging	la ficial elle a selecca d'in a standartic han Otra da	nd a biomism and an af 40 mile		
Packaging:	Individually packaged in a clear plastic bag, Standar			
Mechanical Characteristics (Connectivity)				
Storage Temperature Range:	-40°C To +70°C			
Installation Temperature Range:	-10°C To +60°C			
Applicable Specifications and Agency Complia Suitability	nce (Overall)			
Suitability - Indoor:	Yes - Indoor			
Transmission Characteristics (Connectivity)				
Notes (Overall)				
Notes: For proper installation refer to Installation Guide PX1	03206 available on our web site at http://www.belden.com			
Product Family				
Put Ups and Colors:				

AX101852 1 EA 0.333 LB BLACK MEDIAFLEX TERMINATION STATION	Item #	Putup	Ship Weight	Color	Notes	Item Desc
		1 EA	0.333 LB	BLACK		MEDIAFLEX TERMINATION STATION

Revision Number: 0 Revision Date: 06-05-2009

© 2017 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.