

CABLE PRO®

Connecting with the best has never been easier




7/16" Open End Torque Wrenches

- Use to torque 7/16" F-type fittings
- Also available in 9/16"
- Available in chrome or carbon steel (heat treated) with black oxide finish and cushioned grip
- All torque wrenches are preset in factory to desired torque in./lbs.



Trap Wrenches

- Made of lightweight 6061 aluminum
- 2 steel pins, press fitted into aluminum tube, to remove traps
- Anodized for superior protection and easy identification
- Fits 7/16" hex F-fittings



7/16" Swivel Torque Wrenches

- Use to torque 7/16" F-type fittings
- Designed to work with multi-part taps
- All torque wrenches are preset in factory to desired torque in./lbs
- TRS716 and TRS716SS-EX used to remove plastic security sleeves and TRS716SS to remove metal sleeves



3/8" Torque & Socket Wrenches

- 3/8" fixed socket wrench
- 3/8" swivel torque wrench
- Ability to use different size sockets
- All torque wrenches are preset in factory to desired torque in./lbs.



Extended Socket Wrenches

- Use in headend or behind rack for installation and removal of 7/16" F-type fittings or for BNC fittings
- Socket extends 8" from handle with 1 1/4" socket



Security Wrenches

- Made of chrome 4130 steel
- All include steel spring handle and tightens to 40 in./lbs.
- SWU716 Universal removes metal sleeves, SWU716-EX Thick Wall removes plastic sleeves and DSW716 combines a 7/16" and 1/2" socket



Can Wrench

- Open pedestals and tighten ground straps and taps
- CNW6 combines 3/8" and 7/16" sockets
- CNW8 combines 7/16" and 1/2" sockets
- Can special order socket sizes



Telephone Tool

- Tool has a 5/32" hex end to open telephone pedestals and boxes
- Made of long-lasting, high carbon steel



Gilbert Terminating Tools

- Use with theft proof Gilbert GTP Locking Terminators
- Features solid spring steel ears
- Available in two lengths: 4" and 7"
- Tools are durable, long-lasting and easy to use



Viewsonics Terminating Tools

- Use with all Viewsonics Locking Terminators
- Available in two lengths: 4" and 7"
- Tools are made of zinc plated tool steel



Continuity Testers - Boxes

- Toner boxes features loud audible signal
- LED display detects splitters and shorts in drops
- Two 9-volt batteries (18 volts) allow for testing longer drops



Continuity Testers - Pen

- Pen toner clips to shirt pocket for easy access
- Female or right angle male push-on connector
- Loud audio tone identifies line carrying signal
- Battery included



Installation Tools

- Tools speed the installation and the removal of drop cable
- Available in 7/16" and 9/16" sizes
- Made from 6061 aluminum and features knurled surfaces, a cable slot, and a hard anodized finish



Flaring & Insertion Tool

- Flaring expands jacket to ease the insertion of connectors on to Plenum, Quad and standard size cables in cold weather - Specify size and part#
- Insertion simplifies pushing the connector on to the cable
- Heat treated steel with black oxide finish



Siamese Strippers

- Siamese strippers separate twisted pair cable, coaxial siamese cable and messenger coaxial cable for both RG59 and RG6



A Division of ICM Corp.
6260 Downing Street
Denver, CO 80216
Tel: 1-800-222-2142
or 303-288-8107
FAX: 303-288-4769
Email: sales@icmcorp.net
www.icmcorp.net