
NexBand™ Hardline
Right Angle Adapter

A BELDEN BRAND

Features & Benefits

- Industry leading RF performance to 3GHz
- 1.8GHz/3GHz equipment trim length marked on pin
- Standard long pin for legacy equipment
- Trim length marked on body of adapter
- Swivel nut design for improve installation and pin length accuracy
- New pin contact design



Mechanical Specifications (NXB90 Family - Right Angle Adapter)

Connector	Connector Length (A)	Thread Size	Hex Size (B)	Hex Size (C)	Pin Trim Length
NXB90	1.6 in	5/8-24 UNEF	0.75 in	0.75 in	0.5 in
NXB903	4.8 in	5/8-24 UNEF	0.75 in	0.75 in	0.5 in
NXB906	7.6 in	5/8-24 UNEF	0.75 in	0.75 in	0.5 in

Electrical Specifications

Bandwidth	0 MHz to 3GHz
Impedance	75 Ohms (nominal)
Return Loss	-30 dB to 1.218 GHz -22 dB to 1.794 GHz -18 dB to 3 GHz
Insertion Loss	<-0.25 dB to 3 GHz
Operating Voltage	90 V (at 60 Hz continuous AC)
Operating Current Rating	20 Amps (at 60 Hz continuous AC)
Operating Temperature	-40°F to 140°F (-40°C to 60°C)

Meets or Exceeds all SCTE Specifications



Preparation & Installation Tools

Two (2) adjustable wrenches
Linemen's pliers or other appropriate cutters
Appropriate cable preparation tools

r4_07292026

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200
www.ppc-online.com