

Belden KNX/EIB approved cables

Product Bulletin



Belden's complete offering of KNX certified fieldbus cables provide reliability and safety for your building automation devices should a fire occur.

- **Improved safety** for staff and equipment with the highest CPR Euroclass flame performance rating.
- **Reliability** is ensured through KNX third party certifications and Belden standard 10-year cable warranty.
- **Flexible options** with a complete offering of put up lengths.


Key Features

- Rated up to CPR B2ca, market highest performance, ensuring lowest level of flame spread, smoke and toxicity.
- KNX third-party certification for all cables ensures system compatibility.
- Patented Beldfoil® shield technology delivers 100% coverage, protecting signals from external noise.
- LSZH or PVC jacket designs available.
- B2ca-s1d1a1, Cca-s1a1d1, or Eca CPR Euroclass ratings.
- 1 and 2 pairs configurations available.

About KNX Cables

Thanks to its easy installation, low energy consumption, flexible topologies and cross compatibility, KNX is one of the most flexible and cost-efficient building automation protocols. KNX Cables are internationally recognized and standardized:

- European Standard (CENELEC EN 50090 and CEN EN 13321-1)
- International Standard (ISO/IEC 14543-3)
- Chinese Standard (GB/Z 20965)
- US Standard (ANSI/ASHRAE 135)



Standard Part Number Overview

Part Number	Pairs	Stranding	Insulation	Shield	Jacket	CPR Euroclass
YE00819	1	Solid Bare Copper	PE	Beldfoil	PVC	Eca
YE00905	1	Solid Bare Copper	PE	Beldfoil	LSZH	Eca
77905ELW	1	Solid Bare Copper	LSZH	Beldfoil	LSZH	Cca-s1, d1, a1
77905ELV	1	Solid Bare Copper	LSZH	Beldfoil	LSZH	B2ca-s1, d1, a1
YE00820	2	Solid Bare Copper	PE	Beldfoil	PVC	Eca
YE00906	2	Solid Bare Copper	PE	Beldfoil	LSZH	Eca
77906ELW	2	Solid Bare Copper	LSZH	Beldfoil	LSZH	Cca-s1, d1, a1
77906ELV	2	Solid Bare Copper	LSZH	Beldfoil	LSZH	B2ca-s1, d1, a1



© 2025 | Belden and its affiliated companies claim and reserves all rights to its graphic images and text, trade names and trademarks, logos, service names, and similar proprietary marks, and any other intellectual property rights associated with this publication. BELDEN® and other distinctive identifiers of Belden and its affiliated companies as used herein are or may be pending or registered or unregistered trademarks of Belden, or its affiliates, in the United States and/or other jurisdictions throughout the world. Belden's trade names, trademarks, logos, service names, and similar proprietary marks shall not be reprinted or displayed without Belden's or its affiliated companies' permission and/or in any form inconsistent with Belden's business interests. Belden reserves the right to demand the discontinuation of any improper use at any time.