BELDEN



Belden IBDN®

Pre-Terminated Copper Solutions



TABLE OF CONTENTS

Belden iBDN[®] Pre-Term Solutions

10GX Pre-Terminated Cabling Systems	4
Belden 10GX Pre-Term Patching Cabling System	
Belden REVConnect [®] Pre-Term Systems	
10GX REVConnect Jacks Pre-Terminated Cabling System	
Belden Part Numbers	9
Belden KeyConnect [®] Pre-Term System	
10GX KeyConnect Jacks Pre-Terminated Cabling System	
Belden Part Numbers	





Pre-Term Made Easy

- Easy to configure: only a few standard components to choose from to build an entire system
- Easy to order: simplified ordering process elimates errors
- Easy to install: small and flexible cable assemblies combined with

Reliability and Performance - No Compromise


- Built-in reliability with ultra-robust assemblies and connectors
- Guaranteed Category 6A performance with test results supplied with each assembly
- Guaranteed headroom up to 625 MHz
- Guaranteed headroom in channels as short as 5 ft (1.6 m)
- Fully supported under Belden's IBDN 10GX Certification Program

Save Time and Money


- Reduced planning time with simplified selection of modular components
- Fast delivery to meet short project turn-around deadlines
- Up to 90% reduction in installation time and labor costs
- · Virtually no testing or troubleshooting required

Make it "Green"

- Simplicity of the components means enery and waste savings throughout the manufacturing and supply chain process
- Small and flexible cable assembly design mean less cable to be deployed and no unnecessary slack
- Plug-and-play RJ45 connectivity components significantly reduce installation time and labor costs with almost no product waste during installation and operation
- Up to 50% material reduction in Data Center cabling topology
- All system components can be easily re-deployed and reused







10GX Pre-Term REVConnect System

10GX Pre-Term Coupler System







10GX REVConnect[®] Jacks Pre-Terminated Cabling System

REVConnect Pre-Term Assemblies provide a rapid deployment infrastructure solution for today's data centers and enterprise LANs, with a compact copper preterm bundle OD. They save time on the long process of field termination and offer a more costeffective, proven-guality and flexible plug-and-play solution.

REVConnect Pre-Terminated Assemblies, using our unique cables, are terminated with our award-winning REVConnect termination. Universal Core can be terminated with Jack or RJ45 Plug, providing a versatile solution to End Users. Compact Pulling Eye OD, makes pulling the cable easier for contractors during installation.

Enable faster and more efficient deployment when paired with our REVConnect Preloaded Patch Panels. Providing a true Plug & Play and MAC-Friendly solution. (MAC = Moves added and Changes)

Future-proofing your network for high-bandwidth applications.

Furthermore, with simple planning, fast delivery, up to 90% reduction in installation time and labor cost, bandwidth virtually no testing or troubleshooting required, Belden's 10GX Pre-Terminated Cabling System delivers the promise of pre-terminated cabling systems: dramatically reduced installation time, costsavings, and the reliability and performance of factory terminations – all without compromises or trade-offs.

Utelize REVConnect Jacks for your standard LAN deplyements and Data Center applications redusing inventory and part numbers

BELDEN

Belden understands that the ultimate goal in Data Center networks is to have zero downtime or 'extreme' network availability. In a risk-averse environment with very strict schedule constraints and budgets, demanding reliability and performance without compromise is a must. Belden's 10GX Pre-Terminated Cabling System delivers fast-deployment, with built-in reliability combined with guaranteed performance and headroom. Moreover, the system is fully supported under Belden's IBDN 10GX Certification Program including guaranteed bandwidth of 625MHz, total support for 10 Gb/s Ethernet, and Belden's 25-Year IBDN Product Warranty.





Pre-Term 10GX REVConnect Connectivity	
Description	Part number
10GX REVConnect iPLM Ready Patch Panels (REVConnect Jacks included)	
10GX REVConnect 24-port UTP Cat6A iPLM Ready Panel, Black	PPC6AUR
10GX REVConnect 48-port UTP Cat6A iPLM Ready Panel, Black	PPC6AUR-D
10GX REVConnect 24-port UTP Cat6A iPLM Ready Panel, White	RVAPPF1U24WH
10GX REVConnect 24-port UTP Cat6A iPLM Ready Panel, Black	RVAPPF1U24BK
10GX REVConnect 24-port STP Cat6A iPLM Ready Panel, Black	PPC6ASR
10GX REVConnect 48-port STP Cat6A iPLM Ready Panel, Black	PPC6ASR-D
Includes all Connectivity, without RFID & Hardware	
10GX Pre-Terminated Cable Assembly, 4-Pair, 23 AWG Solid, T568A/B-T568A, 6-Cables Bundle	
10GX UTP REVConnect Assembly LSZH, IEC-1/Eca, White	CB06AUCT1WxxxM
10GX UTP REVConnect Assembly LSZH, Cca, White	CB06AUCT3WxxxM
10GX S/FTP REVConnect Assembly LSZH, IEC-1/Eca, White	CB06ASCT1WxxxM
10GX S/FTP REVConnect Assembly LSZH, Cca, White	CB06ASCT3WxxxM
Use xxx to specify length in meter - 03-15 mt. in increments of 1 mt 15-80 mt. in inc	crements of 5 mt.
Copper Connectivity Patch Cords	
10GX Patch Cords UTP BLUE, LSNH, 1m	CA24106001M
10GX Patch Cords UTP BLUE, LSNH, 2m	CA24106002M
10GX Patch Cords UTP BLUE, LSNH, 3m	CA24106003M
10GX Patch Cords UTP BLUE, LSNH, 5m	CA24106005M
10GX Patch Cords STP BLUE, LSNH, 1m	CAE4106001M
10GX Patch Cords STP BLUE, LSNH, 2m	CAE4106002M
10GX Patch Cords STP BLUE, LSNH, 3m	CAE4106003M
10GX Patch Cords STP BLUE, LSNH, 5m	CAE4106005M

BELDEN

Pre-Term Made Easy

At the heart of Belden's 10GX Pre-Terminated Cabling System are two core components: 10GX Pre-Terminated Cable Assemblies and 10GX RJ45Modular Couplers. Individually, these components offer superior reliability and performance. Together, they deliver the full potential of pre-terminated copper cabling solutions. The Belden solution is referred to as 'Pre-Term Made Easy' because it brings simplicity to the configuring and ordering process and it offers ease of installation through flexible 10GX Cable Assemblies and plugand-play 10GX RJ45 Connectivity. Furthermore, with simple planning, fast delivery, up to 90% reduction in installation time and labor cost, bandwidth virtually no testing or troubleshooting required, Belden's 10GX Pre-Terminated Cabling System delivers the promise of pre-terminated cabling systems: dramatically reduced installation time, cost-savings, and the reliability and performance of factory terminations – all without compromises or trade-offs.

Ideal for Data Centers

Belden understands that the ultimate goal in Data Center networks is to have zero downtime or 'extreme' network availability. In a risk-averse environment with very strict schedule constraints and budgets, demanding reliability and performance without compromise is a must. Belden's 10GX Pre-Terminated Cabling System delivers fastdeployment, with built-in reliability combined with guaranteed performance and headroom. Moreover, the system is fully supported under Belden's IBDN 10GX Certification Program including guaranteed bandwidth of 625MHz, total support for 10 Gb/s Ethernet, and Belden's 25-Year IBDN Product Warranty.



Pre-Term 10GX KeyConnect Connectivity		
Description	Part number	
10GX KeyConnect iPLM Ready Coupler Panels (REVConnect Jacks included)		
10GX KeyConnect 24-port UTP Cat6A iPLM Ready Coupler Panel	PPC6AUC	
10GX KeyConnect 24-port STP Cat6A iPLM Ready Coupler Panel	PPC6ASC	
Includes all Connectivity, without RFID & Hardware		
10GX KeyConnect Patch Coupler Panels (Preloaded)		
10GX KeyConnect 24-port UTP Coupler Panel	AX104141	
10GX KeyConnect 24-port UTP Angled Coupler Panel	AX105300	
10GX KeyConnect 48-port UTP Coupler Panel	AX104592	
10GX KeyConnect 48-port UTP Angled Coupler Panel	AX105348	
10GX Pre-Terminated Cable Assembly, 4-Pair, 23 AWG Solid, T568A/B-T568A, 6-Cable Bundle		
10GX UTP KeyConnect Assembly LSZH, IEC-1/Eca, White	CA24109xxxMA06	
10GX S/FTP KeyConnect Assembly LSZH, IEC-1/Eca, White	CAE4109xxxMA06	
Use xxx to specify length in meter - 03-15 mt. in increments of 1 mt 15-80 mt. in increments of 5 mt		
Copper Connectivity Patch Cords		
10GX Patch Cords UTP BLUE, LSNH, 1m	CA24106001M	
0GX Patch Cords UTP BLUE, LSNH, 2m	CA24106002M	
10GX Patch Cords UTP BLUE, LSNH, 3m	CA24106003M	
10GX Patch Cords UTP BLUE, LSNH, 5m	CA24106005M	
10GX Patch Cords STP BLUE, LSNH, 1m	CAE4106001M	
10GX Patch Cords STP BLUE, LSNH, 2m	CAE4106002M	
10GX Patch Cords STP BLUE, LSNH, 3m	CAE4106003M	
10GX Patch Cords STP BLUE, LSNH, 5m	CAE4106005M	





EUROPE/MIDDLE EAST/AFRICA

France Phone: +33-472-109-990 Iyon.salesinfo@belden.com

Germany Phone: +49-7127-14-0 venlo.salesinfo@belden.com

Italy Phone: 0545 60470 bagnacavallo.itc@belden.com Russia Phone: +7-495-787-06-55 info@belden.ru

Spain Phone: +34-91-746-17-30 madrid.salesinfo@belden.com

Sweden Phone: +46-40-699-88-60 venlo.salesinfo@belden.com The Netherlands Phone: +31-773-878-555 venlo.salesinfo@belden.com

United Arab Emirates Phone: +971-4-391-0490 dubai.salesinfo@belden.com

United Kingdom Phone: +44-161-49837-49 manchester.salesinfo@belden.com

AMERICAS

USA Phone: +1-800-BELDEN1 (1-800-235-3361) ASIA/PACIFIC

China Phone: +86-21-5445-2388 apac.ecsmarketing@belden.com Singapore Phone: +65-6879-9800 apac.ecsmarketing@belden.com



© 2023 | Belden, Hirschmann, GarrettCom, Tofino Security, Lumberg Automation and the Belden logo are trademarks or registered trademarks of Belden Inc. or its affiliated companies in the United States and other jurisdictions. Belden and other parties may also have trademark rights in other terms used herein.