

**FC3X06LDFT Faceplates and Panels - FX ECX Splice Field-Term Cassette**

**Preview Document. Not Live Data.**

For more Information  
please call

1-800-Belden1



**Description**

FX ECX CASSETTE OM3 6 PORTS FIELD-TERM LC DUPLEX, AQUA ADAPTERS

**Image:**

Image

**Usage (Overall):**

Suitable Applications	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
Related Parts	FX ECX Panels, FX Fusion, FX Brilliance

**Physical Characteristics (Connectivity):**

**Capacity:**

Max. Capacity 12 Fibers, 6 LC Duplex Ports

**Access:**

Front Connection Static

**Dimensions:**

Dimensions

Height (in.)	Width (in.)	Length (in.)
1.300	6.340	8.740

**Materials:**

Materials

Description	Type	Material	Color
Adapter Sleeve		Zirconia-Ceramic	
Front Connector Body	LC-Duplex	Plastic - UL94V-0	Aqua
Cassette assy		Plastic - UL94V-0	Black

**Weight:**

Weight: 0.600 lbs.

**FC3X06LDFT Faceplates and Panels - FX ECX Splice Field-Term Cassette**

**Included Parts:**

Included Parts Fiber Routing Accessories and cable ties

---

**Packaging:**

Packaging Individually packaged in a plastic shell, Shipped in cardboard box (12/box)

---

**Mechanical Characteristics (Connectivity):**

Storage Temperature Range -10°C To +75°C

---

Operating Temperature Range -10°C To +60°C

---

**Applicable Specifications and Agency Compliance (Overall):**

**Applicable Standards & Environmental Programs:**

EU Directive 2011/65/EU (ROHS II) Yes

---

EU RoHS Compliance Date (mm/dd/yyyy) 01/01/2013

---

MII Order #39 (China RoHS) EUP 50

---

**Suitability:**

Suitability - Indoor Yes

---

**Transmission Characteristics (Connectivity):**

**Notes (Overall):**

Notes

For additional information about this product, please contact our Technical Support group ([ibdn.ts@belden.com](mailto:ibdn.ts@belden.com)) or your local sales representative.

---

**Product Family:**

Revision Number: 0 Revision Date: 01-01-1900

---

© 2023 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.