




Key Benefits:

- Low Temperature -50C
- Chemical Resistant – Oil Res 1 & 2
- Abrasion Resistant
- Tray Grade

Standards:

- OIL RES 1 & 2 COMPLIANT OUTER JACKET
- TIA/EIA-568.3-D
- NEC/CEC OFNR/OFNR FT4
- ICEA S-104-696 (Indoor/Outdoor Rated)
- ROHS II 2011/65/EU
- REACH EC1907-2006

Temperature Range	
Operating	-40°C to +70°C
Storage	-40°C to +70°C
Installation	-10°C to +60°C

Glass Type	Fiber Grade Code (*)	Jacket	Operating Wavelength (nm)	Max Attenuation (dB/km)	Min. OFL Bandwidth (MHz-km)	Min. Laser Bandwidth (MHz-km)	1 Gigabit Ethernet Min. Link Length (meters)	10 Gigabit Ethernet Min. Link Length (meters)
OS2 - Single Mode	S	Black	1310/1550	0.4/0.3	-	-	5000/-	10,000/40,000
OM1 - 62.5/125µm Multi-Mode	1	Black	850/1300	3.25/1.0	200/500	220/-	275/550	33/-
OM3 - 50/125µm Multi-Mode	3	Black	850/1300	3.0/1.0	1500/500	2000/-	1000/550	300/-
OM4 - 50/125µm Multi-Mode	4	Black	850/1300	3.0/1.0	3500/500	4700/-	1100/550	400/-
OM5 - 50/125µm Multi-Mode	5	Black	850/1300	3.0/1.0	3500/500	4700/-	1100/550	400/-

Single Jacket , All Dielectric

Fiber Count	Part Number Substitute (*) with Fiber Grade Code	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbf (N)	Max. Long Term Load lbf (N)	Min. Bend Radius Load	Min. Long Term Bend Radius
2	TU-*C0-002-RR2N	0.315 (8.0)	42 (63)	600 (2670)	180 (800)	15x Cable OD	10x Cable OD
4	TU-*C0-004-RR2N	0.315 (8.0)	42 (63)	600 (2670)	180 (800)	15x Cable OD	10x Cable OD
6	TU-*C0-006-RR2N	0.315 (8.0)	42 (63)	600 (2670)	180 (800)	15x Cable OD	10x Cable OD
8	TU-*C0-008-RR2N	0.315 (8.0)	42 (63)	600 (2670)	180 (800)	15x Cable OD	10x Cable OD
12	TU-*C0-012-RR2N	0.315 (8.0)	42 (63)	600 (2670)	180 (800)	15x Cable OD	10x Cable OD
24	TU-*C0-024-RR2N	0.315 (8.0)	42 (63)	600 (2670)	180 (800)	15x Cable OD	10x Cable OD

Double Jacket, All Dielectric

Fiber Count	Part Number Substitute (*) with Fiber Grade Code	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbf (N)	Max. Long Term Load lbf (N)	Min. Bend Radius Load	Min. Long Term Bend Radius
2	TU-*C0-002-RX2N	0.500 (12.7)	101 (150)	1000 (4450)	300 (1335)	15x Cable OD	10x Cable OD
4	TU-*C0-004-RX2N	0.500 (12.7)	101 (150)	1000 (4450)	300 (1335)	15x Cable OD	10x Cable OD
6	TU-*C0-006-RX2N	0.500 (12.7)	101 (150)	1000 (4450)	300 (1335)	15x Cable OD	10x Cable OD
8	TU-*C0-008-RX2N	0.500 (12.7)	101 (150)	1000 (4450)	300 (1335)	15x Cable OD	10x Cable OD
12	TU-*C0-012-RX2N	0.500 (12.7)	101 (150)	1000 (4450)	300 (1335)	15x Cable OD	10x Cable OD
24	TU-*C0-024-RX2N	0.500 (12.7)	101 (150)	1000 (4450)	300 (1335)	15x Cable OD	10x Cable OD

†Custom color jackets available