

E300A04 Connectors - DataTuff® Industrial Ethernet Plug Kit Cat 6A FTP IP67

Preview Document. Not Live Data.



For more Information
please call

1-800-Belden1



Description

DataTuff® Industrial Ethernet RJ45 Plug Kit FTP. Suitable for use in IP67 installations.

Usage (Overall):

Suitable Applications Industrial ethernet, harsh environments including 10GBaseT

Applicable Specifications and Agency Compliance (Overall):

Applicable Standards & Environmental Programs:

EU Directive 2002/95/EC (RoHS)	Yes
EU RoHS Compliance Date (mm/dd/yyyy)	01/01/2006
MII Order #39 (China RoHS)	Yes
Safety Listing	c(UL)us Listed

Notes (Overall):

Notes For additional information about this product, visit our web site at <http://www.belden.com>

Connectors:

Connector Type	Cat 6a
Part Number	E300A04
Connector Materials	UL94V-0 flame retardant, UV resistant
Sealing	Suitable for IP67
Connector Interface	IEC 60603-7
Encapsulation Interface	IEC61076-3-106 Variant 1
Tethered Cap	Yes
Shielding	Smooth Coated Aluminum
Electrical Performance	Cat 6A
Maximum Operating Voltage	300 V RMS
Storage Temperature Range	-40°C To +70°C
Installation Temperature Range	-10°C To +60°C
Operating Temperature Range	-10°C To +60°C
Applicable Standards	ANSI/TIA/EIA-568.2-D, EtherNet/IP Specification, UL1863 and CSA-22.2 No. 182.4
Notes	Suitable with Cable OD Range 10.2~6mm (.40~.24in).

Revision Number: 0 Revision Date: 10-09-2019

E300A04 Connectors - DataTuff® Industrial Ethernet Plug Kit Cat 6A FTP IP67

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.