

# Outside Plant (OSP) Indoor/Outdoor (I/O) Cables

## PRODUCT BULLETIN

Belden outdoor cables extend Category 5e, 6 and 6A networks beyond controlled indoor environments. Two versions are available: OSP and indoor/outdoor (I/O). Belden's latest Dry Core Indoor/Outdoor plenum-rated cables eliminate the need to connect different cable types when crossing indoor and outdoor boundaries and are suitable for wet locations. OSP cables are available in gel-filled and gel-free designs that simplify termination at transition points with Belden's game-changing REVConnect® connectivity. No more sticky fingers! Whether protecting against flooding or moisture, extremely low temperatures or high degrees of sunlight, Belden's outdoor products defend against failure.

### Benefits at a Glance

- Extends networks outdoors without performance concerns and eliminate transition points
- Supports fast, easy termination
- Resists sunlight/ultraviolet, abrasion and tearing for better performance
- Operates in conditions of up to -40 degrees C\*

\* Dry OSP cables handles -20°-degree C operating temperature

### Key Features

- Dual-rated versions like CMR/CMX-Outdoor (I/O), OSP/CM-LS (I/O) and CMP/CMX-Outdoor (I/O)
- Specially formulated and more robust jackets
- CMR/CMX versions comply with:
  - > ANSI/ICEA S-100-685
- Gel-filled OSP versions comply with:
  - > ANSI/ICEA S-99-689
  - > ANSI/ICEA S-107-704
  - > Water Penetration Test

### Key Applications

- 10GBASE-T (6A), 1000BASE-T (6A, 6, 5e), PoE Types 1, 2, 3, 4
- OSP & OSP/CM-LS (I/O) (gel-filled) and Dry OSP and Dry CMP/CMX - Wet locations, underground conduit, slab-on-grade conduit
- CMR/CMX-Outdoor (I/O) - Low temperature or high-sunlight environments - Indoor installations that require riser-rated cable
- Arena and stadium wireless systems, exterior camera and Wi-Fi installations

## Ordering Information

Outside Plant (OSP) - UTP - Gel-Free			Indoor/Outdoor - CMP/CMX - Shielded UTP - Gel-Free		
Description	Jacket	Belden Part Number	Description	Jacket	Belden Part Number
Category 6A Premise Horizontal Cable, OSP Rated, 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Gel-Free, Black Jacket, 1000 ft Reel	PE	DOSP6AU 0101000	Category 6 Premise Horizontal Cable, Indoor/Outdoor, 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP/CMX Outdoor, Gel-Free, Black Jacket, 1000 ft Reel	PVDF	IOP6U 0101000
Category 6 Premise Horizontal Cable, OSP Rated, 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Gel-Free, Black Jacket, 1000 ft Reel	PE	DOSP6U 0101000	Category 6A Premise Horizontal Cable, Indoor/Outdoor, 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP/CMX Outdoor, Gel-Free, Black Jacket, 1000 ft Reel	PVDF	IOP6AU 0101000

## Ordering Information

### Indoor/Outdoor - CMP/CMX - Shielded F/UTP - Gel-Free

Description	Jacket	Belden Part Number
Category 6 Premise Horizontal Cable, Indoor/Outdoor, 4 Pair, 23 AWG Solid Bare Copper Conductors, F/UTP - Foil Shielded, Plenum-CMP/CMX Outdoor, Gel-Free, Black Jacket, 1000 ft Reel	PVDF	IOP6F 0101000
Category 6A Premise Horizontal Cable, Indoor/Outdoor, 4 Pair, 23 AWG Solid Bare Copper Conductors, F/UTP - Foil Shielded, Plenum-CMP/CMX Outdoor, Gel-Free, Black Jacket, 1000 ft Reel	PVDF	IOP6AF 0101000

### Outside Plant (OSP) - F/UTP - Gel-Free

Description	Jacket	Belden Part Number
Category 6A Premise Horizontal Cable, OSP Rated, 4 Pair, 23 AWG Solid Bare Copper Conductors, F/UTP - Foil Shielded, Gel-Free, Black Jacket, 1000 ft Reel	PE	DOSP6AF 0101000
Category 6 Premise Horizontal Cable, OSP Rated, 4 Pair, 23 AWG Solid Bare Copper Conductors, F/UTP - Foil Shielded, Gel-Free, Black Jacket, 1000 ft Reel	PE	DOSP6F 0101000

### Indoor/Outdoor - OSP & CM-LS-UTP - Gel-Filled for Wet Locations

Description	Jacket	Belden Part Number
Category 6A, UTP, 4-pair, 23 AWG, Gel-Filled, Black, 1000 ft Reel	PE	2147A 0101000
Category 6, UTP, 4-pair, 23 AWG, Gel-Filled, Black, 1000 ft Reel	PE	2143A 0101000
Category 5e, UTP, 4-pair, 24 AWG, Gel-Filled, Black, 1000 ft Reel	PE	2137A 0101000

### Indoor/Outdoor - OSP & CM-LS - Shielded F/UTP or Corrugated Tape - Gel-Filled for Wet Locations

Description	Jacket	Belden Part Number
Category 6A, F/UTP, Foil Shield, 4-pair, 23 AWG, Gel Filled, Black, 1000 ft Reel	PE	2141A 0101000
Category 6, F/UTP, Foil Shield, 4-pair, 23 AWG, Gel Filled, Black, 1000 ft Reel	PE	2140A 0101000

### Indoor/Outdoor - CMR/CMX Outdoor - UTP - Sunlight Resistant

Description	Jacket	Belden Part Number
Category 6A, UTP, 4-pair, 23 AWG, Indoor/Outdoor, Black, 1000 ft Reel	PVC	2148A 0101000
Category 6, UTP, 4-pair, 23 AWG, Indoor/Outdoor, Black, 1000 ft Reel	PVC	2146A 0101000
Category 5e, UTP, 4-pair, 24 AWG, Indoor/Outdoor, Black or White, 1000 ft Reel	PVC	1594A 0101000 1594A 0091000

### Indoor/Outdoor - CMR/CMX Outdoor - Shielded F/UTP - Sunlight Resistant

Description	Jacket	Belden Part Number
Category 6A, F/UTP, Foil Shield, 4-pair, 23 AWG, Indoor/Outdoor, Black, 1000 ft Reel	PVC	2142A 0101000
Category 6, F/UTP, Foil Shield, 4-pair, 23 AWG, Indoor/Outdoor, Black, 1000 ft Reel	PVC	2149A 0101000
Category 5e, F/UTP, Foil Shield, 4-pair, 24 AWG, Indoor/Outdoor, Black, 1000 ft Reel	PVC	2138A 0101000

### Outside Plant (OSP) - UTP - Gel-Filled for Wet Locations

Description	Jacket	Belden Part Number
Category 6A, UTP, 4-pair, 23 AWG, OSP Gel-Filled, Black, 1000 ft Reel	PE	OSP6AU 0101000
Category 6, UTP, 4-pair, 24 AWG, OSP Gel-Filled, Black, 1000 ft Reel	PE	OSP6U 0101000
Category 5e, UTP, 4-pair, 24 AWG, OSP Gel-Filled, Black, 1000 ft Reel	PE	7997A 0101000

### Outside Plant (OSP) - Shielded F/UTP - Gel-Filled for Wet Locations

Description	Jacket	Belden Part Number
Category 6A, 4-pair, 23 AWG, OSP Gel-Filled, Black 1000 ft Reel	PE	OSP6AF 0101000
Category 6, 4-pair, 23 AWG, OSP Gel-Filled, Black, 1000 ft Reel	PE	OSP6F 0101000



© 2022 | Belden, Hirschmann, GarrettCom, Tofino Security, Lumberg Automation and the Belden logo are trademarks or registered trademarks of Belden Inc. or its affiliated companies in the United States and other jurisdictions. Belden and other parties may also have trademark rights in other terms used herein.