TOFINO SECURITY

Product Bulletin

PB00056

Tofino Xenon Industrial Security Appliance

The Tofino Xenon industrial security appliance provides comprehensive network protection. It is a versatile, extremely ruggedized device that ensures maximum data protection for production systems.

Designed to withstand the harshest industrial conditions, the Tofino Xenon security appliance is ideal for industries such as power and electric utilities, energy (including oil & gas, nuclear, hydro, wind, and other alternatives), transportation, and process automation.

This device complies with global standards and is easy to integrate into existing networks. Its unique "test mode" reduces installation risks, such as network interruptions or configuration errors.

Loadable Security Modules (LSMs) allow the Tofino Xenon to be highly customized to meet the security needs of different protocols, industries, and environments.

Be certain. Belden.



- Safe and cost-effective protection of industrial automation networks
- Plug-n-Protect[™] installation requires no pre-configuration, no network changes, and no disruption to the control system
- Rugged hardware design for years of reliable service

The Tofino Xenon industrial security appliance is the latest addition to the Tofino family of security devices purpose built to meet the needs of industry. This device, which ensures maximum data security for production networks, is a combination of the proven Tofino software with state-of-the-art hardware.

Thanks to its reduced power consumption, it also offers significantly lower operating costs. In addition, the extended operating temperature range of the Tofino Xenon means that it can often be used without supplementary air conditioning equipment.

A further plus is its support for redundant power supplies operating at any voltage from 12 to 48 V DC (or even 24 V AC).

Applications

The robust design of the Tofino Xenon enables it to withstand the harshest environmental conditions and it can be used wherever maximum data security is called for. This makes it the ideal industrial security appliance for mechanical and plant engineering and industrial automation. Other areas for its versatile use include the transportation sector, with applications ranging from road and rail transport right through to shipping. Indeed, the Tofino Xenon has been certified by Germanischer Lloyd for this very purpose. Since this security appliance is also approved for substations (IEC 61850-3) and for explosive environments (ATEX and ISA 12.12.01 HazLoc), it can also be used in the energy sector as well as in power transmission and distribution systems and renewable energy applications such as wind farms.

Your Benefits

The Tofino Xenon security appliance is the ideal solution for segmenting a control network into security zones. It can be installed into an existing control system with no changes to the network, forming, conduits' of communications between the zones. The control engineer defines rules that specify which network devices are allowed to communicate and what protocols they may use. Deep Packet Inspection (DPI) options allow detailed filters to enforce security policy such as only allowing read commands to be sent to a PLC, RTU or an IED device.

Tofino's flexible architecture allows you to create security zones - Zone Level Security throughout your control network to protect critical system components. Tofino helps you meet and exceed NERC CIP requirements and ISA/IEC-62443 Standards. And best of all, it helps you avoid expensive down time and achieve optimal performance in your plant.



Tofino Xenon System

The included Tofino Configurator software makes it easy for the control technician to define rules that specify exactly which devices are allowed to communicate, what protocols they may use, and what actions those protocols perform. Any network traffic that does not fit the rules is automatically blocked by the Tofino Xenon and reported as a security alert.

The standard Tofino Xenon includes a stateful firewall with layer 2, 3 and 4 filtering. Adding Enforcer LSMs provides stateful DPI to manage traffic based on high level message content, such as the commands/services being used or the registers/objects being accessed. There are multiple Enforcers available – each one providing inspection for a different protocol. The LSMs can be pre-loaded onto the Tofino Xenon at the factory, or purchased and installed at a later date as your needs change.

Other features of this security appliance include extensive management facilities and diagnostic tools, a robust metal housing for DIN rail mounting, and a redundant power supply for both DC and AC.

The Tofino Xenon allows for operating temperature ranges from 0°C to +60°C or from -40°C to +70°C. In addition, there are variants for twisted-pair cables or multimode fibers, as well as with a variety of certifications and approvals including ATEX, IEC 61850-3 and EN 50121-4.

Benefits at a Glance

- All-around protection of automation networks with an optimal price-performance ratio
- Stateful firewall with Layer 2, 3 and 4 filtering for all Ethernet-based protocols
- Additional application layer filtering for SCADA and ICS protocols using flexible LSMs
- Prevention of Denial of Service (DoS) attacks with rate limit controls
- Simple configuration over the network or with security USB using the Tofino Configurator software
- · Test mode for verifying firewall rules without risk to your operation
- LSMs pre-installed at factory or purchased separately
- · Simultaneous event logging to remote syslog servers and local nonvolatile memory
- Audit capabilities for tracking configuration changes
- Safe installation in live networks without shutdown
- · Tested for use with all major control system products
- Optional extended operating temperature range from -40°C to +70°C (standard is 0°C to +60°C)
- Variants for twisted-pair cables (RJ45) and multimode fibers (SC)
- · Robust metal housing for DIN rail mounting
- Meets principal standards and approvals:
 - Energy sector: IEC-62443 and IEC-60870-5-104
 - Hazardous areas: ATEX, ISA-12.12.01 Class 1 Div. 2
 - Transport sector: EN 50121-4
 - Shipping: Germanischer Lloyd

Thanks to its conformance with numerous approvals, the Tofino Xenon offers maximum flexibility in its protection of industrial plants, oil rigs, substations and transportation systems.



Technical Information

Product Description								
Туре	TofinoXE-0200T1T1	TofinoXE-0200T1M2 TofinoXE-0200M2T1	TofinoXE-0200M2M2					
Description	Industrial Security Appliance							
Port Type and Quantity	2 x 100BASE-TX	1 x 100BASE-FX 1 x 100BASE-TX 2 x 100BASE-FX						
Additional Interfaces								
USB Interface	1 x USB socket to connect auto-configuration adapter ACA21-USB or approved USB storage device							
Digital Input	1 x plug-in terminal block, 2-pin							
Digital Output (Signaling Contact)	1 x max. 60 V DC or max. 30 V AC, SELV, max. 1A							
Network Size								
Multimode Fiber (MM) 50/125 µm	-	0 to 5000 m, 8 dB Link Budget at 1300 nm, A = 1 dB/km, 3 dB Reserve, B = 800 MHz x km						
Multimode Fiber (MM) 62,5/125 µm	-	0 to 4000 m, 11 dB Link Budget at 1300 nm, A = 1 dB/km, 3 dB Reserve, B = 500 MHz x km						
Twisted Pair (TP)	0 to 100 m	-						
Power Requirements	·							
Operating Voltage	12 to 48 V DC, 24 V AC redundant power supply							
Power Consumption	5 W	6 W	7 W					
Power Supply/Signaling Contact	1 x plug-in terminal block, 6-pin	terminal block, 6-pin						
Software								
Management	Tofino Configurator software							
Diagnostics	LEDs (power, mode, fault, save/load, reset , lin	k status), signal contact, syslog, configuration ve	erify					
Configuration	Network: Tofino Configurator uses secure communications to configure the Tofino Xenon security appliance Manual: Encrypted configuration files may be saved on a USB storage device and loaded into the Tofino Xenon security appliance via a secure USB							
Operating Modes	Test: All traffic is allowed and alerts are generated as per user rules Operational: Traffic is filtered and alerts are generated as per user rules							
Firewall	Stateful layer 2, 3 and 4 filtering with optional deep packet inspection for SCADA protocols (depending on purchased LSMs)							
System Requirements	Windows XP, Windows 7 (32- and 64-bit), or Windows Server 2003, 2008, or 2008 SR2.							
Event Logging	Captured by a syslog server or locally into nonvolatile memory for later download via network or USB storage device							
Ambient Conditions								
Operating Temperature	0°C to +60°C, or -40°C to +70°C (IEC 60068-2-2 Dry Heat Test +85°C 16 hours), dependent on device variant							
Storage/Transport Temperature	-40°C to +85°C							
Relative Humidity (non-condensing)	10% to 95%							
Conformal Coating	Yes (dependent on device variant)							
Mechanical Construction								
Dimensions (WxHxD)	60 x 145 x 125 mm							
Weight	660 g							
Protection Class	IP20							
Mounting	DIN Rail 35 mm							
Approvals								
Declaration of Conformity	CE, FCC, EN 61131, C-TICK, EN 60950							
Safety of Industrial Control Equipment	cUL508 (pending, dependent on device variant)							
Hazardous Locations	ISA-12.1201 Class 1 Div. 2 – Haz. Loc, ATEX-95 Category 3G (Zone 2), (pending, dependent on device variant)							
Germanischer Lloyd	Pending, dependent on device variant							
Railway (norm)	EN 50121-4 (dependent on device variant)							
Substation	IEC 61850-3, IEEE 1613 (dependent on device variant)							
Reliability								
MTBF	74.5 years	69 years	64.2 years					
Warranty	5 years (standard)							

TOFINO SECURITY A BELDEN BRAND

Tofino Xenon Industrial Security Appliance

Το	f i n o X e	-0200T1	T 1 T	DD	Z 9 0	0 0 F T	ΑΤΧ	X . X . X
Design/Model			$ \uparrow \uparrow \uparrow $		1		_ <u>↑</u> _	1
Fast Ethernet Ports 02 = 2 x 10/100 Mbit/s								
Gigabit Ethernet Ports 00 = Not available								
Type Port 1T1= 1 x Twisted Pair RJ45M2= 1 x Multimode SC								
Type Port 2T1= 1 x Twisted Pair RJ45M2= 1 x Multimode SC								
Temperature RangeS= 0°C to +60°CT= -40°C to +70°CE= -40°C to +70°C inclusive Conformal Coating								
Voltage Range DD = 12 to 48 V DC/12 V AC								
Approvals Z9 = CE, FCC, EN 61131, EN 60950 Y9 = Z9 + cUL508 X9 = Z9 + cUL508, ISA12.12 W9 = Z9 + ATEX WX = X9 + ATEX U9 = Z9 + GL UY = U9 + cUL508	UX UT T9 TY V9 VY VU VU	= U9 + cUL508, J = U9 + cUL508 + = Z9 + EN 50121 = T9 + cUL508 = Z9 + IEC 61850 = V9 + cUL508 = V9 + cUL508, G = V9 + cUL508, F	⊢ EN 50121- -4 0, IEEE 1613 GL					
Preloaded Software Modules	VI	= v9 + colsoo, i	EN SUIZI					
$\begin{array}{llllllllllllllllllllllllllllllllllll$	000K 000N 000Q 000S 000V 000X	= FW + EIP $= FW + NC + EIP$ $= FW + MB + EIF$ $= FW + NC + ME$ $= FW + OPC + EI$ $= FW + NC + OP$ $= FW + NC + OP$ $= FW + MB + OF$ $= FW + NC + ME$	P) 3 + EIP IP C + EIP PC + EIP	ΊΡ				
NOTE: FW = Firewall LSM (includes Event Logger LSM), NC = NetCo OPC = OPC Enforcer LSM, EIP = EtherNet/IP Enforcer LSM, DNP = D								
OEM Type — TA = Standard								
Configuration — T = Tofino Standard Configuration								
Software Release								

XX.X.XX = Current Software Release

NOTE: The part number categories (**OEM Type**, **Configuration** and **Software Release**) are optional.

Belden, Belden Sending All The Right Signals, Hirschmann, GarrettCom, Tofino Security, Lumberg Automation and the Belden logo are trademarks or registered trademarks of Belden Inc. or its affiliated companies in the United States and other jurisdictions. Belden and other parties may also have trademark rights in other terms used herein.