

# GECKO Switches

Lite Managed Industrial  
Ethernet Switch Family

PRODUCT BULLETIN 



As one of the smallest managed Industrial Ethernet switches on the market, GECKO switches guarantee reliable data communication and provide security, diagnostic and redundancy functions at an outstanding price, setting new standards in cutting long-term operating costs.

- **Quick installation and handling** due to simple configuration and network management software tools, which enable various tasks to be worked on remotely, such as monitoring the health of the network and troubleshooting.
- **Space-saving design and increased bandwidth performance** with four to eight Fast Ethernet ports and two Gigabit SFP slots.
- **Cost-effective and environment-friendly operation** due to its minimal power consumption of less than 6 Watts.



## Key Features

- Simple Network Management Protocol (SNMP) and HiDiscovery/Industrial HiVision, plus a web interface, ensure fast and convenient administration
- Redundancy protocols like Rapid Spanning Tree Protocol (RSTP) and Media Redundancy Protocol (MRP) guarantee reliable data communication
- A range of diagnostic functions ensures fast identification of errors, resulting in smooth production processes
- Reduced operating costs due to low power consumption
- Compact design for space-saving installation
- High resistance to shocks and vibration
- 24 Volt DC power supply
- Withstand harsh conditions with an IP30 protection rating
- Security features like VLAN
- Industrial protocols like PROFINET
- Extended operating temperature range from -40 to +60 °C

The Hirschmann GECKO Industrial Ethernet switches provide security, diagnostic and redundancy functions at a price competitive to that of managed switches, without the complex operation of them.

## Your Benefits

Although these “lightly” managed switches stand out with their simplicity, they also offer functionalities that enable more advanced capabilities than unmanaged devices.

Featuring four to eight Fast Ethernet ports (10/100 Mbit/s) and two Gigabit Ethernet (100/1000 Mbit/s) SFP slots, plus the ability to mount on a DIN rail, the compact dimensions of the GECKO switches require little space. Additionally, any inactive ports can be disabled to protect against possible misuse.

The switches can be managed through Simple Network Management Protocol (SNMP) or via HiDiscovery and Industrial HiVision from Hirschmann. A web interface for HyperText Transfer Protocol Secure (HTTPS) deployment is also available. For monitoring purposes, the switches provide diagnostic and documentation options, such as a system log, Remote Monitoring (RMON) and Link Layer Discovery Protocol (LLDP). Rapid Spanning Tree Protocol (RSTP), Media Redundancy Protocol (MRP) and Quality of Service (QoS) functions are also supported.

Additional features include Virtual Local Area Networks (VLANs), industrial protocols such as PROFINET and IP30 protection rating, a wide operating temperature range, high resistance to shocks and vibration, and a 24 V DC power supply. What's more, with a power consumption of less than 6 W, the GECKO switches require minimal power.

## Applications

With a combination of managed and unmanaged switches, the GECKO switches are ideally suited for use in smaller networks, or on the edge of larger installations. They can also be used for carrying video signals or transmitting control data. For industrial manufacturers looking for a cost-effective way of entering the world of managed switches, the GECKO switches offer simple network management and enhanced network availability. Network parameters can be centrally configured using a web interface, while redundancy and diagnostic functions ensure high network availability.

## Markets

With their compact, yet robust design, the GECKO switches can be used in a wide range of areas, from solar farms to production lines in the food and beverage sector. Potential application scenarios include machine and plant engineering, material handling, robotics and connecting production cells for various industries. No matter where they are installed, the GECKO switches guarantee reliable data communication.

Hirschmann GECKO switches offer a well-designed and intuitive graphical user interface – even on mobile devices – to get more status information from your network.



## Technical Information

### Product Description

| Type                   | GECKO 4TX   | GECKO 5TX   | GECKO 8TX   | GECKO 8TX/2SFP   |
|------------------------|---|---|---|--|
| Description            | Lite Managed Industrial ETHERNET Rail-Switch, Ethernet/Fast-Ethernet Switch with Gigabit Uplink, Store and Forward Switching Mode, fanless design |   |   |  |
| Port Type and Quantity | 4 x 10BASE-T/100BASE-TX, TP-cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity   | 5 x 10BASE-T/100BASE-TX, TP-cable, RJ45-sockets, auto-crossing, auto-negotiation, auto-polarity | 8 x 10BASE-T/100BASE-TX, TP-cable, RJ45-sockets, auto-crossing, auto-negotiation, auto-polarity | 8 x 10BASE-T/100BASE-TX, TP-cable, RJ45-sockets, auto-crossing, auto-negotiation, auto-polarity, 2 x 100/1000 MBit/s SFP |
| Order No.              | 942 104-001   | 942 104-002   | 942 291-001   | 942 291-002  |

### More Interfaces

|                                |                                 |
|--------------------------------|---------------------------------|
| Power Supply/Signaling Contact | 1 plug-in terminal block, 3-pin |
|--------------------------------|---------------------------------|

### Network Size - Length of Cable

|                   |           |
|-------------------|-----------|
| Twisted Pair (TP) | 0 - 100 m |
|-------------------|-----------|

### Network Size - Cascadability

|                     |     |
|---------------------|-----|
| Line-/Star Topology | Any |
|---------------------|-----|

### Power Requirements

|                   |                             |
|-------------------|-----------------------------|
| Operating Voltage | 12/24 V DC (9.6 to 32 V DC) |
|-------------------|-----------------------------|

### Software

|                      |  |
|----------------------|--|
| Management           | HTML5 Web-Interface, TFTP config file/firmware transfer, SNMP V1/V2/V3   |
| Diagnose             | Device status indication (LEDs), Log-File, RMON (1) statistics, Simple interface statistics, Topology Discovery according to IEEE 802.1AB (LLDP), Syslog |
| Configuration        | BOOTP/DHCP, HiDiscovery  |
| Security             | SNMPv3 (authNoPriv), Possibility to disable each port, SSH, SSL  |
| Redundancy Functions | RSTP (IEEE 802.1D-2004), MRP   |
| Filter               | TOS/DSCP prioritization (Mapping TOS/DSCP to 802.1D/p), QoS (4 queues), Static unicast/multicast filter entries (up to 100), VLAN, Flow Control          |
| Industrial Protocols | PROFINET   |
| Time Synchronization | SNTP Client  |
| Secure Remote Access | SiteManager GECKO  |

### Ambient Conditions

|                                    |                  |                 |
|------------------------------------|------------------|-----------------|
| Operating Temperature              | 0 °C to +60 °C   | -40 to +60 °C * |
| Storage/Transport Temperature      | -40 °C to +85 °C |                 |
| Relative Humidity (non-condensing) | 5% to 95%        |                 |

### Mechanical Construction

|                        |  |       |                                       |       |
|------------------------|--|-------|---------------------------------------|-------|
| Mounting               | DIN Rail                                   |       |                                       |       |
| Protection Class       | IP30                                       |       |                                       |       |
| Dimensions (W x H x D) | 25 mm x 99 mm x 79 mm (w/o terminal block) |       | 38 x 102 x 79 mm (w/o terminal block) |       |
| Weight                 | 100 g                                      | 110 g | 200 g                                 | 220 g |

## Approvals

|  |                                  |
|--|----------------------------------|
| Safety of Industrial Control Equipment | cUL 61010-1 (previously cUL 508) |
|--|----------------------------------|

## Reliability

|          |   |
|----------|---|
| Warranty | EN 62368-1, UL 61010-2-201 & CSA C22.2 NO. 61010-2-201:18 |
|----------|---|

## Scope of Delivery and Accessories

|                                 |   |
|---------------------------------|---|
| Scope of Delivery               | Device, terminal block, start-up instructions   |
| Accessories to Order Separately | Rail power supply RPS 30, RPS 80 EEC or RPS 120 EEC (CC), Fast Ethernet SFP Transceivers, Fast Ethernet Bi-Directional SFP Transceivers, Gigabit Ethernet SFP Transceivers, Gigabit Ethernet Bi-Directional SFP Transceivers , Mounting Accessories |

\* Temperature derating depending on used SFP. More information can be found in the manual.

**NOTE:** These are the prominent technical specifications. For complete technical specifications visit: [www.belden.com](http://www.belden.com)