

MASTER SPECIFICATION F/UTP CABLE 4 PAIR #23 AWG CATEGORY 6A RISER

Design Number:
LT58030

DESCRIPTION

SHIELDED TWISTED PAIR (F/UTP) CABLE FOR USE IN HORIZONTAL CABLING SYSTEMS PER ANSI/TIA-568-C AND ISO/IEC 11801:2002 CLASS EA. THE CABLE IS UL COMPONENT COMPLIANT TO ANSI/TIA-568-C.2 CATEGORY 6A ELECTRICAL CHARACTERISTICS. THE CABLE CONSISTS OF #23 AWG SOLID BARE COPPER INSULATED CONDUCTORS, ASSEMBLED INTO FOUR TIGHTLY TWISTED PAIRS, WITH A FLEXWEB® CORE SEPARATOR AND FOIL SHIELD, UNDER AN OVERALL JACKET. PRINT INCLUDES DESCENDING FOOTAGE MARKERS FROM 1000 TO 0. SEE BELDEN.COM/P FOR ANY/ALL APPLICABLE PATENT DETAILS.

THE CABLE IS RISER (NON-PLENUM) RATED FOR USE AS A VERTICAL RUN IN A SHAFT AND FOR GENERAL PURPOSE COMMUNICATIONS USE IN ACCORDANCE WITH ARTICLE 800 OF THE NATIONAL ELECTRICAL CODE (NEC). THE CABLE IS US (USA) & cUS (CANADA) LISTED FOR THIS APPLICATION BY PASSING THE UL 1666 RISER CABLE FLAMMABILITY TEST. THE CABLE ALSO PASSES THE CSA FT4 VERTICAL FLAME TEST - CABLES IN CABLE TROUGH FROM CLAUSE 4.11.4 OF CSA C22.2 NO. 0.3.

SUPPORTED APPLICATIONS

IEEE 802.3 10BASE-T (ETHERNET), 100BASE-T (FAST ETHERNET), AND 1000BASE-T (GIGABIT ETHERNET), IEEE 802.3 10GBASE-T (10 GIGABIT ETHERNET) ANSI.X3.263 FDDI TP-PMD, IEEE 802.5 4 AND 16 Mbps TOKEN RING, 550 MHz BROADBAND VIDEO AND ATM UP TO 4.8 GBPS.

CONSTRUCTION

PRIMARIES: CONDUCTOR: 23 AWG (.6 mm) SOLID BARE COPPER
INSULATION: THERMOPLASTIC POLYOLEFIN

PAIR ASSEMBLY: 2 PRIMARIES TWISTED IN VARIED LAYS

COLOR CODE: SEE TABLE 1

CABLE ASSEMBLY: 4 PAIRS CABLED TOGETHER WITH A CORE SEPARATOR

SHEILD: ALUINUM / MYLAR TAPE SHIELD

JACKET: NO LEAD FLAME RETARDANT THERMOPLASTIC
JACKET COLOR: SEE TABLE 2
NOMINAL CABLE OD: .265" (6.35 mm)

LISTING: C(UL)US OR C(ETL)US TYPE CMR
UL OR ETL VERIFIED CAT 6A




FIGURE 1

TABLE 1

PAIR NUMBER	PAIR COLOR CODE	
1	WHITE	BLUE
2	WHITE	ORANGE
3	WHITE	GREEN
4	WHITE	BROWN

TABLE 2

MOHAWK PART NUMBER	MOHAWK DESIGN NUMBER	JACKET COLOR
M59246	HT58031	RED
M59247	HT58032	ORANGE
M59248	HT58033	YELLOW
M59249	HT58034	GREEN
M59250	HT58035	GRAY
M59251	HT58036	WHITE
M59252	HT58037	BLACK
M59253	HT58038	BLUE

PHYSICAL CHARACTERISTICS

CABLE WEIGHT w/reel: 37 lbs/1000ft (53.7 kg/km)

BENDING RADIUS: 2.35" (58.7 mm) MIN

PULLING TENSION: 25 lbf (110 N) MAX

OPERATING TEMP.: -20°C to +75°C (-4°F to +167°F)

STORAGE TEMP.: -20°C to +75°C (-4°F to +167°F)

***INSTALLATION TEMP.:** 0°C to +50°C (+32°F to +122°F)

* THE INSTALLATION TEMPERATURE REFERS TO THE TEMPERATURE OF THE CABLE WHILE BEING INSTALLED OR PULLED. DO NOT INSTALL BELOW 0°C (+32°F).

MOHAWK
Cabling Excellence for Open Architecture

(978) 537-9961 Fax: (978) 537-4358
(800) 422-9961 www.mohawk-cable.com

This document is the property of Mohawk. The information contained herein is considered proprietary and not to be reproduced by any means without written consent of Mohawk.

Rev	Description	Date	Init.
A	ELEC, OD, CONSTRUCTION UPDATED	12/20/2021	CMA
B	FIXED DESIGN NUMBER	02/10/2023	CMA
Date: 12/20/21	Page 1 of 2	Design Number: LT58030	
Orig: CMA	Review:		

Mohawk reserves the right to change any specification in the interest of product enhancement.

This cable complies with the EU-RoHS directive 2002/95/EC (restrictions on hazardous substances) regulations.

MASTER SPECIFICATION
F/UTP CABLE
4 PAIR #23 AWG CATEGORY 6A RISER

Design Number:
LT58030

ELECTRICAL CHARACTERISTICS (REF TABLE 3)
STANDARDS: EXCEEDS ANSI/TIA-568-C.2 CAT 6A,
ICEA S-90-661-1997 CAT 6 &
ISO/IEC 11801 ed 2.0 AMEND 1 CLASS EA
HORIZONTAL CABLE

CONDUCTOR DCR: 8.2 Ω/100m (25.0 Ω/Mft) MAX
DCR UNBALANCE: 5% MAX

MUTUAL CAPACITANCE: 46 pF/m NOM

CAPACITANCE UNBALANCE PAIR/GROUND: 90 pF/100m MAX

CHARACTERISTIC IMPEDANCE: 100 Ω ± 10% (10-550 MHz)

INPUT IMPEDANCE: 100 Ω ± 15% (1-100 MHz)
100 Ω ± 18% (>100-250 MHz)
100 Ω ± 32% (>250 MHz)

RETURN LOSS (RL): 20 + 5 log₁₀(f) dB MIN (1-10 MHz)
25 dB MIN (>10-20 MHz)
25 - 7 log₁₀(f/20) dB MIN (>20 MHz)

PROPAGATION DELAY: 534+36 / √f ns/100m MAX
PROPAGATION DELAY SKEW: 45 ns/100m MAX
NOMINAL VELOCITY OF PROPAGATION (NVP): 70%

INSERTION LOSS (ATTENUATION): $1.82\sqrt{f} + .00091f + .25/\sqrt{f}$ dB/100m MAX

NEAR END CROSSTALK (NEXT): 44.3 - 15 log₁₀(f/100) dB/100m MIN

POWER SUM NEAR END CROSSTALK (PS NEXT): 42.3 - 15 log₁₀(f/100) dB/100m MIN

ATTENUATION TO CROSSTALK RATIO FAR END (ACRF): 27.8 - 20 log₁₀(f/100) dB/100m MIN

POWER SUM ATTENUATION TO CROSSTALK RATIO FAR END (PS ACRF): 24.8 - 20 log₁₀(f/100) dB/100m MIN

TCL: 30 - 10 log₁₀(f/100)

ELTCL: 35 - 20 log₁₀(f) 1 ≤ f ≤ 30 MHz

COUPLING ATTENUATION: 55 - 20 log₁₀(f/100) 30 ≤ f ≤ 500 MHz

POWER SUM ALIEN NEAR END CROSSTALK (PS ANEXT): 62.5 - 15 log₁₀(f/100) dB/100m MIN

POWER SUM ALIEN ATTENUATION TO CROSSTALK RATIO FAR END (PS AACRF): 38.2 - 20 log₁₀(f/100) dB/100m MIN
77 dB MAX

NOTE: Attenuation To Crosstalk Ratio Far End (ACRF) was previously referred to as Equal Level Far End Crosstalk (ELFEXT).
WHERE f = Frequency In MHz from 1 to 500 MHz.

TABLE 3
REFERENCE ELECTRICAL CHARACTERISTICS

FREQ (MHz)	INSERTION LOSS (dB/100m)	NEXT (dB/100m)	PS NEXT (dB/100m)	ACRF (dB/100m)	PS ACRF (dB/100m)	RETURN LOSS (dB)	PROP. DELAY (ns/100m)	ALIEN CROSSTALK	
								PS ANEXT (dB/100m)	PS AACRF (dB/100m)
1.0	max	min	min	min	min	min	max	min	min
1.0	2.1	74.3	72.3	67.8	64.8	20.0	575.0	67.0	67.0
4.0	3.8	65.3	63.3	55.8	52.8	23.0	557.0	67.0	66.2
8.0	5.3	60.8	58.8	49.7	46.7	24.5	551.7	67.0	60.1
10.0	5.9	59.3	57.3	47.8	44.8	25.0	550.4	67.0	58.2
16.0	7.5	56.2	54.2	43.7	40.7	25.0	548.0	67.0	54.1
20.0	8.4	54.8	52.8	41.8	38.8	25.0	547.0	67.0	52.2
25.0	9.4	53.3	51.3	39.8	36.8	24.3	546.2	67.0	50.2
31.25	10.5	51.9	49.9	37.9	34.9	23.6	545.4	67.0	48.3
62.5	15.0	47.4	45.4	31.9	28.9	21.5	543.6	65.6	42.3
100.0	19.1	44.3	42.3	27.8	24.8	20.1	542.6	62.5	38.2
155.0	24.1	41.4	39.4	24.0	21.0	18.8	542.1	59.6	34.4
200.0	27.6	39.8	37.8	21.8	18.8	18.0	541.5	58.0	32.2
250.0	31.1	38.3	36.3	19.8	16.8	17.3	541.3	56.5	30.2
300.0	34.3	37.1	35.1	18.3	15.3	16.8	541.1	55.3	28.7
350.0	37.2	36.1	34.1	16.9	13.9	16.3	540.9	54.3	27.3
400.0	40.1	35.3	33.3	15.8	12.8	15.9	540.8	53.5	26.2
500.0	45.3	33.8	31.8	13.8	10.8	15.2	540.6	52.0	24.2

SWEEP TESTED TO 500



(978) 537-9961 Fax: (978) 537-4358
(800) 422-9961 www.mohawk-cable.com

This document is the property of Mohawk. The information contained herein is considered proprietary and not to be reproduced by any means without written consent of Mohawk.

Rev	Description	Date	Init.
A	ELEC, OD, CONSTRUCTION UPDATED	12/20/2021	CMA
B	FIXED DESIGN NUMBER	02/10/2023	CMA
Date: 12/20/21		Page 2 of 2	
Orig: CMA		Review:	
			Design Number: LT58030