
NexBand™ Hardline Splice Block

A BELDEN BRAND

Features & Benefits

- Industry leading RF performance
- Trim length marked on body of adapter
- New pin contact design
- Can be used in multiple configurations
  - o Through
  - o 90 Degrees
  - o 180 Degrees



Mechanical Specifications

Connector	Height (A)	Width (B)	Port Spacing (C)	Hex Size (D)	Thickness (E)	Thread Size (F)
NXBSPB	1.175 in	3.375 in	1.75 in	0.75 in	0.75 in	5/8-24 UNEF-2B


Electrical Specifications

Bandwidth	0 Mhz to 3 GHz
Impedance	75 Ohms
Return Loss	(Through Configuration) -30 dB to 1.218 GHz -25 dB to 1.794 GHZ (90 Configuration) -25 dB to 1.218 GHz -22 dB to 1.794 GHZ (180 Configuration) -25 dB to 1.218 GHz -22 dB to 1.794 GHZ
Insertion Loss	(Through Configuration) <-0.1 dB to 1.794 GHz <-0.6 dB to 3 GHZ (90 Configuration) <-0.1 dB to 1.794 GHz <-1.0 dB to 3 GHZ (180 Configuration) <-0.1 dB to 1.794 GHz <-1.5 dB to 3 GHZ
Operating Voltage	90 V (at 60 Hz continuous AC)
Operating Current Rating	20 Amps (at 60 Hz continuous AC)
Operating Temperature	-40°F to 140°F (-40°C to 60°C)

Meets or Exceeds all SCTE Specifications

Preparation & Installation Tools

Two (2) adjustable wrenches
Linemen's pliers or other appropriate cutters
Appropriate cable preparation tools



r3_03062026

These products may be protected by one or more patents. For further information, please visit: www.ppc-online.com/patents

6176 E. Molloy Rd. East Syracuse, NY 13057
bbs.cs@belden.com
1-800-800-6652 • +1 315-431-7200
www.ppc-online.com