

Communication Solutions

for Rockwell Automation® Users



Contents

ELX3 ProLinx Edge™ Gateway	3
Linux Development Modules	4
Ethernet and Serial Gateway Solutions	5
Automotive and Inertial Navigation Gateways	6
Serial & Ethernet Modbus® Solutions	7
Scalable Modbus® and Modbus® TCP Solutions for CompactLogix™	8
Secure Remote Connectivity	9
Belden Horizon Console	12
In-Chassis Flow Computer Solutions	13
HART Solutions	14
Power and Energy Solutions	15
DNP3 Solutions	16
Modernization Solutions	17
PROFINET Solutions	20
Automated Material Handling	22
Amusement	23
ProLinx Edge Mini	24
Wireless Support from Trusted Experts	25
Radiating Cable 2.4 and 5 GHz Band	26
802.11n (abgn) Fast Watertight Industrial Hotspots	27
Wireless Comparison Product Selection Chart	28
In-Chassis Product Selection Chart	29
Stand-Alone Gateways Product Selection Chart	30

ELX3 ProLinx Edge™ Gateway

The newest protocol converter from ProSoft is the start of a new era for the company. The ELX3 ProLinx Edge Gateway unites operational technology (OT) protocol conversions with the ability to run custom Docker containers on a single hardware platform.

With this multi-purpose gateway:



Enable seamless OT protocol conversion

Enables EtherNet/IP™ and Modbus TCP/IP data exchange to allow for communication between your dissimilar devices in the field.

Take control with user-defined containers

Empowers custom code and algorithm creation for advanced applications like machine learning and predictive maintenance.

Industrial grade hardware

Designed for harsh environments, requiring class 1 Div 2 installations and extended temperature ranges of -40 to 70C.



The gateway is ideal for companies looking to unite data from disparate IIoT devices and legacy OT equipment. Via the ELX3, bring silos of automation into centralized control systems for analysis and action. By supporting both ProSoft Protocol Gateway containers and custom containers, the ELX3 gives you the flexibility you need to address today's most demanding edge applications and scale as your operation evolves.





Linux Development Modules

Connect Your Logix Processor to ThingWorx or to a MQTT Broker



These edge-compute modules are ideal for custom algorithm applications, including the transfer of key operational data. The ControlLogix module's library has sample applications (complete with source code!) for ThingWorx®, Sparkplug B MQTT, and standard MQTT. These samples help enable direct connectivity, expanding your IIoT application.

- In-chassis modules simplify your site and bring data directly into your ControlLogix or CompactLogix; help minimize cabinet space
- Linux Virtual Machine (VM) and C/C++ development environment provided on separate DVD
- VM contains preinstalled toolchain and libraries




Ethernet and Serial Gateway Solutions

ProSoft Technology's stand-alone, DIN rail-mounted industrial gateways provide a means to read or write data from devices using dissimilar protocols. All gateways come with our ProSoft Discovery Service feature. With PDS, you don't have to change your PC to the default subnet of the module, saving you time during setup.

Building Automation solutions – including QuickServer gateways – bring key operational data directly to your Rockwell Automation controller. Use these solutions to boost energy efficiency, use the resource most productively, and decrease your usage and costs.



- Gateways with two Ethernet ports allow you to isolate networks, passing only the data you want between devices
- EtherNet/IP™ gateways support multiple I/O connections for fast real-time data
- Remote configuration and diagnostics via Ethernet
- SD Card slot for disaster recovery of configuration data
- Up to four Serial ports



PROFIBUS DP, FOUNDATION Fieldbus, and many other protocols are also available.



Automotive and Inertial Navigation Gateways



- The **CANOpen Router** is an ideal solution for motion-oriented machine control systems, primarily in automotive applications. The module supports EtherNet/IP to CANOpen communications, and can support either Master or Slave mode
- The **J1939 Router** enables automotive diagnostic communications via EtherNet/IP between Logix controllers and J1939 devices. The module is used to facilitate automatic unpacking and scaling of J1939 devices' data to your controller's UDT structure, saving you time
- The **Time Sync Module** enables precise time syncing with Logix controllers and HMIs, and provides GPS data as well for inertial navigation applications. Velocity and odometer data is available thanks to the onboard GPS receiver. This module can also be used as a replacement for Rockwell Automation's discontinued 1756-TIME solution
- The **XPosition Module** delivers highly precise location data from GPS or inertial navigation devices, ensuring you know the placement of your crane system, marine crafts, or drilling equipment

Serial & Ethernet Modbus® Solutions

ProSoft Technology's stand-alone, DIN rail-mounted industrial gateways provide a means to read or write data from devices using dissimilar protocols. All gateways come with our ProSoft Discovery Service feature. With PDS, you don't have to change your PC to the default subnet of the module, saving you time during setup. Building Automation solutions - including QuickServer gateways - bring key operational data directly to your Rockwell Automation controller. Use these solutions to boost energy efficiency, use the resource most productively, and decrease your usage and costs.





Modbus® TCP/IP

- Fast Multi-Server/Multi-Client capabilities
- Add-On Instruction reduces configuration effort and simplifies maintenance



Modbus® Serial

- Module configuration stored within the Studio 5000®/RSLogix™ 5000 project (ACD file) for simplified disaster recovery
- Add-On Profile (AOP) improves integration into Studio 5000/RSLogix 5000
- Add-On Instruction (AOI) reduces configuration effort and simplifies maintenance
- Modules also available for the Logix-XT platform; support operations in extreme environments at higher operating temperatures, and have a conformal coating to protect them in harsh conditions




Scalable Modbus® and Modbus® TCP Solutions for 1769 CompactLogix™




Modbus® Serial

- Enhanced modules allow up to 10,000 I/O words
- Lite modules allow up to 240 I/O words
- Integrated Modbus® Serial communications in 1734 Point I/O™ applications



Secure Remote Connectivity



Our Secure Remote Access suite, easy to use by design, provides IT-secure and OT-friendly solutions that help you connect to your equipment anywhere, at any time. Remote access gateways and always-on networks can be monitored securely and easily in Belden Horizon™ Console, part of Belden Horizon.

We aim to make remote access as secure and streamlined as possible, and put the end user in the driver's seat, ensuring complete access control of remote equipment. Our remote access solutions feature:




- Virtual Lockout-Tagout feature for greater access control of specific equipment
- A multi-layered Defense-in-Depth approach to security, including advanced two-factor authentication (we avoid the less-secure SMS mode of authentication) and Active Directory support via Single Sign-On (SSO), which means you can access Belden Horizon with your corporate login credentials
- Role-based device and user access
- No software updates on your part – no user-installed software means you'll eliminate an entry point for hackers, and save time for your team
- OpenVPN support: One-time-use tunnels provide a secure connection between your equipment and Belden Horizon
- Layer 2 Tunneling Protocol (L2TP)/IPSec and Secure Socket Tunneling Protocol (SSTP) support increases VPN security for all popular clients, including Windows, iOS, and Android products, and easily allows you to see your remote devices rather than try to remember them
- Support for SMS messaging from your EtherNet/IP or Modbus TCP/IP PAC (Cellular Gateway only)

Secure Remote Connectivity

Persistent Data Network (PDN)

Always-on, secure, and managed cloud-based network to connect geographically dispersed remote sites. This simple, secure solution is ideal for infrastructure communications networks.



Check for product availability in your country.

Secure Remote Connectivity

Gateways



Industrial Cellular Gateway

(ICX35-HWC)

- 4G LTE cellular or wired access via WAN/LAN port
- Ethernet port available for Internet connection or SIM card
- Monitor and manage via Belden Horizon Console



Data Logger Plus

(PLX51-DLplus-232)

- Ideal for remote sites with limited communications that need to log data (stores over 16M records!)
- Can help OEMs identify operational issues and improve OEE
- Data can be downloaded as a .csv file
- Support for 200 tags; minimum log interval: 50 milliseconds
- Features support for JSON interface, enabling easy exporting of logged data to business CRM systems
- Features an integrated webserver to trend variables and upload logged data
- XLReporter connection available



Network Bridge

(PLX35-NB2)

- Wired remote access
- Monitor and manage via Belden Horizon Console
- Enable / Disable remote access locally via an EtherNet/IP message
- File Relay - transfer files across segmented networks maintenance



Belden Horizon Console

- EasyBridge™ technology enables your PC to act like it is connected directly to a switch on the remote network
- Allows software tools, such as RSWHo and Studio 5000, to work without routing
- Multi-layered defense-in-depth approach, including support for Active Directory (SSO) and token-based 2F Authentication, keeps your data and equipment safe

Case Study →


Wastewater Monitoring via
Always-On Managed Network
psft.com/DC4

Case Study →

Oil and Gas Company Now
Remotely Monitoring Operation
psft.com/DCE

Case Study →

Monitoring a City's Remote Lift
Stations
psft.com/C19



Belden Horizon Lite App

What if you're not at your desk or office when the customer call comes in, or sitting on a beach and your customer calls with a critical issue? You don't have to give up that view or worry you'll upset your customer – Belden Horizon has gone mobile, and the app is available to download on the iOS platform!





App Store is a trademark
of Apple Inc.

For a list of popular gateway solutions
and part numbers, see page 30.

In-Chassis Flow Computer Solutions

For Multi-Well Pad and LACT Applications



ControlLogix® CompactLogix™

- Supports 8-16 meter runs with 4 streams per meter run for the measurement of hydrocarbon gases and liquids
- In-chassis solution brings data directly into your ControlLogix® or CompactLogix™; helps minimize cabinet space
- Pair with Rockwell Automation's distributed I/O capability + ProSoft's wireless radios to reduce wiring to transmitters and I/O devices
- Includes the use of EAFC Manager, a free Windows 11-based tool for configuration, reporting, and monitoring; hourly or daily archives with user-selected data are available
- NMI certified for OIML, WELMEC, and MID type approval (AGA/API)
- No additional licensing fee for liquid meter runs

- Add another AFC card in same chassis if more meter runs are required
- Secure data archiving / meter run
- Archive records stored in non-volatile memory in module
- Archive data cannot be altered/changed
- Integration to SCADA with Modbus/Enron Modbus support (Cygnet, Autosol, and FlowCa)
- System designs can support more than 80 metering locations

ProSoft's integrated flow computer helped Pelican Gathering decrease the number of components, minimize their panel space, and streamline integration.

Case Study →


Integrated flow computer helped Pelican Gathering
psft.com/DCE






HART Solutions

Gain additional diagnostic information from your distributed process equipment – and boost efficiency as a result.



Point to Point—Modbus/TCP, DNP3 (TCP/IP and UDP), EtherNet/IP
 Point to Multipoint—EtherNet/IP, Modbus/TCP

For a list of popular in-chassis solutions and part numbers, see page 29.

 Find out how you'll benefit psft.com/DCB

Power and Energy Solutions

Connecting your Rockwell Automation controller to intelligent electronic devices (IEDs), including substation power monitors and relays.



IEC 61850 Solutions



(IEC 61850 Client Module)

- Allows ControlLogix® PACs to interface with IEC 61850 IEDs, including power protection equipment; features support for up to 40 IEC 61850 Server devices on the network
- Supports up to 225 I/O connections to ControlLogix PAC
- Supports MMS and GOOSE messaging, helping you eliminate hard-wired I/O signals for interlocking of protection relays and load shedding applications
- Streamlined configuration: Highly integrated into Studio 5000 with Add-On Profile; custom Add-On Instruction available
- An IEC 61850 Server Module is also available for ControlLogix PACs



IEC 61850 Gateway

- Fast, real-time data transfers with a maximum of 10,000 bytes in and 9,920 out (PLX82)
- Polls up to 20 IEC 61850 server devices
- Application-specific Add-On Instructions are automatically generated
- IEC 61850 IED tags are created in your Studio 5000®/RSLogix 5000™ Project, reducing configuration time and errors



Other protocol solutions are available, including modules supporting IEC-60870-5-104, Modbus, PROFIBUS, and PROFINET



DNP3 Solutions


Connect power and energy, oil and gas, or water and wastewater sites with industrial DNP3 solutions.



DNP3 Master and Slave Gateways

The PLX51-DNPM and -DNPS gateways enable intelligent routing between DNP3 and EtherNet/IP or Modbus protocols. Adding these modules into your SCADA and telemetry system will help you reliably capture key data with no holes, with time- and date-stamped data at the source.

- Supports secure authentication
- Optimized for Rockwell Automation architectures
- Flexible and easy to configure



For a list of popular in-chassis solutions and part numbers, see page 29.

Modernization Solutions

Lower-risk, phased updates of legacy equipment can be completed on your timeline - without using up CapEx. Avoid extended downtime with this gradual approach.





Legacy Rockwell Automation Remote I/O and DH+™ Modernization Solutions

Modernize your legacy control system in phases with OpEx dollars



AN-X4-AB-DHRIO EtherNet/IP to Remote I/O or DH+ Gateway

- Replace old Remote I/O drives with new drives on EtherNet/IP without modifying PLC code
- Replace PanelView™ units on Remote I/O to new PanelView Plus 7 models on EtherNet/IP without modifying PLC code
- Enables your Remote I/O PLC-5® or SLC™ to communicate with EtherNet/IP FLEX™ I/O adapters, giving you a phased migration option when your 1794-ASB spares are gone



This mode allows PLC's on Remote I/O to connect to and control 1794-AENT EtherNet/IP Flex adapters.

Designed to replace obsolete 1794-ASB adapters
 Supports up to 16 EtherNet/IP connections
 Each adapter and rack of discrete count as a single connection
 Each analog module counts as a single connection




Modernization Solutions

Legacy Competitive PLC Migration Solutions



AN-X3 Family of Gateways

- Enables Allen-Bradley PAC via EtherNet/IP to control I/O devices on legacy networks
- Enables a phase-based approach for migrating legacy control systems
- Monitor mode enables testing & verification of PAC logic before controlling I/O
- Currently available for AutoMax, Modicon, PROFIBUS DP and GE Genius migrations




Check for product availability in your country.

1761-NET-ENI Replacement – Update Your Legacy DF1 Systems

Need a 1761-NET-ENI now that it's been discontinued? The Routing Module can be used in nearly every application as the NET-ENI. Now you can modernize your legacy DF1 control system in phases using your OpEx budget.



- Intelligent routing to ControlLogix® or CompactLogix™ from PLC-5, SLC, MicroLogix™ controllers
- Direct-to-tag technology simplifies data mapping, reducing configuration time




DCS migration solutions
psft.com/DB3

1761-NET-AIC Replacement – Update your legacy DH485 systems

Need a 1761-NET-AIC replacement? This module can be used in nearly every application as the NET-AIC. Now you can modernize your legacy DH485-based system in phases using your OpEx budget.



- Intelligent data routing between DH485 and EtherNet/IP devices
- Direct-to-tag technology simplifies data mapping, reducing configuration time
- 2-port unmanaged switch or Device Level Ring (DLR) support



ControlNet and DeviceNet Modernizations



ControlNet Router: Connect existing equipment to new EtherNet/IP -using PanelView Plus terminals - without having to do some major re-cabling. The module also supports Device Level Ring networks or can be used as a two-port Ethernet switch.




DeviceNet Router: Allows you to exchange data between DeviceNet and EtherNet/IP networks. The router can be configured as a DeviceNet Scanner or a DeviceNet Device, which allows the device be integrated into a new Logix system while also allowing the EtherNet/IP device to be added to the DeviceNet network. The router also features two Ethernet ports to support Device Level Ring (DLR) applications.



ControlNet and CAN Bus Solutions

- ProSoft's A-CANBR/B CAN Bus Router enables intelligent data routing between either EtherNet/IP™ or Modbus® TCP/RTU and a CAN Bus network. This allows you to integrate CAN Bus devices into a Rockwell Automation® ControlLogix® or CompactLogix™ or any Modbus Client or Server device with minimal effort.
- The ControlNet Fiber Repeater extends the length of a network for a point-to-point topology while performing network media conversion from copper to fiber, and from fiber to copper. It's ideal for applications in which a medium-distance fiber link between two ControlNet products is needed.



Replacement for 1786-RPA + 1786-RPFM combination



PROFINET Solutions

The Only In-Rack PROFINET Module for ControlLogix® power monitors and relays.



ProSoft's first-of-its-kind in-chassis modules for Rockwell Automation® ControlLogix® PACs provide reliable connectivity for these two industrial powerhouses. The new ILX56-PNC PROFINET Controller Module and ILX56-PND PROFINET Device Module allow your ControlLogix controller to communicate on a PROFINET RT network. The Controller Module can communicate with up to 64 PROFINET Devices and pass up to 4096 bytes of input and output data as high-speed cyclic I/O data on your PROFINET network. The Device Module can transfer up to 1440 bytes of Input/Output data to a PROFINET RT network with ControlLogix RPI times as low as 2 mSec, meeting the needs of some of the most demanding PROFINET RT applications.

As with most ProSoft in-chassis modules, the units allow for streamlined integration into your application. With the PLX50 Configuration Utility, you have access to advanced features such as custom-built Add-On Routines to minimize the amount of time and effort in getting your ControlLogix operating on your PROFINET RT network.



PROFINET Gateways

- PROFINET Controller and Device Gateways connect to EtherNet/IP-based systems.
- Gateways with two Ethernet ports allow you to isolate networks, passing only the data you want between devices
- EtherNet/IP gateways support multiple I/O connections for fast real-time data

PROFIBUS Solutions

ProSoft's PROFIBUS DP modules are ideal for the most demanding applications.



For ControlLogix®

Through premier integration tools, you can minimize the time required to get a PROFIBUS DP network configured in a ControlLogix environment.

Master/multi-slave module: Can transfer up to 5000 bytes of cyclic I/O data with various slave devices on the network.

Multi-slave module: Can pass up to 2440 bytes of input and output data as high-speed cyclic I/O data on a PROFIBUS DP network.



For CompactLogix™

Master module: Supports remote Ethernet connectivity with Asset Management Software, significantly lowering your maintenance costs.

Slave module: Supports DPV1 Acyclic Messaging; Add-On Profile provided to allow for seamless integration to Studio 5000 and RSLogix 5000.



PROFIBUS Gateways

Master and Slave gateways connect PROFIBUS DP equipment to devices using EtherNet/IP, Modbus Serial, or Modbus TCP/IP. PROFIBUS DP network commissioning time can be greatly reduced with the modules' built-in PROFIBUS DP packet capture utility. With support for up to 1536 bytes of Input and Output data, and up to 4 EtherNet/IP connections back to the processor, the modules provide performance and data throughput for even the most demanding of PROFIBUS applications.

For a list of popular in-chassis solutions and part numbers, see page 29.



Automated Material Handling



Reliability is key for any Automated Material Handling application.

Industrial gateways and wireless radios enable communications between equipment in busy facilities, helping you maintain production and meet increased consumer demand.

Logistics

Increased consumer demand for goods bought online has heightened the need for reliable, on-time delivery of many household goods. Industrial protocol gateways and wireless radios can help ensure accurate production and distribution; real-time communications between moving equipment such as smart conveyors and automated guided vehicles (AGVs); and the safety of on-site employees in increasingly mobile applications.

Automotive Skillet Line Communication



Automotive

Automotive production is an intricate process whose automated elements rely on real-time communications. Moving parts throughout a facility - whether they're half-finished vehicle frames moving down a production line or AGVs ferrying supplies - require reliable communications to protect workers and product throughout the site. Ultra-Fast Industrial Hotspots can help.

Case Studies

A perfume manufacturer produces its samples thanks to improved communication with their scale.
psft.com/DEB

Fiat Chrysler increased production flexibility - and saved downtime - when they paired wireless radios with new Rockwell Automation controllers.
psft.com/DD4

A logistics end user needed to find a reliable alternative to slip rings for a conveyor application. Wireless radios now communicate with their CompactLogix.
psft.com/DEA

A UK end user needed to transport materials within its automotive facility. The machine builder Mirage paired AGVs with wireless radios
psft.com/DD9

Check for product availability in your country.

Amusement


At the top of any amusement end user or machine builder's mind is the need to maintain riders' safety.

Using wireless communications over CIP Safety helps increase communications for thrilling rides – as well as the safety of everyone on-board.

Case Studies →

Safety on the Skyfall: The company Funtime added radiating cable and a wireless radio to best monitor this freefall ride's signals.
psft.com/DEC


Improvements to the Disk'O Coaster: Using a wireless Ethernet-based solution paired with a safety protocol helped this ride manufacturer improve the data rate of communication.
psft.com/DED



802.11n (abgn) Fast Industrial Hotspots

- Ultra-Fast access point switchover times of less than 10 ms are perfect for applications such as automated storage-retrieval systems, AGVs, and automotive skillet lines
- EtherNet/IP™ embedded object and Modbus® agent support lets users get radio diagnostics into their PAC/PLC, where the information can be analyzed and acted upon, helping to reduce downtime
- WPA/WPA2-Personal (PSK, AES and/or TKIP); WPA/WPA2-Enterprise (IEEE 802.1X/RADIUS, AES and/or TKIP)
- Secure digital configuration storage for quick field replacement
- Radios support wireless safety Ethernet networks, ideal for automated material handling applications

802.11abgn Wireless Plant Architecture 2.4 GHz or 5 GHz High-Speed Wireless Network



For a list of popular wireless solutions and part numbers, see page 29.

2.4 GHz and 5 GHz High-Power Industrial Hotspots are also available for longer-distance applications.



Reliably Connect Your Material Handling Application with the ProLinx Edge Mini

The ProLinx Edge Mini features hitless roaming of less than 100 milliseconds, enabling large-scale wireless applications featuring mobile equipment, including those in logistics and material handling.

The radio's Wi-Fi 6 technology ensures reliable connectivity for massive applications. The radio is:

- Able to maintain high throughput due to reliable connectivity even in crowded facilities
- Optimized for efficient single and multi-channel Wi-Fi of more than 300 devices per facility

ProLinx Edge Mini wireless networks are also easily expandable by design – so as your application grows, adding new radios will be a streamlined process.



Wireless Support from Trusted Experts

Designing and implementing a wireless network is a major investment. ProSoft's wireless field application engineers can help ensure a smooth design and installation for your application. Our professional wireless services include:

- Expert Phone Support
- Engineering Drawing Review
- Site Surveys
- Configuration Support
- Troubleshooting

Check for product availability in your country.



Contact us at
psft.com/DB3
to learn more.



Radiating Cable 2.4 and 5 GHz Band

Acting as a long, flexible antenna, Radiating Cable is an alternative to traditional RF antenna systems.

Features


- Special coaxial shield design uses slots to radiate RF Signals
- Available in variable lengths
- Pre-assembled cable for easy installation
- Frequency Range: 2.4 GHz, 5 GHz to 6 GHz

Benefits

- Wireless signal more stable in terms of response time – useful in communicating with I/O
- Used in metallic environments, rotating/spinning machines, conveyors, AGVs, warehousing, and more

Rotating Equipment

Radiating Cable (replaces slip-ring)



How you'll benefit from radiating cable
psft.com/CXL


802.11n (abgn) Fast Watertight Industrial Hotspots

- IP67 water/dust-rated
- Designed for extreme temperatures (-40° to +70°C), high vibration/shock and hazardous locations (UL C1D2, ATEX Zone 2)
- Ultra-Fast Roaming with under 10 ms switchover times maintains connections for moving machines/platforms
- Power over Ethernet (PoE)
- QoS and VLAN for optimum traffic management
- WPA/WPA2-Personal (PSK, AES and/or TKIP)
- WPA/WPA2-Enterprise (IEEE 802.1X/RADIUS, AES and/or TKIP)

Wireless Application Guide [→](#)

In this comprehensive resource, find out the key considerations for adding wireless communications over CIP Safety.

psft.com/DD7



For a list of popular wireless solutions and part numbers, see page 28.



Wireless Comparison Product Selection Chart

Model	802.11abgn Weatherproof Industrial Hotspot RLX2-IHNF-W(C)	802.11abgn Fast Industrial Hotspot RLX2-IHNF	Industrial Cellular Gateway ICX35-HWC	ProLinX Edge Mini ELXM-SW6
Features & Specifications				
Device Connectivity	Ethernet	Ethernet/Serial	Ethernet/Serial	Ethernet, Digital Input & Output
Frequency Band(s)	2.4 & 5 GHz	2.4 & 5 GHz	Cellular	2.4 & 5 GHz
Regions Unlicensed Use Allowed	Global	Global	Global	Global
Wireless Technology	IEEE 802.11abgn (WiFi 4)	IEEE 802.11abgn (WiFi 4)	4G LTE Cellular HSPA	IEEE 802.11ax (WiFi 6)
Max Outdoor Range (miles/km)	5 mi /8 km	5 mi /8 km	Unlimited	5 mi /8 km
Fast Roaming (802.11r)	Yes	Yes	N/A	Yes
Fast Roaming (< 10 milliseconds)	Yes	Yes	N/A	-
Repeater Mode	Yes	Yes	N/A	-
Max RF Data Rate (Gross)	300 Mbps	300 Mbps	N/A	1020 Mbps
Security/Encryption	WPA2 PSK and Enterprise	WPA2 PSK and Enterprise	Internal Firewall, Belden Horizon VPN, OpenVPN, IPSec	WPA3 PSK and Enterprise
Advanced Diagnostics	Yes	Yes	N/A	Yes
Hazardous Location Approvals	Class 1, Div 2/ Atex Zone 2 (WC)	Class 1, Div 2/ Atex Zone 2	Class 1, Div 2	Class 1, Div 2/ Atex Zone 2
Outdoor/Wash Down Rated Model	IP67	-	-	-
Wireless Applications				
Mobile Robots, AGV	Yes	Yes	-	Yes
Long-Range SCADA	N/A	N/A	Yes	-
Short-Range SCADA	Yes	Yes	Yes	Yes
Mobile Worker (Wi-Fi)	Yes	Yes	-	Yes
EtherNet/IP™ Object	Yes	Yes	Yes	Yes
EtherNet/IP™ Implicit Messaging (High-Speed IO)	Yes	Yes	-	Yes
Serial DF1, ASCII, Modbus®, DNP3, etc.	-	Yes (encapsulation)	Yes (encapsulation)	-
Video	Fast Frame Rate	Fast Frame Rate	Yes	Fast Frame Rate

Check for product availability in your country.

In-Chassis Product Selection Chart

Platform	ControlLogix®	CompactLogix™	Point I/O
Protocol/Application			
AGA/API Gas & Liquid Flow Computer	MVI56E-AFC	MVI69E-AFC	
ASCII	MVI56E-GSC MVI56E-GSCXT	MVI69E-GSC	
'C' Programmable	MVI56E-LDM	MVI69E-LDM	
DNP3 Ethernet	MVI56E-DNPNET		
FA Control/Network	MVI56E-FLN		
GE Ethernet Global Data	MVI56-EGD		
Generic Ethernet ASCII	MVI56E-GEC	MVI69E-GEC	
IEC 61850 Client	MVI56E-61850C		
IEC 61850 Server	MVI56E-61850S		
Modbus® Serial	MVI56E-MCM MVI56E-MCMR MVI56E-MCMXT	MVI69E-MBS MVI69L-MBS	ILX34-MBS232 ILX34-MBS485
Modbus® TCP/IP	MVI56E-MNET MVI56E-MNETC MVI56E-MNETR MVI56E-MNETCR MVI56E-MNETXT	MVI69E-MBTCP MVI69L-MBTCP	
PROFIBUS DP Master	ILX56-PBM	ILX69-PBM	
PROFIBUS DP Slave	ILX56-PBS	ILX69-PBS	
Siemens® Industrial Ethernet	MVI56E-SIE		
PROFINET	ILX56-PNC ILX56-PND		

➔ Learn more about solutions for legacy controllers at psft.com/DB3 or by contacting your local ProSoft office

Have a legacy product that's no longer on these charts?

ProSoft can help you migrate to a newer solution with expanded functionality.

Stand-Alone Gateways Product Selection Chart

Protocol/Application		ASCII	DF1 Master/ Slave	DNP 3.0 (Serial + Ethernet)	EtherNet/IP™	HART Multidrop/ Analog (4 ch1)	IEC 60870-5- 104 Server	Modbus® Serial	Modbus® TCP/ IP	OPC UA	PROFIBUS DP Master	PROFIBUS DP Slave	PROFINET
ASCII			PLX31-EIP-ASCII PLX31-EIP-ASCII4					Contact support	Contact support				
BACnet®/IP, BACnet® MS/TP			PS-QS-2010-F (250 Pt) PS-QS-2210-F (500 Pt) PS-QS-3010-F (250 Pt) PS-QS-3110-F (500 Pt) PS-QS-3210-F (1000 Pt)					PS-QS-2010-F (250 Pt) PS-QS-2210-F (500 Pt) PS-QS-3010-F (250 Pt) PS-QS-3110-F (500 Pt) PS-QS-3210-F (1000 Pt)	PS-QS-2010-F (250 Pt) PS-QS-2210-F (500 Pt) PS-QS-3010-F (250 Pt) PS-QS-3110-F (500 Pt) PS-QS-3210-F (1000 Pt)				
DF1 Master/ Slave			PLX51-DF1-ENI PLX51-DF1-MSG					Contact support	Contact support			Contact support	
DH485			A-DH485R/B										
DNP 3.0 (Serial + Ethernet)			PLX51-DNPM PLX51-DNPS			PLX51-HART-4 (4 channel)		PLX51-DNPM PLX51-DNPS	PLX51-DNPM PLX51-DNPS			Contact support	
EtherNet/IP™		PLX31-EIP-ASCII PLX31-EIP-ASCII4	PLX51-DF1-ENI PLX51-DF1-MSG	PLX51-DNPM PLX51-DNPS	PLX35-NB2	PLX51-HART-4I (4 channel) PLX51-HART-4O	PLX32-EIP-104	PLX31-EIP-MBS PLX31-EIP-MBS4 A-MBR/B	PLX31-EIP-MBTC PLX32-EIP-MBTC PLX32-EIP-MBTC- UA A-XGPS A-MBR/B ELX3	PLX32-EIP- MBTCP-UA	PLX51-PBM	PLX51-PBS	PLX31-EIP-PND PLX32-EIP-PND PLX82-EIP-PNC
HART® Analog			PLX51-HART-4I PLX51-HART-4O						PLX51-HART-4I PLX51-HART-4O				
HART® Multi- drop			PLX51-HART-4I (4 channel) PLX51-HART-4O	PLX51-HART-4I					PLX51-HART-4I PLX51-HART-4O				
IEC 60870-5- 104 Server			PLX32-EIP-104						PLX32-MBTC-104				
IEC 61850			PLX82-EIP-61850						PLX82-MNET-61850				
LonWorks™			PS-QS-1011-F (250 Pt) PS-QS-1211-F (500 Pt)	PS-QS-1011-F (250 Pt) PS-QS-1211-F (500 Pt)				PS-QS-1011-0154 (250 Pt) PS-QS-1511-0154 (500 Pt)	PS-QS-1011-0154 (250 Pt) PS-QS-1511-0154 (500 Pt)				





Stand-Alone Gateways Product Selection Chart cont.

Protocol/Application												
Application/ Protocol	ASCII	DF1 Master/ Slave	DNP 3.0 (Serial + Ethernet)	EtherNet/IP™	HART Multidrop/ Analog (4 ch1)	IEC 60870-5- 104 Server	Modbus® Serial	Modbus® TCP/ IP	OPC UA	PROFIBUS DP Master	PROFIBUS DP Slave	PROFINET
Metasys® N2		PS-QS-2010-F (250 Pt) PS-QS-2210-F (500 Pt) PS-QS-3010-F (250 Pt) PS-QS-3110-F (500 Pt) PS-QS-3210-F (1000 Pt)		PS-QS-2010-F (250 Pt) PS-QS-2210-F (500 Pt) PS-QS-3010-F (250 Pt) PS-QS-3110-F (500 Pt) PS-QS-3210-F (1000 Pt)			PS-QS-2010-F (250 Pt) PS-QS-2210-F (500 Pt) PS-QS-3010-F (250 Pt) PS-QS-3110-F (500 Pt) PS-QS-3210-F (1000 Pt)	PS-QS-2010-F (250 Pt) PS-QS-2210-F (500 Pt) PS-QS-3010-F (250 Pt) PS-QS-3110-F (500 Pt) PS-QS-3210-F (1000 Pt)				
Modbus® Serial			PLX51-DNPS PLX51-DNPM	PLX31-EIP-MBS PLX31-EIP-MBS4 A-MBR/B	Contact support		Contact support			PLX51-PBM	PLX51-PBS	PLX31-PND-MBS PLX31-PND-MBS4
Modbus® TCP/IP	Contact support		PLX51-DNPS PLX51-DNPM	PLX31-EIP-MBTCP PLX32-EIP-MBTCP PLX32-EIP-MBTCP-UA A-XGPS A-MBR/B ELX3	PLX51-HART-40 PLX51-HART-4I	PLX32-MBTCP-104			PLX32-EIP- MBTCP-UA	PLX51-PBM	PLX51-PBS	PLX31-MBTCP-PND PLX32-MBTCP-PND PLX82-MBTCP-PNC
OPC UA				PLX32-EIP-MBTCP-UA				PLX32-EIP-MBTCP-UA				
PROFIBUS DP				PLX51-PBM PLX51-PBS			PLX51-PBM PLX51-PBS	PLX51-PBM PLX51-PBS				
PROFIBUS PA				A-PAL/B				A-PAL/B				
PROFINET				PLX31-EIP-PND PLX32-EIP-PND PLX82-EIP-PNC			PLX31-PND-MBS PLX31-PND-MBS4	PLX31-MBTCP-PND PLX32-MBTCP-PND PLX82-MBTCP-PNC				
Siemens® Industrial Ethernet				PLX31-EIP-SIE PLX32-EIP-SIE				PLX31-MBTCP-SIE PLX32-MBTCP-SIE				
CAN Protocols (CAN Open, DeviceNet, J1939)				A-CANOR/B A-DNTR/B A-J1939/B			A-CANOR/B A-DNTR/B A-J1939/B	A-CANOR/B A-DNTR/B A-J1939/B				
ControlNet				A-CNR				A-CNR				
PTP/NTP				A-TSM/B								
Data Logging	PLX51-DL-232 PLX51-DLplus-232			PLX51-DL-232 PLX51-DLplus-232			PLX51-DL-232 PLX51-DLplus-232	PLX51-DL-232 PLX51-DLplus-232				
FOUNDATION Fieldbus				A-FFL/B				A-FFL/B				

Connect to what's possible.



About Belden

Belden Inc. delivers complete connection solutions that unlock untold possibilities for our customers, their customers and the world. We advance ideas and technologies that enable a safer, smarter and more prosperous future. Throughout our 120+ year history we have evolved as a company, but our purpose remains – making connections. By connecting people, information and ideas, we make it possible. We are headquartered in St. Louis, USA and have manufacturing capabilities in North America, Europe, Asia and Africa.

For more information, visit us at:

[belden.com](https://www.belden.com)

follow us on



© 2025 | Belden and its affiliated companies claim and reserves all rights to its graphic images and text, trade names and trademarks, logos, service names, and similar proprietary marks, and any other intellectual property rights associated with this publication. BELDEN® and other distinctive identifiers of Belden and its affiliated companies as used herein are or may be pending or registered or unregistered trademarks of Belden, or its affiliates, in the United States and/or other jurisdictions throughout the world. Belden's trade names, trademarks, logos, service names, and similar proprietary marks shall not be reprinted or displayed without Belden's or its affiliated companies' permission and/or in any form inconsistent with Belden's business interests. Belden reserves the right to demand the discontinuation of any improper use at any time.