



# MarineTuff® Offshore and Marine Cable Solutions



CATALOG



Belden offers the industry's largest selection of industrial cables for offshore and marine certified applications





Whether you are handling oil, natural gas or petrochemicals, working onshore or offshore, Belden's cable, connectivity and networking solutions will solve your toughest problems.





# MarineTuff®

## About Our MarineTuff Cable Offering



### MarineTuff - Safe, Robust Cable for Offshore Applications

Thank you for choosing Belden's MarineTuff cables for your offshore cable needs. Belden is known for providing highly reliable, rugged signal transmission solutions for some of the most demanding applications. With the MarineTuff line of cables, Belden's heritage of rugged signal transmission solutions now extends to offshore applications.

### All MarineTuff cables are certified by the American Bureau of Shipping (ABS) and/or DNV (Det Norske Veritas).

The American Bureau of Shipping (ABS) is one of the governing bodies overseeing the safe construction and operation of ABS-classed vessels, modular offshore drilling units (MODUs) or facilities. Belden MarineTuff cables meet or exceed the requirements set for by ABS for offshore applications.

In addition to ABS certification, our HaloarrestXLink (low smoke zero halogen) cables meet numerous requirements for harsh offshore environments. These include UL 1309 (Marine Shipboard Cable), IEEE 1580 Type P insulation (IEEE Recommended Practice for Marine Cable for Use on Shipboard and Fixed or Floating Facilities) UL Oil Resistance II, IEEE 1202 & FT4 (Flame Resistance), IEC 60754-1 (Compliant for Halogen Content), and IEC 60754-2 (Compliant for Acid Gas Emissions). In other words, we make the toughest cables around and we've got the certifications to prove it!

DNV (Det Norske Veritas) applies to some products in this catalog. The DNV logo at the top of the page indicates there are DNV certified products on that page.

For complete details on all of the certifications each product family meets, please see the individual sections contained later in this catalog.



## MarineTuff®

About Belden



### Peace of Mind with Zero Downtime

Belden is a long-time leader in offering high-performance data and signal transmission solutions for the industrial environment where reliability is absolutely required to maintain safe operations with zero unplanned downtime.

That's why solutions for the industrial environment – one that imposes harsh or severe working conditions on active devices and media installations – are vital. At one time or another, the signaling components at these facilities will have to withstand the destructive effects of temperature extremes, humidity/moisture, dust, oil and solvents, and the potentially corrosive effects of chemicals. As if those weren't enough, add to the list ultraviolet radiation caused by extensive sunlight, electromagnetic interference and the ever-present danger of fire and explosion.

Whether you are handling oil, natural gas or petrochemicals, working onshore or offshore, Belden's cable, connectivity and networking solutions will solve your toughest problems.

### Always the Right Solution

Belden is the world's leading supplier of signal transmission solutions including cable, connectivity and active components for mission-critical applications ranging from industrial automation and alternative power generation through to professional broadcasting. Belden offers an extensive portfolio of highly specialized products for steering, control and field level, which the company produces and markets under its proprietary Belden, Hirschmann™, and Lumberg Automation™ brands. We would be glad to introduce to you our integrated product palette for industrial applications and the worldwide Belden Service.

You will find further information and technical details online at [www.belden.com](http://www.belden.com) or contact Belden Technical Support directly: Tel. 1.800.235.3361



# MarineTuff®

## Table of Contents



|   |              |
|---|--------------|
| <b>About our MarineTuff Cable Offering</b> .....  | <b>3</b>     |
| <b>About Belden</b> .....   | <b>4</b>     |
| <b>Table of Contents</b> .....  | <b>5</b>     |
| <b>Product Characteristic Symbols</b> .....   | <b>6</b>     |
| <b>Fiber Optic Cables</b> .....   | <b>7</b>     |
| Loose Tube Indoor/Outdoor Low Smoke Zero Halogen (LSZH) .....   | <b>8</b>     |
| Breakout Style Cable Tight Buffer - LSZH Indoor/Outdoor.....  | <b>9</b>     |
| <b>Industrial Ethernet Cables</b> .....   | <b>10-12</b> |
| Category 6 DataTuff Cables Unshielded, 4-Pair, 23 AWG.....  | <b>11-12</b> |
| UL Control Cables .....   | <b>13-34</b> |
| 600 V Type TC Cables, 18 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                                  | <b>14-17</b> |
| 600 V Type TC Cables, 18 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                                  | <b>17</b>    |
| 600 V Type TC Cables, 16 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                                  | <b>18-20</b> |
| 600 V Type TC Cables, 16 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                                  | <b>20</b>    |
| 600 V Type TC Cables, 14 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                                  | <b>21-23</b> |
| 600 V Type TC Cables, 14 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                                  | <b>23</b>    |
| 600 V Type TC Cables, 12 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                                  | <b>24-26</b> |
| 600 V Type TC Cables, 10 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                                  | <b>27-28</b> |
| 600 V Type TC Cables, 8 AWG, - 10 AWG Uninsulated Ground Wire, Thermoset Low Smoke Zero Halogen Jacket..... | <b>29</b>    |
| 600 V Type TC Cables, 6 AWG, - 8 AWG Uninsulated Ground Wire, Thermoset Low Smoke Zero Halogen Jacket.....  | <b>30</b>    |
| 600 V Type TC Cables, 4 AWG, - 8 AWG Uninsulated Ground Wire, Thermoset Low Smoke Zero Halogen Jacket.....  | <b>31</b>    |
| 600 V Type TC Cables, 2 AWG, - 6 AWG Uninsulated Ground Wire, Thermoset Low Smoke Zero Halogen Jacket.....  | <b>32</b>    |
| 600 V Type TC Cables, 1 AWG to 4/0 AWG, Thermoset Low Smoke Zero Halogen Jacket.....                        | <b>33-34</b> |
| <b>UL Instrumentation Cables</b> .....  | <b>35-42</b> |
| 600 V Type TC Cables, 18 AWG, Shielded, Thermoset Low Smoke Zero Halogen Jacket.....                        | <b>36-37</b> |
| 600 V Type TC Cables, 16 AWG, Shielded, Thermoset Low Smoke Zero Halogen Jacket.....                        | <b>38-40</b> |
| 600 V Type TC Cables, 14 AWG, Shielded, Thermoset Low Smoke Zero Halogen Jacket.....                        | <b>41</b>    |
| 600 V Type TC Cables, 12 AWG, Shielded, Thermoset Low Smoke Zero Halogen Jacket.....                        | <b>42</b>    |
| <b>Variable Frequency Drive (VFD) Cables</b> .....  | <b>43-47</b> |
| Classic Foil/Braid Design Thermoset Low Smoke Zero Halogen.....   | <b>44-45</b> |
| Classic Symmetrical Design Thermoset Low Smoke Zero Halogen.....  | <b>46-47</b> |
| <b>Foundation Fieldbus Cables</b> .....   | <b>48-52</b> |
| <b>PROFIBUS DP Cables</b> .....   | <b>53-55</b> |
| <b>RS-485 Cables</b> .....  | <b>56-58</b> |
| <b>ControlNet Cables</b> .....  | <b>59-61</b> |
| <b>Blue Hose Cables</b> .....   | <b>62-64</b> |
| <b>DeviceNet Cables</b> .....   | <b>65-67</b> |
| <b>A/V and Electronic Cable</b> .....   | <b>68-78</b> |
| Electronic Audio, Control and Instrumentation Cable.....  | <b>69-70</b> |
| Audio and Speaker Cable.....  | <b>71-72</b> |
| Coaxial Broadcast AV Cable.....   | <b>73-74</b> |
| DataTwist® Nonbonded Pair .....   | <b>75-76</b> |
| Security Composite Cable .....  | <b>77-78</b> |
| <b>Part Number Index</b> .....  | <b>79-82</b> |



## MarineTuff®

### Product Characteristic Symbols



Type P Insulation



Zero Halogen Jacket



Flame Retardant



Oil Resistant



Low Toxicity



Low Smoke



Low Corrosion



## MarineTuff® Industrial Fiber Cables



The demand for enhanced security and high quality data, audio, and video is increasing in the offshore environment. Therefore, the quality and reliability of your fiber optic cables is of increasing importance. MarineTuff fiber products offer quality data, audio, and video functions for offshore structures. For instance, in the event of an electromagnetic surge, fiber guarantees 100% of your communication and the network infrastructure remains available. Furthermore, fiber decreases latency and better supports the high bandwidth demands of your growing auxiliary and surveillance networks. Cost efficiency with bidirectional fiber decreases latency and expenditures of commissioning expansive networks.

In addition to offshore rigs and control room applications, Belden products are widely used in separator stations, metering stations, pumping/compressor stations, LNG processing plants, transportation/storage, refining facilities and shipboards.

The MarineTuff fiber line features all-dielectric cable, but metallic armoring can be added when needed for a specific installation. Cable designs feature flame retardant, thermoplastic buffers/tubes, aramid yarn strength members, optional aluminum armor, overall water-blocking tape and low smoke zero halogen jackets (LSZH).

### Key Attributes

- Low smoke zero halogen jacketed
- Aluminum interlock (for tight buffer) or steel corrugated (for loose tube) armoring optional
- Flame retardant
- 10 year warranty



## MarineTuff® Industrial Fiber Cables

Loose Tube Indoor/Outdoor

Low Smoke Zero Halogen (LSZH)



### Featured Options:


- Sunlight resistance
- Fully water-blocked
- Singlemode and multimode riser rated LSZH

### Certifications/Compliance

- NEC/CEC
- UL Type OFNR/OFCR
- cUL OFNR/OFCR FT-4
- Marine approvals: ABS type approval

### Construction:

1. LSZH Outer Jacket
2. Aramid Yarn
3. Central E-Glass Strength Member
4. Water Blocking Tape
5. Loose Tube Buffer



| No. of Fibers | Fibers/ Bundle | Part No.                      |                                  |                                  |                                | OD (Nom) |       |
|---------------|----------------|-------------------------------|----------------------------------|----------------------------------|--------------------------------|----------|-------|
|               |                | OM1<br>(62.5/125)<br>Std. 1Gb | OM3<br>(50/125)<br>10 Gb - 300 m | OM4<br>(50/125)<br>10 Gb - 550 m | OS2<br>Single-mode<br>Enhanced | Inch     | mm    |
| 6             | 6              | FD1L006LF                     | FD3L006LF                        | FD4L006LF                        | FDSL006LF                      | .38      | 9.65  |
| 12            | 12             | FD1L012LG                     | FD3L012LG                        | FD4L012LG                        | FDSL012LG                      |          |       |
| 24            | 12             | FD1L024LG                     | FD3L024LG                        | FD4L024LG                        | FDSL024LG                      |          |       |
| 36            | 12             | FD1L036LG                     | FD3L036LG                        | FD4L036LG                        | FDSL036LG                      | .48      | 12.18 |
| 48            | 12             | FD1L048LG                     | FD3L048LG                        | FD4L048LG                        | FDSL048LG                      |          |       |

\* Indicates common part numbers.

Standard Jacket Color: Black (non-standard jacket colors are available).



# MarineTuff® Industrial Fiber Cables

Breakout Style Cable


Tight Buffer - LSZH Indoor/Outdoor

### Featured Options:

- LSZH
- 900 um tight buffer fibers
- Flame retardant
- Direct connectorization
- Also available in a 2.5mm sub-unit

### Certifications/Compliance

- NEC/CEC
- UL Type OFNR (unarmored)/ OFCR (armored)
- cUL OFNR/OFCR FT-4
- Marine approvals: ABS type approval



FD1B004HB shown

### Construction:

1. Black Outer Jacket
2. Central E-Glass Strength Member
3. 2.0mm Subunits
4. 900 Micron Tight Buffered Fiber
5. Aramid Yarn



| No of Fibers | Fibers/Bundle | Part No.                |                           |                           |                            | OD (Nom) |       |
|--------------|---------------|-------------------------|---------------------------|---------------------------|----------------------------|----------|-------|
|              |               | OM1 (62.5/125) Std. 1Gb | OM3 (50/125) 10 Gb - 300m | OM4 (50/125) 10 Gb - 550m | "OS2 Single-mode Enhanced" | Inch     | mm    |
| 2            | 1             | FD1B002LB               | FD3B002LB                 | FD4B002LB                 | FDSB002LB                  | .260     | 6.60  |
| 4            | 1             | FD1B004LB               | FD3B004LB                 | FD4B004LB                 | FDSB004LB                  | .321     | 8.15  |
| 6            | 1             | FD1B006LB               | FD3B006LB                 | FD4B006LB                 | FDSB006LB                  | .358     | 9.09  |
| 10           | 1             | FD1B010LB               | FD3B010LB                 | FD4B010LB                 | FDSB010LB                  | .455     | 11.56 |
| 12           | 1             | FD1B012LB               | FD3B012LB                 | FD4B012LB                 | FDSB012LB                  | .514     | 13.06 |



## MarineTuff® Industrial Ethernet Cables



Only Belden offers the most comprehensive range of Industrial Ethernet cabling solutions available in the world today – all specifically engineered and ruggedly constructed to ensure optimum network performance and uptime, even in the harshest settings. Belden Industrial Ethernet cables, the DataTuff cable line, are far and away the industry's top choice for signal transmission integrity and consistently reliable electrical performance. Unlike commercial off-the-shelf (COTS) Ethernet cabling, our Category 6 copper-based cables are built Belden-tough to withstand the harsh environmental conditions and mechanical stresses typically present in offshore environments.

Belden Bonded-Pair Cables feature a patented design that bonds individual conductors along their longitudinal axis. This assures an extremely uniform spacing within each twisted pair which is a key factor in maintaining consistent electrical performance and providing optimal RFI immunity. Ideally, this distance should remain fixed and stable along the length of the twisted pair. Installation and termination of cable disturbs this relationship and therefore also affects the cable's electrical performance. Even minor disturbances in the spacing can have a significant impact on the electrical performance, particularly impedance, return loss and crosstalk. Since the two conductors of a Bonded-Pair cable are bonded together, gaps cannot form in between the conductors. The physical integrity of the pair is maintained, resulting in consistent electrical performance.

The normal cable installation stresses routing around and through tight passages typical of offshore facilities can impact cable reliability. In a recent survey, contractors indicated that Bonded-Pair cables maintain their physical integrity (and electrical performance) requiring less troubleshooting and re-work.

The performance of the entire network in a marine vessel or offshore facility depends on the integrity and reliability of the cables connecting network devices. A weak or compromised section of the cabling puts the entire network in jeopardy. The MarineTuff suite of Industrial Ethernet cabling is the best choice to meet these challenges.

### Key Attributes

- LSZH jackets on all cables and options
- Bronze braid options on all cables and options
- ABS certified
- 10 year warranty
- Consistently reliable electrical performance
- Bonded Pair Technology



# MarineTuff® Industrial Ethernet Cables

Category 6, DataTuff® Cables

Unshielded, 4-Pair, 23 AWG



## Features:

- Sunlight and Oil resistant
- Bonded Pairs
- Oil Res II (Thermoset)


## Certifications/Compliance

- ABS certified
- NEC: CMG
- CEC: CMG
- EtherNet/IP compliant
- FT4/IEEE 1202
- IEC 60332-3-22
- IEC 60754-1 (Jacket)
- IEC 60754-2 (Jacket)

## Construction:

1. LSZH Thermoplastic or Thermoset Jacket
2. Internal Tape Separator
3. Four Bonded Pairs
4. Solid Copper Conductor

NOTE: Also available on all options, bronze braid armor with LSZH second jacket not pictured





## MarineTuff® Industrial Ethernet Cables

Category 6, DataTuff® Cables

Shielded and Unshielded, 4-Pair, 23 AWG



| Part No.  | Nominal OD        |      | Additional Features/Ratings |
|---|-------------------|------|-----------------------------|
|   | Inch              | mm   |                             |
| <b>23 AWG, Shielded</b>   |                   |      |                             |
| <b>Category 6 with Overall Beldfoil Shielding • LSZH Jacket • Cable Design Under Development</b>        |                   |      |                             |
| <b>Thermoset Jacket</b>   |                   |      |                             |
| 7953Z*  | Under development |      | CMG-LS, Category 6          |
| <b>Thermoplastic Jacket</b>   |                   |      |                             |
| 7953T*  | Under development |      |                             |
| <b>23 AWG, Unshielded</b>   |                   |      |                             |
| <b>Solid BC Conductors • Polyolefin Insulation • LSZH Outer Jacket</b>                                  |                   |      |                             |
| <b>Thermoset Jacket</b>   |                   |      |                             |
| 7940Z   | 0.295             | 7.4  | CMG-LS, Category 6          |
| <b>Thermoplastic Jacket</b>   |                   |      |                             |
| 7940T   | 0.295             | 7.4  |                             |
| <b>23 AWG, Shielded with Bronze Braid Armor</b>   |                   |      |                             |
| <b>Category 6 with Overall Beldfoil Shielding • Double LSZH Jacket • Cable Design Under Development</b> |                   |      |                             |
| <b>Thermoset Jacket</b>   |                   |      |                             |
| 977953Z*  | Under development |      | CMG-LS, Category 6          |
| <b>Thermoplastic Jacket</b>   |                   |      |                             |
| 777953T*  | Under development |      |                             |
| <b>23 AWG, Unshielded with Bronze Braid Armor</b>   |                   |      |                             |
| <b>Solid BC Conductors • Polyolefin Insulation • Double LSZH Outer Jackets</b>                          |                   |      |                             |
| <b>Thermoset Jacket</b>   |                   |      |                             |
| 977940Z   | 0.43              | 11.1 | CMG-LS, Category 6          |
| <b>Thermoplastic Jacket</b>   |                   |      |                             |
| 777940T   | 0.43              | 11.1 |                             |

Conductor Color Codes: Pair 1: White/Blue Stripe & Blue • Pair 2: White/Orange Stripe & Orange • Pair 3: White/Green Stripe & Green • Pair 4: White/Brown Stripe & Brown

All reels of Bonded Pair cable come with bonded pair separator tool (part no. 1797B)

EtherNet/IP is a trademark of ODVA. To learn more visit <https://www.odva.org/Technology-Standards/EtherNet-IP/Overview>

BC = Bare Copper

\* These products are not ABS approved



# MarineTuff®

## UL Control and Instrumentation Cables



MarineTuff certified Belden instrumentation and control cables bring reliable, safety conscious wiring solutions to offshore platforms, equipment suppliers and commercial shipbuilders. These ABS-certified cables offer physical toughness and the safety benefits of low smoke and zero halogen (LSZH) jackets to provide a no-compromise solution that can withstand the harshest offshore environments. Belden's MarineTuff certified cables are highly reliable, rugged solutions that will function in a variety of challenging offshore activities: mobile drilling, fixed platform, floating production, storage and offloading (FPSO), marine vessels.

Oil and Gas platforms must continuously achieve optimal performance, while operating in harsh environments under mission-critical conditions. Demands on communication networks include safety, availability, reliability and durability in environments where vibration, corrosion, fluctuating temperature, splash water, and pollution occur. The MarineTuff instrumentation and control cables are designed to operate in these conditions.

The MarineTuff instrumentation and control line features 600V TC-ER rated multiconductor, paired, and triad cables. They feature XLP conductors appropriate for 90 degrees C wet/dry demands, class I and II / Division 2 hazardous location ratings, and HaloarrestXLink low smoke zero halogen jackets (LSZH).

### Key Attributes

- Type P rated insulations on all cables and options
- LSZH jackets on all cables and options
- Bronze braid or continuous aluminum armoring available
- ABS certified
- 10 year warranty

## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables




### Featured Options:

- Bronze Braid Armoring
- Continuous Aluminum Armor (ABS) - Type MC
- LSZH Thermoset Jacket (Standard)
- Type P Rated Insulations
- Sunlight and Oil Resistant

### Certifications/Compliance

- ABS (American Bureau of Shipping)
  - IEEE 45 Electrical Installation on Shipboard
  - IEEE 1580 Type P insulations (recommended practice for marine cables for use on shipboard in fixed or floating facilities)
  - UL 1309 marine shipboard cables
  - IEC 60811-2-1 compliant for hydrocarbon resistance
  - IEC 60754-1 compliant jacket for halogen content
  - IEC 60754-2 compliant jacket for acid gas emissions
  - IEC 60092-350 electrical installations on ships )
  - UL 1277 TC-ER crush and impact resistant (UL TC for 2-conductor cables)
  - IEEE 1202 and FT4 flame-resistant
  - IEC 60332-3-22
- \* excludes continuous armored constructions



### Construction:

1. LSZH Thermoset Jacket
2. XLP Insulation
3. Flexible Stranded Tinned Copper Conductors
4. Round and Smooth

NOTE: Also available on all options, foil shield, bronze braid armor with LSZH second jacket, continuous aluminum armor with LSZH second jacket (not pictured).



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 18 AWG, Unshielded, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom)   |           | Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|------------|-----------|------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch       | mm        | Inch             | mm  |
| <b>18 AWG • Unshielded • Thermoset Jacket • Type TC</b>                          |            |            |                    |                   |       |            |           |                  |     |
| <b>Flexible Stranded (16 x 30) TC Conductors • XLPE Insulation • LSZH Jacket</b> |            |            |                    |                   |       |            |           |                  |     |
| 27916Z   | 2          | E2         | 44                 | 3.20              | 81.3  | .21 x 0.31 | 5.3 x 7.9 | 0.05             | 1.1 |
| 27325Z   | 2          | E2         | 44                 | 3.10              | 78.7  | 0.31       | 7.9       | 0.05             | 1.1 |
| 28334Z   | 3          | E2         | 66                 | 3.30              | 83.8  | 0.33       | 8.4       | 0.05             | 1.1 |
| 28326Z   | 4          | E2         | 88                 | 3.60              | 91.4  | 0.36       | 9.1       | 0.05             | 1.1 |
| 28335Z   | 5          | E2         | 110                | 3.90              | 99.1  | 0.39       | 9.9       | 0.05             | 1.1 |
| 28600Z   | 6          | E2         | 132                | 4.20              | 106.7 | 0.41       | 10.4      | 0.05             | 1.1 |
| 28327Z   | 7          | E2         | 154                | 4.30              | 109.2 | 0.42       | 10.7      | 0.05             | 1.1 |
| 28601Z   | 8          | E2         | 176                | 4.50              | 114.3 | 0.45       | 11.4      | 0.05             | 1.1 |
| 28336Z   | 9          | E2         | 198                | 4.90              | 124.5 | 0.49       | 12.4      | 0.05             | 1.1 |
| 28328Z   | 10         | E2         | 220                | 5.70              | 144.8 | 0.56       | 14.2      | 0.06             | 1.5 |
| 28602Z   | 11         | E2         | 242                | 5.80              | 147.3 | 0.58       | 14.7      | 0.06             | 1.5 |
| 28329Z   | 12         | E2         | 264                | 5.80              | 147.3 | 0.58       | 14.7      | 0.06             | 1.5 |
| 28603Z   | 13         | E2         | 286                | 6.10              | 154.9 | 0.61       | 15.5      | 0.06             | 1.5 |
| 28604Z   | 14         | E2         | 308                | 6.10              | 154.9 | 0.61       | 15.5      | 0.06             | 1.5 |
| 28605Z   | 15         | E2         | 330                | 6.40              | 162.6 | 0.64       | 16.3      | 0.06             | 1.5 |
| 28606Z   | 16         | E2         | 352                | 6.40              | 162.6 | 0.64       | 16.3      | 0.06             | 1.5 |
| 28607Z   | 17         | E2         | 374                | 6.80              | 172.7 | 0.67       | 17.0      | 0.06             | 1.5 |
| 28608Z   | 18         | E2         | 396                | 6.80              | 172.7 | 0.67       | 17.0      | 0.06             | 1.5 |
| 28609Z   | 19         | E2         | 418                | 6.80              | 172.7 | 0.67       | 17.0      | 0.06             | 1.5 |
| 28610Z   | 20         | E2         | 440                | 7.10              | 180.3 | 0.70       | 17.8      | 0.06             | 1.5 |
| 28611Z   | 25         | E2         | 550                | 8.00              | 203.2 | 0.80       | 20.3      | 0.06             | 1.5 |
| 28612Z   | 30         | E2         | 660                | 8.30              | 210.8 | 0.82       | 20.8      | 0.06             | 1.5 |
| 28613Z   | 37         | E2         | 814                | 9.40              | 238.8 | 0.93       | 23.6      | 0.08             | 2.0 |
| 28614Z   | 50         | E2         | 1100               | 10.90             | 276.9 | 1.09       | 27.7      | 0.08             | 2.0 |
| 28632Z   | 60         | E2         | 1320               | 11.70             | 297.2 | 1.17       | 29.7      | 0.08             | 2.0 |

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>18 AWG • Unshielded • Double Thermoset Jackets • Bronze Braid Armor • Type TC (continued next page)</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (16 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                   |            |            |                    |                   |       |          |      |                  |     |                        |     |
| Z27916Z  | 2          | E2         | 44                 | 4.13              | 105.0 | 0.45     | 8.7  | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z27325Z  | 2          | E2         | 44                 | 5.45              | 105.0 | 0.45     | 8.7  | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28334Z  | 3          | E2         | 66                 | 5.69              | 111.1 | 0.47     | 9.3  | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28326Z  | 4          | E2         | 88                 | 6.05              | 120.2 | 0.50     | 10.0 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28335Z  | 5          | E2         | 110                | 6.41              | 129.4 | 0.53     | 10.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28600Z  | 6          | E2         | 132                | 6.86              | 140.7 | 0.57     | 11.7 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28327Z  | 7          | E2         | 154                | 6.98              | 143.8 | 0.58     | 12.0 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28601Z  | 8          | E2         | 176                | 7.34              | 152.9 | 0.61     | 12.7 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28336Z  | 9          | E2         | 198                | 7.82              | 165.1 | 0.65     | 13.8 | 0.05             | 1.1 | 0.06                   | 1.4 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 18 AWG, Unshielded, Thermoset Jacket



| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>18 AWG • Unshielded • Double Thermoset Jackets • Bronze Braid Armor • Type TC (continued from previous page)</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (16 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                            |            |            |                    |                   |       |          |      |                  |     |                        |     |
| Z28328Z   | 10         | E2         | 220                | 8.66              | 186.4 | 0.72     | 15.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28602Z   | 11         | E2         | 242                | 8.90              | 192.5 | 0.74     | 16.0 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28329Z   | 12         | E2         | 264                | 8.90              | 192.5 | 0.74     | 16.0 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28603Z   | 13         | E2         | 286                | 9.26              | 201.7 | 0.77     | 16.8 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28604Z   | 14         | E2         | 308                | 9.26              | 201.7 | 0.77     | 16.8 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28605Z   | 15         | E2         | 330                | 9.62              | 210.8 | 0.80     | 17.6 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28606Z   | 16         | E2         | 352                | 9.62              | 210.8 | 0.80     | 17.6 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28607Z   | 17         | E2         | 374                | 9.98              | 220.0 | 0.83     | 18.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28608Z   | 18         | E2         | 396                | 9.98              | 220.0 | 0.83     | 18.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28609Z   | 19         | E2         | 418                | 9.98              | 220.0 | 0.83     | 18.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28610Z   | 20         | E2         | 440                | 10.34             | 229.1 | 0.86     | 19.1 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28611Z   | 25         | E2         | 550                | 11.54             | 259.6 | 0.96     | 21.6 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28612Z   | 30         | E2         | 660                | 11.78             | 265.7 | 0.98     | 22.1 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28613Z   | 37         | E2         | 814                | 13.10             | 299.2 | 1.09     | 24.9 | 0.08             | 2.0 | 0.06                   | 1.4 |
| Z28614Z   | 50         | E2         | 1100               | 15.02             | 348.0 | 1.25     | 29.0 | 0.08             | 2.0 | 0.06                   | 1.4 |

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>18 AWG • Unshielded • Continuous Armor • Double Thermoset Jackets • Type MC (continued next page)</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (16 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                 |            |            |                    |                   |       |          |      |                  |     |                        |     |
| W27916Z  | 2          | E2         | 44                 | 6.98              | 177.4 | 0.58     | 14.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W27325Z  | 2          | E2         | 44                 | 6.98              | 177.4 | 0.58     | 14.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28334Z  | 3          | E2         | 66                 | 7.22              | 183.5 | 0.60     | 15.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28326Z  | 4          | E2         | 88                 | 7.58              | 192.6 | 0.63     | 16.1 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28335Z  | 5          | E2         | 110                | 7.94              | 201.8 | 0.66     | 16.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28600Z  | 6          | E2         | 132                | 8.18              | 207.9 | 0.68     | 17.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28327Z  | 7          | E2         | 154                | 8.30              | 210.9 | 0.69     | 17.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28601Z  | 8          | E2         | 176                | 8.66              | 220.1 | 0.72     | 18.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28336Z  | 9          | E2         | 198                | 9.14              | 232.3 | 0.76     | 19.4 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28328Z  | 10         | E2         | 220                | 9.98              | 253.6 | 0.83     | 21.1 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28602Z  | 11         | E2         | 242                | 10.22             | 259.7 | 0.85     | 21.6 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28329Z  | 12         | E2         | 264                | 10.22             | 259.7 | 0.85     | 21.6 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28603Z  | 13         | E2         | 286                | 10.58             | 268.8 | 0.88     | 22.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28604Z  | 14         | E2         | 308                | 10.58             | 268.8 | 0.88     | 22.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28605Z  | 15         | E2         | 330                | 10.94             | 278.0 | 0.91     | 23.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28606Z  | 16         | E2         | 352                | 10.94             | 278.0 | 0.91     | 23.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28607Z  | 17         | E2         | 374                | 11.30             | 287.1 | 0.94     | 23.9 | 0.06             | 1.5 | 0.06                   | 1.4 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 18 AWG, Unshielded and Shielded, Thermoset Jacket

| Part No. | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|------------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |            |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

18 AWG • Unshielded • Continuous Armor • Double Thermoset Jackets • Type MC (continued from previous page)

| Flexible Stranded (16 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets |    |    |     |       |       |      |      |      |     |      |     |
|---|----|----|-----|-------|-------|------|------|------|-----|------|-----|
| W28608Z   | 18 | E2 | 396 | 11.30 | 287.1 | 0.94 | 23.9 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28609Z   | 19 | E2 | 418 | 11.30 | 287.1 | 0.94 | 23.9 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28610Z   | 20 | E2 | 440 | 11.66 | 296.3 | 0.97 | 24.7 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28611Z   | 25 | E2 | 550 | 12.86 | 326.7 | 1.07 | 27.2 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28612Z   | 30 | E2 | 660 | 13.10 | 332.8 | 1.09 | 27.7 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28613Z   | 37 | E2 | 814 | 14.42 | 366.4 | 1.20 | 30.5 | 0.08 | 2.0 | 0.06 | 1.4 |

| Part No. | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    |
|----------|------------|------------|--------------------|-------------------|----|----------|----|------------------|----|
|          |            |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm |

18 AWG • Shielded 100%, Beldfoil • Thermoset Jacket • Type TC

| Flexible Stranded (16 x 30) TC Conductors • XLPE Insulation • LSZH Jacket |   |    |     |      |      |      |     |      |     |
|---|---|----|-----|------|------|------|-----|------|-----|
| 27325ZS   | 2 | E2 | 67  | 3.13 | 79.5 | 0.31 | 8.0 | 0.05 | 1.1 |
| 28334ZS   | 3 | E2 | 90  | 3.33 | 84.6 | 0.33 | 8.5 | 0.05 | 1.1 |
| 28326ZS   | 4 | E2 | 112 | 3.63 | 92.2 | 0.36 | 9.2 | 0.05 | 1.1 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 16 AWG, Unshielded, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom)    |             | Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|-------------|-------------|------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch        | mm          | Inch             | mm  |
| <b>16 AWG • Unshielded • Thermoset Jacket • Type TC</b>                          |            |            |                    |                   |       |             |             |                  |     |
| <b>Flexible Stranded (26 x 30) TC Conductors • XLPE Insulation • LSZH Jacket</b> |            |            |                    |                   |       |             |             |                  |     |
| 27917Z   | 2          | E2         | 44                 | 3.30              | 83.8  | .212 x .330 | 5.38 x 8.38 | 0.05             | 1.1 |
| 27337Z   | 2          | E2         | 44                 | 3.50              | 88.9  | 0.34        | 8.6         | 0.05             | 1.1 |
| 28331Z   | 3          | E2         | 66                 | 3.60              | 91.4  | 0.35        | 8.9         | 0.05             | 1.1 |
| 28338Z   | 4          | E2         | 88                 | 3.90              | 99.1  | 0.39        | 9.9         | 0.05             | 1.1 |
| 28339Z   | 5          | E2         | 110                | 4.30              | 109.2 | 0.42        | 10.7        | 0.05             | 1.1 |
| 28615Z   | 6          | E2         | 132                | 4.60              | 116.8 | 0.46        | 11.7        | 0.05             | 1.1 |
| 28323Z   | 7          | E2         | 154                | 4.60              | 116.8 | 0.46        | 11.7        | 0.05             | 1.1 |
| 28616Z   | 8          | E2         | 176                | 5.00              | 127.0 | 0.49        | 12.4        | 0.05             | 1.1 |
| 28340Z   | 9          | E2         | 198                | 5.70              | 144.8 | 0.56        | 14.2        | 0.05             | 1.1 |
| 28617Z   | 10         | E2         | 220                | 6.10              | 154.9 | 0.61        | 15.5        | 0.05             | 1.1 |
| 28618Z   | 11         | E2         | 242                | 6.30              | 160.0 | 0.63        | 16.0        | 0.05             | 1.1 |
| 28341Z   | 12         | E2         | 264                | 6.30              | 160.0 | 0.63        | 16.0        | 0.05             | 1.1 |
| 28619Z   | 13         | E2         | 286                | 6.60              | 167.6 | 0.66        | 16.8        | 0.05             | 1.1 |
| 28620Z   | 14         | E2         | 308                | 6.60              | 167.6 | 0.66        | 16.8        | 0.05             | 1.1 |
| 28621Z   | 15         | E2         | 330                | 7.00              | 177.8 | 0.69        | 17.5        | 0.06             | 1.5 |
| 28330Z   | 16         | E2         | 352                | 7.00              | 177.8 | 0.69        | 17.5        | 0.06             | 1.5 |
| 28622Z   | 17         | E2         | 374                | 7.40              | 188.0 | 0.73        | 18.5        | 0.06             | 1.5 |
| 28623Z   | 18         | E2         | 396                | 7.40              | 188.0 | 0.73        | 18.5        | 0.06             | 1.5 |
| 28624Z   | 19         | E2         | 418                | 7.40              | 188.0 | 0.73        | 18.5        | 0.06             | 1.5 |
| 28625Z   | 20         | E2         | 440                | 7.70              | 195.6 | 0.77        | 19.6        | 0.06             | 1.5 |
| 28324Z   | 25         | E2         | 550                | 9.20              | 233.7 | 0.91        | 23.1        | 0.08             | 2.0 |
| 28626Z   | 30         | E2         | 660                | 9.50              | 241.3 | 0.95        | 24.1        | 0.08             | 2.0 |
| 28627Z   | 37         | E2         | 814                | 10.20             | 259.1 | 1.02        | 25.9        | 0.08             | 2.0 |
| 28628Z   | 50         | E2         | 1100               | 11.90             | 302.3 | 1.19        | 30.2        | 0.08             | 2.0 |

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>16 AWG • Unshielded • Double Thermoset Jackets • Bronze Braid Armor • Type TC (continued next page)</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (26 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                   |            |            |                    |                   |       |          |      |                  |     |                        |     |
| Z27917Z  | 2          | E2         | 44                 | 5.69              | 144.6 | 0.47     | 12.0 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z27337Z  | 2          | E2         | 44                 | 5.81              | 147.7 | 0.48     | 12.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28331Z  | 3          | E2         | 66                 | 5.93              | 150.7 | 0.49     | 12.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28338Z  | 4          | E2         | 88                 | 6.41              | 162.9 | 0.53     | 13.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28339Z  | 5          | E2         | 110                | 6.98              | 177.3 | 0.58     | 14.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28615Z  | 6          | E2         | 132                | 7.46              | 189.5 | 0.62     | 15.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28323Z  | 7          | E2         | 154                | 7.46              | 189.5 | 0.62     | 15.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28616Z  | 8          | E2         | 176                | 7.82              | 198.6 | 0.65     | 16.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28340Z  | 9          | E2         | 198                | 8.66              | 220.0 | 0.72     | 18.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28617Z  | 10         | E2         | 220                | 9.26              | 235.2 | 0.77     | 19.6 | 0.05             | 1.1 | 0.06                   | 1.4 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 16 AWG, Unshielded, Thermoset Jacket



| Part No. | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|------------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |            |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

16 AWG • Unshielded • Double Thermoset Jackets • Bronze Braid Armor • Type TC (continued from previous page)

| Flexible Stranded (26 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets |    |    |     |       |       |      |      |      |     |      |     |
|---|----|----|-----|-------|-------|------|------|------|-----|------|-----|
| Z28618Z   | 11 | E2 | 242 | 9.50  | 241.3 | 0.79 | 20.1 | 0.05 | 1.1 | 0.06 | 1.4 |
| Z28341Z   | 12 | E2 | 264 | 9.50  | 241.3 | 0.79 | 20.1 | 0.05 | 1.1 | 0.06 | 1.4 |
| Z28619Z   | 13 | E2 | 286 | 9.86  | 250.4 | 0.82 | 20.9 | 0.05 | 1.1 | 0.06 | 1.4 |
| Z28620Z   | 14 | E2 | 308 | 9.86  | 250.4 | 0.82 | 20.9 | 0.05 | 1.1 | 0.06 | 1.4 |
| Z28621Z   | 15 | E2 | 330 | 10.22 | 259.6 | 0.85 | 21.6 | 0.06 | 1.5 | 0.06 | 1.4 |
| Z28330Z   | 16 | E2 | 352 | 10.22 | 259.6 | 0.85 | 21.6 | 0.06 | 1.5 | 0.06 | 1.4 |
| Z28622Z   | 17 | E2 | 374 | 10.70 | 271.8 | 0.89 | 22.6 | 0.06 | 1.5 | 0.06 | 1.4 |
| Z28623Z   | 18 | E2 | 396 | 10.70 | 271.8 | 0.89 | 22.6 | 0.06 | 1.5 | 0.06 | 1.4 |
| Z28624Z   | 19 | E2 | 418 | 10.70 | 271.8 | 0.89 | 22.6 | 0.06 | 1.5 | 0.06 | 1.4 |
| Z28625Z   | 20 | E2 | 440 | 11.18 | 284.0 | 0.93 | 23.7 | 0.06 | 1.5 | 0.06 | 1.4 |
| Z28324Z   | 25 | E2 | 550 | 12.86 | 326.6 | 1.07 | 27.2 | 0.08 | 2.0 | 0.06 | 1.4 |
| Z28626Z   | 30 | E2 | 660 | 13.34 | 338.8 | 1.11 | 28.2 | 0.08 | 2.0 | 0.06 | 1.4 |
| Z28627Z   | 37 | E2 | 814 | 14.18 | 360.2 | 1.18 | 30.0 | 0.08 | 2.0 | 0.06 | 1.4 |

| Part No. | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|------------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |            |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

16 AWG • Unshielded • Continuous Armor • Double Thermoset Jackets • Type MC (continued next page)

| Flexible Stranded (26 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets |    |    |     |       |       |      |      |      |     |      |     |
|---|----|----|-----|-------|-------|------|------|------|-----|------|-----|
| W27917Z   | 2  | E2 | 44  | 7.22  | 183.5 | 0.60 | 15.3 | 0.05 | 1.1 | 0.06 | 1.4 |
| W27337Z   | 2  | E2 | 44  | 7.34  | 186.5 | 0.61 | 15.5 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28331Z   | 3  | E2 | 66  | 7.46  | 189.6 | 0.62 | 15.8 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28338Z   | 4  | E2 | 88  | 7.94  | 201.8 | 0.66 | 16.8 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28339Z   | 5  | E2 | 110 | 8.30  | 210.9 | 0.69 | 17.6 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28615Z   | 6  | E2 | 132 | 8.78  | 223.1 | 0.73 | 18.6 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28323Z   | 7  | E2 | 154 | 8.78  | 223.1 | 0.73 | 18.6 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28616Z   | 8  | E2 | 176 | 9.14  | 232.3 | 0.76 | 19.4 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28340Z   | 9  | E2 | 198 | 9.98  | 253.6 | 0.83 | 21.1 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28617Z   | 10 | E2 | 220 | 10.58 | 268.8 | 0.88 | 22.4 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28618Z   | 11 | E2 | 242 | 10.82 | 274.9 | 0.90 | 22.9 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28341Z   | 12 | E2 | 264 | 10.82 | 274.9 | 0.90 | 22.9 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28619Z   | 13 | E2 | 286 | 11.18 | 284.1 | 0.93 | 23.7 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28620Z   | 14 | E2 | 308 | 11.18 | 284.1 | 0.93 | 23.7 | 0.05 | 1.1 | 0.06 | 1.4 |
| W28621Z   | 15 | E2 | 330 | 11.54 | 293.2 | 0.96 | 24.4 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28330Z   | 16 | E2 | 352 | 11.54 | 293.2 | 0.96 | 24.4 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28622Z   | 17 | E2 | 374 | 12.02 | 305.4 | 1.00 | 25.5 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28623Z   | 18 | E2 | 396 | 12.02 | 305.4 | 1.00 | 25.5 | 0.06 | 1.5 | 0.06 | 1.4 |
| W28624Z   | 19 | E2 | 418 | 12.02 | 305.4 | 1.00 | 25.5 | 0.06 | 1.5 | 0.06 | 1.4 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 16 AWG, Unshielded and Shielded, Thermoset Jacket



| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>16 AWG • Unshielded • Continuous Armor • Double Thermoset Jackets • Type MC (continued from previous page)</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (26 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                          |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>W28324Z</b>  | 25         | E2         | 550                | 14.18             | 360.3 | 1.18     | 30.0 | 0.08             | 2.0 | 0.06                   | 1.4 |
| <b>W28626Z</b>  | 30         | E2         | 660                | 14.66             | 372.5 | 1.22     | 31.0 | 0.08             | 2.0 | 0.06                   | 1.4 |
| <b>W28627Z</b>  | 37         | E2         | 814                | 15.50             | 393.8 | 1.29     | 32.8 | 0.08             | 2.0 | 0.06                   | 1.4 |

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |      | OD (Nom) |     | Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|------|----------|-----|------------------|-----|
|  |            |            | Lbs                | Inch              | mm   | Inch     | mm  | Inch             | mm  |
| <b>16 AWG • Shielded 100%, Beldfoil • Thermoset Jacket • Type TC</b>             |            |            |                    |                   |      |          |     |                  |     |
| <b>Flexible Stranded (26 x 30) TC Conductors • XLPE Insulation • LSZH Jacket</b> |            |            |                    |                   |      |          |     |                  |     |
| <b>27337ZS</b>   | 2          | E2         | 94                 | 3.43              | 87.1 | 0.34     | 8.7 | 0.05             | 1.1 |
| <b>28331ZS</b>   | 3          | E2         | 130                | 3.53              | 89.7 | 0.35     | 9.0 | 0.05             | 1.1 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 14 AWG, Unshielded, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom)  |           | Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|-----------|-----------|------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch      | mm        | Inch             | mm  |
| <b>14 AWG • Unshielded • Thermoset Jacket • Type TC</b>                          |            |            |                    |                   |       |           |           |                  |     |
| <b>Flexible Stranded (41 x 30) TC Conductors • XLPE Insulation • LSZH Jacket</b> |            |            |                    |                   |       |           |           |                  |     |
| 27080Z   | 2          | E2         | 108                | 3.70              | 94.0  | .24 x .37 | 6.1 x 9.4 | 0.05             | 1.1 |
| 27636Z   | 2          | E2         | 108                | 3.70              | 94.0  | 0.36      | 9.1       | 0.05             | 1.1 |
| 28081Z   | 3          | E2         | 162                | 3.80              | 96.5  | 0.38      | 9.7       | 0.05             | 1.1 |
| 28082Z   | 4          | E2         | 216                | 4.20              | 106.7 | 0.42      | 10.7      | 0.05             | 1.1 |
| 28083Z   | 5          | E2         | 270                | 4.60              | 116.8 | 0.45      | 11.4      | 0.05             | 1.1 |
| 28084Z   | 6          | E2         | 324                | 5.00              | 127.0 | 0.50      | 12.7      | 0.05             | 1.1 |
| 28085Z   | 7          | E2         | 378                | 5.00              | 127.0 | 0.50      | 12.7      | 0.05             | 1.1 |
| 28086Z   | 8          | E2         | 432                | 5.70              | 144.8 | 0.57      | 14.5      | 0.05             | 1.1 |
| 28087Z   | 9          | E2         | 486                | 6.20              | 157.5 | 0.62      | 15.7      | 0.05             | 1.1 |
| 28088Z   | 10         | E2         | 540                | 6.70              | 170.2 | 0.66      | 16.8      | 0.06             | 1.5 |
| 28089Z   | 11         | E2         | 594                | 6.90              | 175.3 | 0.68      | 17.3      | 0.06             | 1.5 |
| 28090Z   | 12         | E2         | 648                | 6.90              | 175.3 | 0.68      | 17.3      | 0.06             | 1.5 |
| 28091Z   | 13         | E2         | 702                | 7.20              | 182.9 | 0.72      | 18.3      | 0.06             | 1.5 |
| 28092Z   | 14         | E2         | 756                | 7.20              | 182.9 | 0.72      | 18.3      | 0.06             | 1.5 |
| 28093Z   | 15         | E2         | 810                | 7.60              | 193.0 | 0.76      | 19.3      | 0.06             | 1.5 |
| 28094Z   | 16         | E2         | 864                | 7.60              | 193.0 | 0.76      | 19.3      | 0.06             | 1.5 |
| 28095Z   | 17         | E2         | 918                | 8.00              | 203.2 | 0.80      | 20.3      | 0.06             | 1.5 |
| 28096Z   | 18         | E2         | 972                | 8.00              | 203.2 | 0.80      | 20.3      | 0.06             | 1.5 |
| 28097Z   | 19         | E2         | 1026               | 8.00              | 203.2 | 0.80      | 20.3      | 0.06             | 1.5 |
| 28098Z   | 20         | E2         | 1080               | 8.90              | 226.1 | 0.88      | 22.4      | 0.06             | 1.5 |
| 28099Z   | 21         | E2         | 1134               | 8.90              | 226.1 | 0.88      | 22.4      | 0.06             | 1.5 |
| 28100Z   | 22         | E2         | 1188               | 9.30              | 236.2 | 0.92      | 23.4      | 0.06             | 1.5 |
| 28101Z   | 23         | E2         | 1242               | 9.30              | 236.2 | 0.92      | 23.4      | 0.06             | 1.5 |
| 28102Z   | 24         | E2         | 1296               | 9.80              | 248.9 | 0.97      | 24.6      | 0.06             | 1.5 |
| 28103Z   | 25         | E2         | 1350               | 10.00             | 254.0 | 0.99      | 25.1      | 0.06             | 1.5 |
| 28104Z   | 26         | E2         | 1404               | 10.00             | 254.0 | 0.99      | 25.1      | 0.06             | 1.5 |
| 28105Z   | 27         | E2         | 1458               | 10.00             | 254.0 | 0.99      | 25.1      | 0.08             | 2.0 |
| 28106Z   | 28         | E2         | 1512               | 10.30             | 261.6 | 1.03      | 26.2      | 0.08             | 2.0 |
| 28107Z   | 29         | E2         | 1566               | 10.30             | 261.6 | 1.03      | 26.2      | 0.08             | 2.0 |
| 28108Z   | 30         | E2         | 1620               | 10.30             | 261.6 | 1.03      | 26.2      | 0.08             | 2.0 |
| 28629Z   | 37         | E2         | 1998               | 11.10             | 281.9 | 1.11      | 28.2      | 0.08             | 2.0 |
| 28912Z   | 50         | E2         | 2700               | 13.00             | 330.2 | 1.30      | 33.0      | 0.08             | 2.0 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 14 AWG, Unshielded, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>14 AWG • Unshielded • Double Thermoset Jackets • Bronze Braid Armor • Type TC</b>     |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (41 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| Z27080Z  | 2          | E2         | 108                | 6.17              | 156.8 | 0.51     | 13.1 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z27636Z  | 2          | E2         | 108                | 6.05              | 153.8 | 0.50     | 12.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28081Z  | 3          | E2         | 162                | 6.29              | 159.9 | 0.52     | 13.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28082Z  | 4          | E2         | 216                | 6.98              | 177.3 | 0.58     | 14.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28083Z  | 5          | E2         | 270                | 7.34              | 186.4 | 0.61     | 15.5 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28084Z  | 6          | E2         | 324                | 7.94              | 201.7 | 0.66     | 16.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28085Z  | 7          | E2         | 378                | 7.94              | 201.7 | 0.66     | 16.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28086Z  | 8          | E2         | 432                | 8.78              | 223.0 | 0.73     | 18.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28087Z  | 9          | E2         | 486                | 9.38              | 238.3 | 0.78     | 19.9 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28088Z  | 10         | E2         | 540                | 9.86              | 250.4 | 0.82     | 20.9 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28089Z  | 11         | E2         | 594                | 10.10             | 256.5 | 0.84     | 21.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28090Z  | 12         | E2         | 648                | 10.10             | 256.5 | 0.84     | 21.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28091Z  | 13         | E2         | 702                | 10.58             | 268.7 | 0.88     | 22.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28092Z  | 14         | E2         | 756                | 10.58             | 268.7 | 0.88     | 22.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28093Z  | 15         | E2         | 810                | 11.06             | 280.9 | 0.92     | 23.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28094Z  | 16         | E2         | 864                | 11.06             | 280.9 | 0.92     | 23.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28095Z  | 17         | E2         | 918                | 11.54             | 293.1 | 0.96     | 24.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28096Z  | 18         | E2         | 972                | 11.54             | 293.1 | 0.96     | 24.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28097Z  | 19         | E2         | 1026               | 11.54             | 293.1 | 0.96     | 24.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28098Z  | 20         | E2         | 1080               | 12.50             | 317.5 | 1.04     | 26.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28099Z  | 21         | E2         | 1134               | 12.50             | 317.5 | 1.04     | 26.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28100Z  | 22         | E2         | 1188               | 12.98             | 329.7 | 1.08     | 27.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28101Z  | 23         | E2         | 1242               | 12.98             | 329.7 | 1.08     | 27.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28102Z  | 24         | E2         | 1296               | 13.58             | 344.9 | 1.13     | 28.7 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28103Z  | 25         | E2         | 1350               | 13.82             | 351.0 | 1.15     | 29.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28104Z  | 26         | E2         | 1404               | 13.82             | 351.0 | 1.15     | 29.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28105Z  | 27         | E2         | 1458               | 13.82             | 351.0 | 1.15     | 29.3 | 0.08             | 2.0 | 0.06                   | 1.4 |
| Z28106Z  | 28         | E2         | 1512               | 14.30             | 363.2 | 1.19     | 30.3 | 0.08             | 2.0 | 0.06                   | 1.4 |
| Z28107Z  | 29         | E2         | 1566               | 14.30             | 363.2 | 1.19     | 30.3 | 0.08             | 2.0 | 0.06                   | 1.4 |
| Z28108Z  | 30         | E2         | 1620               | 14.30             | 363.2 | 1.19     | 30.3 | 0.08             | 2.0 | 0.06                   | 1.4 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 14 AWG, Unshielded and Shielded,  
Thermoset Jacket

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>14 AWG • Unshielded • Continuous Armor • Double Thermoset Jackets • Type MC</b>       |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (41 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| W27080Z  | 2          | E2         | 108                | 7.70              | 195.7 | 0.64     | 16.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W27636Z  | 2          | E2         | 108                | 7.58              | 192.6 | 0.63     | 16.1 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28081Z  | 3          | E2         | 162                | 7.82              | 198.7 | 0.65     | 16.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28082Z  | 4          | E2         | 216                | 8.30              | 210.9 | 0.69     | 17.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28083Z  | 5          | E2         | 270                | 8.66              | 220.1 | 0.72     | 18.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28084Z  | 6          | E2         | 324                | 9.26              | 235.3 | 0.77     | 19.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28085Z  | 7          | E2         | 378                | 9.26              | 235.3 | 0.77     | 19.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28086Z  | 8          | E2         | 432                | 10.10             | 256.6 | 0.84     | 21.4 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28087Z  | 9          | E2         | 486                | 10.70             | 271.9 | 0.89     | 22.7 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28088Z  | 10         | E2         | 540                | 11.18             | 284.1 | 0.93     | 23.7 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28089Z  | 11         | E2         | 594                | 11.42             | 290.2 | 0.95     | 24.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28090Z  | 12         | E2         | 648                | 11.42             | 290.2 | 0.95     | 24.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28091Z  | 13         | E2         | 702                | 11.90             | 302.4 | 0.99     | 25.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28092Z  | 14         | E2         | 756                | 11.90             | 302.4 | 0.99     | 25.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28093Z  | 15         | E2         | 810                | 12.38             | 314.6 | 1.03     | 26.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28094Z  | 16         | E2         | 864                | 12.38             | 314.6 | 1.03     | 26.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28095Z  | 17         | E2         | 918                | 12.86             | 326.7 | 1.07     | 27.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28096Z  | 18         | E2         | 972                | 12.86             | 326.7 | 1.07     | 27.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28097Z  | 19         | E2         | 1026               | 12.86             | 326.7 | 1.07     | 27.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28098Z  | 20         | E2         | 1080               | 13.82             | 351.1 | 1.15     | 29.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28099Z  | 21         | E2         | 1134               | 13.82             | 351.1 | 1.15     | 29.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28100Z  | 22         | E2         | 1188               | 14.30             | 363.3 | 1.19     | 30.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28101Z  | 23         | E2         | 1242               | 14.30             | 363.3 | 1.19     | 30.3 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28102Z  | 24         | E2         | 1296               | 14.90             | 378.6 | 1.24     | 31.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28103Z  | 25         | E2         | 1350               | 15.14             | 384.7 | 1.26     | 32.1 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28104Z  | 26         | E2         | 1404               | 15.14             | 384.7 | 1.26     | 32.1 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28105Z  | 27         | E2         | 1458               | 15.14             | 384.7 | 1.26     | 32.1 | 0.08             | 2.0 | 0.06                   | 1.4 |
| W28106Z  | 28         | E2         | 1512               | 15.62             | 396.8 | 1.30     | 33.1 | 0.08             | 2.0 | 0.06                   | 1.4 |
| W28107Z  | 29         | E2         | 1566               | 15.62             | 396.8 | 1.30     | 33.1 | 0.08             | 2.0 | 0.06                   | 1.4 |
| W28108Z  | 30         | E2         | 1620               | 15.62             | 396.8 | 1.30     | 33.1 | 0.08             | 2.0 | 0.06                   | 1.4 |

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  |
| <b>14 AWG • Shielded 100%, Beldfoil • Thermoset Jacket • Type TC</b>             |            |            |                    |                   |       |          |      |                  |     |
| <b>Flexible Stranded (41 x 30) TC Conductors • XLPE Insulation • LSZH Jacket</b> |            |            |                    |                   |       |          |      |                  |     |
| 28081ZS  | 3          | E2         | 99                 | 3.83              | 97.3  | 0.38     | 9.7  | 0.05             | 1.1 |
| 28082ZS  | 4          | E2         | 273                | 4.23              | 107.4 | 0.42     | 10.7 | 0.05             | 1.1 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 12 AWG, Unshielded, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  |
| <b>12 AWG • Unshielded • Thermoset Jacket • Type TC</b>                          |            |            |                    |                   |       |          |      |                  |     |
| <b>Flexible Stranded (65 x 30) TC Conductors • XLPE Insulation • LSZH Jacket</b> |            |            |                    |                   |       |          |      |                  |     |
| <b>27109Z</b>  | 2          | E2         | 172                | 4.10              | 104.1 | 0.40     | 10.2 | 0.05             | 1.1 |
| <b>27641Z</b>  | 2          | E2         | 172                | 4.10              | 104.1 | 0.40     | 10.2 | 0.05             | 1.1 |
| <b>28110Z</b>  | 3          | E2         | 258                | 4.20              | 106.7 | 0.42     | 10.7 | 0.05             | 1.1 |
| <b>28111Z</b>  | 4          | E2         | 344                | 4.60              | 116.8 | 0.46     | 11.7 | 0.05             | 1.1 |
| <b>28112Z</b>  | 5          | E2         | 430                | 5.00              | 127.0 | 0.50     | 12.7 | 0.05             | 1.1 |
| <b>28113Z</b>  | 6          | E2         | 516                | 6.00              | 152.4 | 0.59     | 15.0 | 0.05             | 1.1 |
| <b>28114Z</b>  | 7          | E2         | 602                | 6.00              | 152.4 | 0.59     | 15.0 | 0.05             | 1.1 |
| <b>28115Z</b>  | 8          | E2         | 688                | 6.40              | 162.6 | 0.64     | 16.3 | 0.06             | 1.5 |
| <b>28116Z</b>  | 9          | E2         | 774                | 6.90              | 175.3 | 0.69     | 17.5 | 0.06             | 1.5 |
| <b>28117Z</b>  | 10         | E2         | 860                | 7.50              | 190.5 | 0.75     | 19.1 | 0.06             | 1.5 |
| <b>28118Z</b>  | 11         | E2         | 946                | 7.70              | 195.6 | 0.77     | 19.6 | 0.06             | 1.5 |
| <b>28119Z</b>  | 12         | E2         | 1032               | 7.70              | 195.6 | 0.77     | 19.6 | 0.06             | 1.5 |
| <b>28120Z</b>  | 13         | E2         | 1118               | 8.10              | 205.7 | 0.81     | 20.6 | 0.06             | 1.5 |
| <b>28121Z</b>  | 14         | E2         | 1204               | 8.20              | 208.3 | 0.81     | 20.6 | 0.06             | 1.5 |
| <b>28122Z</b>  | 15         | E2         | 1290               | 9.00              | 228.6 | 0.90     | 22.9 | 0.06             | 1.5 |
| <b>28123Z</b>  | 16         | E2         | 1376               | 9.00              | 228.6 | 0.90     | 22.9 | 0.06             | 1.5 |
| <b>28124Z</b>  | 17         | E2         | 1462               | 9.50              | 241.3 | 0.95     | 24.1 | 0.06             | 1.5 |
| <b>28125Z</b>  | 18         | E2         | 1548               | 9.50              | 241.3 | 0.95     | 24.1 | 0.06             | 1.5 |
| <b>28126Z</b>  | 19         | E2         | 1634               | 9.50              | 241.3 | 0.95     | 24.1 | 0.06             | 1.5 |
| <b>28127Z</b>  | 20         | E2         | 1720               | 10.00             | 254.0 | 0.99     | 25.1 | 0.08             | 2.0 |
| <b>28128Z</b>  | 21         | E2         | 1806               | 10.00             | 254.0 | 0.99     | 25.1 | 0.08             | 2.0 |
| <b>28129Z</b>  | 22         | E2         | 1892               | 10.50             | 266.7 | 1.04     | 26.4 | 0.08             | 2.0 |
| <b>28130Z</b>  | 23         | E2         | 1978               | 10.50             | 266.7 | 1.04     | 26.4 | 0.08             | 2.0 |
| <b>28131Z</b>  | 24         | E2         | 2064               | 11.00             | 279.4 | 1.10     | 27.9 | 0.08             | 2.0 |
| <b>28132Z</b>  | 25         | E2         | 2150               | 11.30             | 287.0 | 1.12     | 28.4 | 0.08             | 2.0 |
| <b>28133Z</b>  | 26         | E2         | 2236               | 11.30             | 287.0 | 1.12     | 28.4 | 0.08             | 2.0 |
| <b>28134Z</b>  | 27         | E2         | 2322               | 11.30             | 287.0 | 1.12     | 28.4 | 0.08             | 2.0 |
| <b>28135Z</b>  | 28         | E2         | 2408               | 11.70             | 297.2 | 1.16     | 29.5 | 0.08             | 2.0 |
| <b>28136Z</b>  | 29         | E2         | 2494               | 11.70             | 297.2 | 1.16     | 29.5 | 0.08             | 2.0 |
| <b>28137Z</b>  | 30         | E2         | 2580               | 11.70             | 297.2 | 1.16     | 29.5 | 0.08             | 2.0 |
| <b>28630Z</b>  | 37         | E2         | 3182               | 12.60             | 320.0 | 1.26     | 32.0 | 0.08             | 2.0 |
| <b>28634Z</b>  | 50         | E2         | 4300               | 14.80             | 375.9 | 1.47     | 37.3 | 0.08             | 2.0 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 12 AWG, Unshielded, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>12 AWG • Unshielded • Double Thermoset Jackets • Bronze Braid Armor • Type TC</b>     |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (65 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| Z27109Z  | 2          | E2         | 172                | 6.64              | 171.2 | 0.55     | 14.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z27641Z  | 2          | E2         | 172                | 6.64              | 171.2 | 0.55     | 14.3 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28110Z  | 3          | E2         | 258                | 6.87              | 177.3 | 0.57     | 14.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28111Z  | 4          | E2         | 344                | 7.34              | 189.5 | 0.61     | 15.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28112Z  | 5          | E2         | 430                | 7.82              | 201.7 | 0.65     | 16.8 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28113Z  | 6          | E2         | 516                | 8.88              | 229.1 | 0.74     | 19.1 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28114Z  | 7          | E2         | 602                | 8.88              | 229.1 | 0.74     | 19.1 | 0.05             | 1.1 | 0.06                   | 1.4 |
| Z28115Z  | 8          | E2         | 688                | 9.47              | 244.4 | 0.79     | 20.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28116Z  | 9          | E2         | 774                | 10.06             | 259.6 | 0.84     | 21.6 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28117Z  | 10         | E2         | 860                | 10.77             | 277.9 | 0.90     | 23.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28118Z  | 11         | E2         | 946                | 11.01             | 284.0 | 0.92     | 23.7 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28119Z  | 12         | E2         | 1032               | 11.01             | 284.0 | 0.92     | 23.7 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28120Z  | 13         | E2         | 1118               | 11.48             | 296.2 | 0.96     | 24.7 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28121Z  | 14         | E2         | 1204               | 11.48             | 296.2 | 0.96     | 24.7 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28122Z  | 15         | E2         | 1290               | 12.54             | 323.6 | 1.05     | 27.0 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28123Z  | 16         | E2         | 1376               | 12.54             | 323.6 | 1.05     | 27.0 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28124Z  | 17         | E2         | 1462               | 13.13             | 338.8 | 1.09     | 28.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28125Z  | 18         | E2         | 1548               | 13.13             | 338.8 | 1.09     | 28.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28126Z  | 19         | E2         | 1634               | 13.13             | 338.8 | 1.09     | 28.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| Z28127Z  | 20         | E2         | 1720               | 13.61             | 351.0 | 1.13     | 29.3 | 0.08             | 2.0 | 0.06                   | 1.4 |
| Z28128Z  | 21         | E2         | 1806               | 13.61             | 351.0 | 1.13     | 29.3 | 0.08             | 2.0 | 0.06                   | 1.4 |
| Z28129Z  | 22         | E2         | 1892               | 14.20             | 366.3 | 1.18     | 30.5 | 0.08             | 2.0 | 0.06                   | 1.4 |
| Z28130Z  | 23         | E2         | 1978               | 14.20             | 366.3 | 1.18     | 30.5 | 0.08             | 2.0 | 0.06                   | 1.4 |
| Z28131Z  | 24         | E2         | 2064               | 14.91             | 384.6 | 1.24     | 32.0 | 0.08             | 2.0 | 0.06                   | 1.4 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 12 AWG, Unshielded, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>12 AWG • Unshielded • Continuous Armor • Double Thermoset Jackets • Type MC</b>       |            |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded (65 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b> |            |            |                    |                   |       |          |      |                  |     |                        |     |
| W27109Z  | 2          | E2         | 172                | 8.06              | 204.8 | 0.67     | 17.1 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W27641Z  | 2          | E2         | 172                | 8.06              | 204.8 | 0.67     | 17.1 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28110Z  | 3          | E2         | 258                | 8.30              | 210.9 | 0.69     | 17.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28111Z  | 4          | E2         | 344                | 8.78              | 223.1 | 0.73     | 18.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28112Z  | 5          | E2         | 430                | 9.26              | 235.3 | 0.77     | 19.6 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28113Z  | 6          | E2         | 516                | 10.34             | 262.7 | 0.86     | 21.9 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28114Z  | 7          | E2         | 602                | 10.34             | 262.7 | 0.86     | 21.9 | 0.05             | 1.1 | 0.06                   | 1.4 |
| W28115Z  | 8          | E2         | 688                | 10.94             | 278.0 | 0.91     | 23.2 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28116Z  | 9          | E2         | 774                | 11.54             | 293.2 | 0.96     | 24.4 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28117Z  | 10         | E2         | 860                | 12.26             | 311.5 | 1.02     | 26.0 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28118Z  | 11         | E2         | 946                | 12.50             | 317.6 | 1.04     | 26.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28119Z  | 12         | E2         | 1032               | 12.50             | 317.6 | 1.04     | 26.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28120Z  | 13         | E2         | 1118               | 12.98             | 329.8 | 1.08     | 27.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28121Z  | 14         | E2         | 1204               | 12.98             | 329.8 | 1.08     | 27.5 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28122Z  | 15         | E2         | 1290               | 14.06             | 357.2 | 1.17     | 29.8 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28123Z  | 16         | E2         | 1376               | 14.06             | 357.2 | 1.17     | 29.8 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28124Z  | 17         | E2         | 1462               | 14.66             | 372.5 | 1.22     | 31.0 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28125Z  | 18         | E2         | 1548               | 14.66             | 372.5 | 1.22     | 31.0 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28126Z  | 19         | E2         | 1634               | 14.66             | 372.5 | 1.22     | 31.0 | 0.06             | 1.5 | 0.06                   | 1.4 |
| W28127Z  | 20         | E2         | 1720               | 15.14             | 384.7 | 1.26     | 32.1 | 0.08             | 2.0 | 0.06                   | 1.4 |
| W28128Z  | 21         | E2         | 1806               | 15.14             | 384.7 | 1.26     | 32.1 | 0.08             | 2.0 | 0.06                   | 1.4 |
| W28129Z  | 22         | E2         | 1892               | 15.74             | 399.9 | 1.31     | 33.3 | 0.08             | 2.0 | 0.06                   | 1.4 |
| W28130Z  | 23         | E2         | 1978               | 15.74             | 399.9 | 1.31     | 33.3 | 0.08             | 2.0 | 0.06                   | 1.4 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 10 AWG, Unshielded, Thermoset Jacket



| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |        | OD (Nom) |      | Jacket Thickness |      |
|---|------------|------------|--------------------|-------------------|--------|----------|------|------------------|------|
|   |            |            | Lbs                | Inch              | mm     | Inch     | mm   | Inch             | mm   |
| <b>10 AWG • Unshielded • Thermoset Jacket • Type TC</b>                           |            |            |                    |                   |        |          |      |                  |      |
| <b>Flexible Stranded (105 x 30) TC Conductors • XLPE Insulation • LSZH Jacket</b> |            |            |                    |                   |        |          |      |                  |      |
| <b>27138Z</b>   | 2          | E2         | 296                | 4.50              | 114.3  | 0.44     | 11.2 | 0.045            | 1.14 |
| <b>27643Z</b>   | 2          | E2         | 296                | 4.50              | 114.3  | 0.44     | 11.2 | 0.045            | 1.14 |
| <b>28139Z</b>   | 3          | E2         | 444                | 4.70              | 119.38 | 0.47     | 11.9 | 0.045            | 1.14 |
| <b>28140Z</b>   | 4          | E2         | 592                | 5.20              | 132.08 | 0.51     | 13.0 | 0.045            | 1.14 |
| <b>28141Z</b>   | 5          | E2         | 740                | 6.00              | 152.4  | 0.60     | 15.2 | 0.06             | 1.52 |
| <b>28142Z</b>   | 6          | E2         | 888                | 6.60              | 167.64 | 0.65     | 16.5 | 0.06             | 1.52 |
| <b>28143Z</b>   | 7          | E2         | 1036               | 6.60              | 167.64 | 0.65     | 16.5 | 0.06             | 1.52 |
| <b>28144Z</b>   | 8          | E2         | 1184               | 7.10              | 180.34 | 0.71     | 18.0 | 0.06             | 1.52 |
| <b>28145Z</b>   | 9          | E2         | 1332               | 7.60              | 193.04 | 0.76     | 19.3 | 0.06             | 1.52 |
| <b>28146Z</b>   | 10         | E2         | 1480               | 8.70              | 220.98 | 0.87     | 22.1 | 0.06             | 1.52 |
| <b>28147Z</b>   | 11         | E2         | 1628               | 9.00              | 228.6  | 0.90     | 22.9 | 0.06             | 1.52 |
| <b>28148Z</b>   | 12         | E2         | 1776               | 9.00              | 228.6  | 0.90     | 22.9 | 0.08             | 2.03 |

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>10 AWG • Unshielded • Double Thermoset Jackets • Bronze Braid Armor • Type TC</b>      |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (105 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Z27138Z</b>  | 2          | E2         | 296                | 7.22              | 183.4 | 0.60     | 15.3 | 0.045            | 1.14 | 0.06                   | 1.4 |
| <b>Z27643Z</b>  | 2          | E2         | 296                | 7.22              | 183.4 | 0.60     | 15.3 | 0.045            | 1.14 | 0.06                   | 1.4 |
| <b>Z28139Z</b>  | 3          | E2         | 444                | 7.58              | 192.5 | 0.63     | 16.0 | 0.045            | 1.14 | 0.06                   | 1.4 |
| <b>Z28140Z</b>  | 4          | E2         | 592                | 8.06              | 204.7 | 0.67     | 17.1 | 0.045            | 1.14 | 0.06                   | 1.4 |
| <b>Z28141Z</b>  | 5          | E2         | 740                | 9.14              | 232.2 | 0.76     | 19.3 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28142Z</b>  | 6          | E2         | 888                | 9.74              | 247.4 | 0.81     | 20.6 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28143Z</b>  | 7          | E2         | 1036               | 9.74              | 247.4 | 0.81     | 20.6 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28144Z</b>  | 8          | E2         | 1184               | 10.46             | 265.7 | 0.87     | 22.1 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28145Z</b>  | 9          | E2         | 1332               | 11.06             | 280.9 | 0.92     | 23.4 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28146Z</b>  | 10         | E2         | 1480               | 12.38             | 314.5 | 1.03     | 26.2 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28147Z</b>  | 11         | E2         | 1628               | 12.74             | 323.6 | 1.06     | 27.0 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28148Z</b>  | 12         | E2         | 1776               | 12.74             | 323.6 | 1.06     | 27.0 | 0.08             | 2.03 | 0.06                   | 1.4 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 8 AWG, Unshielded - 10 AWG  
Uninsulated Ground Wire, Thermoset Jacket



| Part No. | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|------------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |            |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

**10 AWG • Unshielded • Continuous Armor • Double Thermoset Jackets • Type MC**

**Flexible Stranded (105 x 30) TC Conductors • XLPE Insulation • Double LSZH Jackets**

|                |    |    |      |       |       |      |      |       |      |      |     |
|----------------|----|----|------|-------|-------|------|------|-------|------|------|-----|
| <b>W27138Z</b> | 2  | E2 | 296  | 8.54  | 217.0 | 0.71 | 18.1 | 0.045 | 1.14 | 0.06 | 1.4 |
| <b>W27643Z</b> | 2  | E2 | 296  | 8.54  | 217.0 | 0.71 | 18.1 | 0.045 | 1.14 | 0.06 | 1.4 |
| <b>W28139Z</b> | 3  | E2 | 444  | 8.90  | 226.2 | 0.74 | 18.8 | 0.045 | 1.14 | 0.06 | 1.4 |
| <b>W28140Z</b> | 4  | E2 | 592  | 9.38  | 238.4 | 0.78 | 19.9 | 0.045 | 1.14 | 0.06 | 1.4 |
| <b>W28141Z</b> | 5  | E2 | 740  | 10.46 | 265.8 | 0.87 | 22.1 | 0.06  | 1.52 | 0.06 | 1.4 |
| <b>W28142Z</b> | 6  | E2 | 888  | 11.06 | 281.0 | 0.92 | 23.4 | 0.06  | 1.52 | 0.06 | 1.4 |
| <b>W28143Z</b> | 7  | E2 | 1036 | 11.06 | 281.0 | 0.92 | 23.4 | 0.06  | 1.52 | 0.06 | 1.4 |
| <b>W28144Z</b> | 8  | E2 | 1184 | 11.78 | 299.3 | 0.98 | 24.9 | 0.06  | 1.52 | 0.06 | 1.4 |
| <b>W28145Z</b> | 9  | E2 | 1332 | 12.38 | 314.6 | 1.03 | 26.2 | 0.06  | 1.52 | 0.06 | 1.4 |
| <b>W28146Z</b> | 10 | E2 | 1480 | 13.70 | 348.1 | 1.14 | 29.0 | 0.06  | 1.52 | 0.06 | 1.4 |
| <b>W28147Z</b> | 11 | E2 | 1628 | 14.06 | 357.2 | 1.17 | 29.8 | 0.06  | 1.52 | 0.06 | 1.4 |
| <b>W28148Z</b> | 12 | E2 | 1776 | 14.06 | 357.2 | 1.17 | 29.8 | 0.08  | 2.03 | 0.06 | 1.4 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 8 AWG, Unshielded - 10 AWG  
Uninsulated Ground Wire, Thermoset Jacket

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   |
| <b>8 AWG • Unshielded - 10 AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b> |            |            |                    |                   |       |          |      |                  |      |
| <b>Flexible Stranded (7 x 19 x 29) TC Conductors • XLPE Insulation • LSZH Jacket</b>    |            |            |                    |                   |       |          |      |                  |      |
| <b>Z28149Z</b>  | 2          | E2         | 384                | 6.00              | 152.4 | 0.60     | 15.2 | 0.06             | 1.52 |
| <b>Z28150Z</b>  | 3          | E2         | 576                | 6.40              | 162.6 | 0.63     | 16.0 | 0.06             | 1.52 |
| <b>Z28151Z</b>  | 4          | E2         | 768                | 7.00              | 177.8 | 0.69     | 17.5 | 0.06             | 1.52 |

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>8 AWG • Unshielded - 10 AWG Uninsulated Ground Wire • Bronze Braid Armor • Double Thermoset Jackets • Type TC</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (7 x 19 x 29) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                         |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Z28149Z</b>   | 2          | E2         | 296                | 9.14              | 232.2 | 0.76     | 19.3 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28150Z</b>   | 3          | E2         | 296                | 9.50              | 241.3 | 0.79     | 20.1 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28151Z</b>   | 4          | E2         | 444                | 10.22             | 259.6 | 0.85     | 21.6 | 0.06             | 1.52 | 0.06                   | 1.4 |

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>8 AWG • Unshielded - 10 AWG Uninsulated Ground Wire • Continuous Armor • Double Thermoset Jackets • Type MC</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (7 x 19 x 29) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                       |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>W28149Z</b>   | 2          | E2         | 296                | 10.46             | 265.8 | 0.87     | 22.1 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>W28150Z</b>   | 3          | E2         | 296                | 10.82             | 274.9 | 0.90     | 22.9 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>W28151Z</b>   | 4          | E2         | 444                | 11.54             | 293.2 | 0.96     | 24.4 | 0.06             | 1.52 | 0.06                   | 1.4 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 6 AWG, Unshielded - 8 AWG  
Uninsulated Ground Wire, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   |
| <b>6 AWG • Unshielded - 8 AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b> |            |            |                    |                   |       |          |      |                  |      |
| <b>Flexible Stranded (7 x 19 x 27) TC Conductors • XLPE Insulation • LSZH Jacket</b>   |            |            |                    |                   |       |          |      |                  |      |
| <b>Z28152Z</b>   | 2          | E2         | 610                | 6.8               | 172.7 | 0.67     | 17.0 | 0.06             | 1.52 |
| <b>Z28153Z</b>   | 3          | E2         | 915                | 7.2               | 182.9 | 0.71     | 18.0 | 0.06             | 1.52 |
| <b>Z28154Z</b>   | 4          | E2         | 1220               | 7.9               | 200.7 | 0.78     | 19.8 | 0.06             | 1.52 |

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>6 AWG • Unshielded - 8 AWG Uninsulated Ground Wire • Bronze Braid Armor • Double Thermoset Jackets • Type TC</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (7 x 19 x 27) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                        |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Z28152Z</b>  | 2          | E2         | 296                | 9.98              | 253.5 | 0.83     | 21.1 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28153Z</b>  | 2          | E2         | 296                | 10.46             | 265.7 | 0.87     | 22.1 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28154Z</b>  | 3          | E2         | 444                | 11.30             | 287.0 | 0.94     | 23.9 | 0.06             | 1.52 | 0.06                   | 1.4 |

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>6 AWG • Unshielded - 8 AWG Uninsulated Ground Wire • Continuous Armor • Double Thermoset Jackets • Type MC</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (7 x 19 x 27) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                      |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>W28152Z</b>  | 2          | E2         | 296                | 11.30             | 287.1 | 0.94     | 23.9 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>W28153Z</b>  | 2          | E2         | 296                | 11.78             | 299.3 | 0.98     | 24.9 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>W28154Z</b>  | 3          | E2         | 444                | 12.62             | 320.6 | 1.05     | 26.7 | 0.06             | 1.52 | 0.06                   | 1.4 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 4 AWG, Unshielded - 8 AWG

Uninsulated Ground Wire, Thermoset Jacket

| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   |
| <b>4 AWG • Unshielded - 8 AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b> |            |            |                    |                   |       |          |      |                  |      |
| <b>Flexible Stranded (7 x 19 x 25) TC Conductors • XLPE Insulation • LSZH Jacket</b>   |            |            |                    |                   |       |          |      |                  |      |
| <b>28155Z</b>  | 2          | E2         | 970                | 7.7               | 195.6 | 0.77     | 19.6 | 0.06             | 1.52 |
| <b>28156Z</b>  | 3          | E2         | 1455               | 8.2               | 208.3 | 0.81     | 20.6 | 0.08             | 2.03 |
| <b>28157Z</b>  | 4          | E2         | 1940               | 9.5               | 241.3 | 0.94     | 23.9 | 0.08             | 2.03 |

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>4 AWG • Unshielded - 8 AWG Uninsulated Ground Wire • Bronze Braid Armor • Double Thermoset Jackets • Type TC</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (7 x 19 x 25) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                        |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Z28155Z</b>  | 2          | E2         | 970                | 11.18             | 284.0 | 0.93     | 23.7 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>Z28156Z</b>  | 2          | E2         | 1455               | 11.66             | 296.2 | 0.97     | 24.7 | 0.08             | 2.03 | 0.06                   | 1.4 |
| <b>Z28157Z</b>  | 3          | E2         | 1940               | 13.22             | 335.8 | 1.10     | 28.0 | 0.08             | 2.03 | 0.06                   | 1.4 |

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>4 AWG • Unshielded - 8 AWG Uninsulated Ground Wire • Continuous Armor • Double Thermoset Jackets • Type MC</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (7 x 19 x 25) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                      |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>W28155Z</b>  | 2          | E2         | 970                | 12.50             | 317.6 | 1.04     | 26.5 | 0.06             | 1.52 | 0.06                   | 1.4 |
| <b>W28156Z</b>  | 2          | E2         | 1455               | 12.98             | 329.8 | 1.08     | 27.5 | 0.08             | 2.03 | 0.06                   | 1.4 |
| <b>W28157Z</b>  | 3          | E2         | 1940               | 14.54             | 369.4 | 1.21     | 30.8 | 0.08             | 2.03 | 0.06                   | 1.4 |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 2 AWG, Unshielded - 6 AWG  
Uninsulated Ground Wire, Thermoset Jacket



| Part No.   | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      |
|--|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|
|  |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   |
| <b>2 AWG • Unshielded - 6 AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b> |            |            |                    |                   |       |          |      |                  |      |
| <b>Flexible Stranded (7 x 19 x 23) TC Conductors • XLPE Insulation • LSZH Jacket</b>   |            |            |                    |                   |       |          |      |                  |      |
| <b>28158Z</b>  | 2          | E2         | 1544               | 9.3               | 236.2 | 0.93     | 23.6 | 0.08             | 2.03 |
| <b>28159Z</b>  | 3          | E2         | 2316               | 9.8               | 248.9 | 0.98     | 24.9 | 0.08             | 2.03 |

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>2 AWG • Unshielded - 6 AWG Uninsulated Ground Wire • Bronze Braid Armor • Double Thermoset Jackets • Type TC</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (7 x 19 x 23) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                        |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Z28158Z</b>  | 2          | E2         | 1544               | 13.10             | 332.7 | 1.09     | 27.7 | 0.08             | 2.03 | 0.06                   | 1.4 |
| <b>Z28159Z</b>  | 2          | E2         | 2316               | 13.70             | 348.0 | 1.14     | 29.0 | 0.08             | 2.03 | 0.06                   | 1.4 |

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |     |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|------|------------------------|-----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm   | Inch                   | mm  |
| <b>2 AWG • Unshielded - 6 AWG Uninsulated Ground Wire • Continuous Armor • Double Thermoset Jackets • Type MC</b> |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>Flexible Stranded (7 x 19 x 23) TC Conductors • XLPE Insulation • Double LSZH Jackets</b>                      |            |            |                    |                   |       |          |      |                  |      |                        |     |
| <b>W28158Z</b>  | 2          | E2         | 1544               | 14.42             | 366.4 | 1.20     | 30.5 | 0.08             | 2.03 | 0.06                   | 1.4 |
| <b>W28159Z</b>  | 2          | E2         | 2316               | 15.02             | 381.6 | 1.25     | 31.8 | 0.08             | 2.03 | 0.06                   | 1.4 |



# MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 1 AWG to 4/0 AWG, Unshielded,  
Thermoset Jacket

| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |    |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm |
| <b>1 AWG • Unshielded - 6AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b>   |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>Flexible Stranded (7 x 19 x 22) TC Conductors • XLPE Insulation • LSZH Jacket</b>    |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>28161Z</b>   | 2          | E2         | 2919               | 12.00             | 304.8 | 1.19     | 30.2 | 0.08             | 2.0 | –                      | –  |
| <b>1/0 AWG • Unshielded - 6AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b> |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>Flexible Stranded (7 x 19 x 21) TC Conductors • XLPE Insulation • LSZH Jacket</b>    |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>28167Z</b>   | 2          | E2         | 1690               | 11.40             | 289.6 | 1.13     | 28.7 | 0.08             | 2.0 | –                      | –  |
| <b>28168Z</b>   | 3          | E2         | 2535               | 12.10             | 307.3 | 1.21     | 30.7 | 0.08             | 2.1 | –                      | –  |
| <b>28169Z</b>   | 4          | E2         | 3380               | 13.20             | 335.3 | 1.32     | 33.5 | 0.08             | 2.1 | –                      | –  |
| <b>2/0 AWG • Unshielded - 6AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b> |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>Flexible Stranded (7 x 19 x 20) TC Conductors • XLPE Insulation • LSZH Jacket</b>    |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>28170Z</b>   | 2          | E2         | 2130               | 12.20             | 309.9 | 1.21     | 30.7 | 0.08             | 2.1 | –                      | –  |
| <b>28171Z</b>   | 3          | E2         | 3195               | 13.00             | 330.2 | 1.30     | 33.0 | 0.08             | 2.1 | –                      | –  |
| <b>28172Z</b>   | 4          | E2         | 4260               | 14.30             | 363.2 | 1.43     | 36.3 | 0.08             | 2.1 | –                      | –  |



## MarineTuff® UL Control Cable

600 V Type TC (or MC) Cables, 1 AWG to 4/0 AWG, Unshielded, Thermoset Jacket



| Part No.  | Conductors | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |    |
|---|------------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|----|
|   |            |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm |
| <b>3/0 AWG • Unshielded - 6AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b> |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>Flexible Stranded (7 x 19 x 19) TC Conductors • XLPE Insulation • LSZH Jacket</b>    |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>28173Z</b>   | 2          | E2         | 2686               | 14.20             | 360.7 | 1.41     | 35.8 | 0.08             | 2.1 | –                      | –  |
| <b>28174Z</b>   | 3          | E2         | 4029               | 15.20             | 386.1 | 1.51     | 38.4 | 0.08             | 2.1 | –                      | –  |
| <b>28175Z</b>   | 4          | E2         | 5372               | 15.50             | 393.7 | 1.55     | 39.4 | 0.08             | 2.1 | –                      | –  |
| <b>4/0 AWG • Unshielded - 6AWG Uninsulated Ground Wire • Thermoset Jacket • Type TC</b> |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>Flexible Stranded (7 x 19 x 18) TC Conductors • XLPE Insulation • LSZH Jacket</b>    |            |            |                    |                   |       |          |      |                  |     |                        |    |
| <b>28176Z</b>   | 2          | E2         | 3386               | 13.20             | 335.3 | 1.31     | 33.3 | 0.08             | 2.1 | –                      | –  |
| <b>28177Z</b>   | 3          | E2         | 5078               | 15.20             | 386.1 | 1.51     | 38.4 | 0.08             | 2.1 | –                      | –  |
| <b>28178Z</b>   | 4          | E2         | 6771               | 17.50             | 444.5 | 1.75     | 44.5 | 0.12             | 3.0 | –                      | –  |



# MarineTuff® UL Instrumentation Cable

600 V Type TC (or MC) Cables




## Featured Options:

- Bronze Braid Armoring
- Continuous Aluminum Armor (ABS) - Type MC
- LSZH Thermoset Jacket (Standard)
- Type P Rated Insulations
- Sunlight and Oil Resistant
- Unshielded, overall shield, or individually shielded

## Certifications/Compliance

- ABS (American Bureau of Shipping)
- IEEE 45 Electrical Installation on Shipboard
- IEEE 1580 Type P insulations (recommended practice for marine cables for use on shipboard in fixed or floating facilities)
- UL 1309 marine shipboard cables
- IEC 60811-2-1 compliant for hydrocarbon resistance
- IEC 60754-1 compliant jacket for halogen content
- IEC 60754-2 compliant for acid gas emissions
- IEC 60092-350 electrical installation on ships
- UL 1277 TC-ER crush and impact resistance (UL TC for 2-conductor cables)
- IEEE 1202 and FT4 flame-resistance
- IEC 60332-3-22

\*excludes continuous armored constructions



## Construction:

1. LSZH Thermoset Jacket
2. Beldfoil Shield
3. Flexible Stranded Tinned Copper Conductors
4. XLP Insulation

NOTE: Also available on all options, bronze braid armor with LSZH second jacket, continuous armor with LSZH second jacket, overall foil shield 100% coverage (not pictured).



## MarineTuff® UL Instrumentation Cable

600 V Type TC (or MC) Cables, 18 AWG, Shielded, Thermoset Jacket



| Part No. | Pairs | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    |
|----------|-------|------------|--------------------|-------------------|----|----------|----|------------------|----|
|          |       |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm |

**18 AWG • Individually Shielded Pairs + Overall Shield 100% Beldfoil • Thermoset Jacket • Type TC**

| Flexible Stranded TC Conductors • XLPE Insulation • LSZH Jacket |    |    |      |       |       |      |      |      |     |
|---|----|----|------|-------|-------|------|------|------|-----|
| 1120Z   | 1  | E2 | 59   | 3.20  | 81.3  | 0.32 | 8.1  | 0.05 | 1.2 |
| 3088Z   | 1  | E1 | 67   | 3.20  | 81.3  | 0.32 | 8.1  | 0.05 | 1.2 |
| 1048Z   | 2  | E1 | 140  | 5.10  | 129.5 | 0.51 | 13.0 | 0.05 | 1.2 |
| 1049Z   | 4  | E1 | 258  | 6.30  | 160.0 | 0.63 | 16.0 | 0.05 | 1.3 |
| 1050Z   | 8  | E1 | 350  | 8.00  | 203.2 | 0.79 | 20.1 | 0.06 | 1.6 |
| 1051Z   | 12 | E1 | 728  | 10.10 | 256.5 | 1.01 | 25.7 | 0.06 | 1.6 |
| 1052Z   | 16 | E1 | 963  | 11.30 | 287.0 | 1.12 | 28.4 | 0.08 | 2.1 |
| 1053Z   | 24 | E1 | 1434 | 13.90 | 353.1 | 1.38 | 35.1 | 0.08 | 2.1 |
| 1054Z   | 36 | E1 | 2139 | 15.90 | 403.9 | 1.58 | 40.1 | 0.08 | 2.1 |
| 1038Z   | 50 | E1 | 2962 | 19.40 | 492.8 | 1.94 | 49.3 | 0.08 | 2.1 |

| Part No. | Pairs | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|-------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |       |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

**18 AWG • Individually Shielded Pairs + Overall Shield 100% Beldfoil • Bronze Braid Armor • Double Thermoset Jackets • Type TC**

| Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets |    |    |     |       |       |      |      |      |     |      |     |
|---|----|----|-----|-------|-------|------|------|------|-----|------|-----|
| Z1120Z  | 1  | E2 | 59  | 5.57  | 141.6 | 0.46 | 11.8 | 0.05 | 1.2 | 0.06 | 1.4 |
| Z3088Z  | 1  | E1 | 67  | 5.57  | 141.6 | 0.46 | 11.8 | 0.05 | 1.2 | 0.06 | 1.4 |
| Z1048Z  | 2  | E1 | 140 | 7.85  | 199.5 | 0.65 | 16.6 | 0.05 | 1.2 | 0.06 | 1.4 |
| Z1049Z  | 4  | E1 | 258 | 9.29  | 236.1 | 0.77 | 19.7 | 0.05 | 1.3 | 0.06 | 1.4 |
| Z1050Z  | 8  | E1 | 350 | 11.21 | 284.8 | 0.93 | 23.7 | 0.06 | 1.6 | 0.06 | 1.4 |
| Z1051Z  | 12 | E1 | 728 | 13.85 | 351.9 | 1.15 | 29.3 | 0.06 | 1.6 | 0.06 | 1.4 |

| Part No. | Pairs | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|-------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |       |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

**18 AWG • Individually Shielded Pairs + Overall Shield 100% Beldfoil • Continuous Armor • Double Thermoset Jackets • Type MC**

| Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets |    |    |     |       |       |      |      |      |     |      |     |
|---|----|----|-----|-------|-------|------|------|------|-----|------|-----|
| W1120Z  | 1  | E2 | 59  | 7.10  | 180.4 | 0.59 | 15.0 | 0.05 | 1.2 | 0.06 | 1.4 |
| W3088Z  | 1  | E1 | 67  | 7.10  | 180.4 | 0.59 | 15.0 | 0.05 | 1.2 | 0.06 | 1.4 |
| W1048Z  | 2  | E1 | 140 | 9.38  | 238.4 | 0.78 | 19.9 | 0.05 | 1.2 | 0.06 | 1.4 |
| W1049Z  | 4  | E1 | 258 | 10.82 | 274.9 | 0.90 | 22.9 | 0.05 | 1.3 | 0.06 | 1.4 |
| W1050Z  | 8  | E1 | 350 | 12.74 | 323.7 | 1.06 | 27.0 | 0.06 | 1.6 | 0.06 | 1.4 |
| W1051Z  | 12 | E1 | 728 | 15.38 | 390.8 | 1.28 | 32.6 | 0.06 | 1.6 | 0.06 | 1.4 |



# MarineTuff® UL Instrumentation Cable

600 V Type TC (or MC) Cables, 18 AWG, Shielded, Thermoset Jacket



| Part No. | Triads | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    |
|----------|--------|------------|--------------------|-------------------|----|----------|----|------------------|----|
|          |        |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm |

18 AWG • Individually Shielded Triads + Overall Shield 100% Beldfoil • Thermoset Jacket • Type TC

Flexible Stranded TC Conductors • XLPE Insulation • LSZH Jacket

|       |    |    |      |       |       |      |      |      |     |
|-------|----|----|------|-------|-------|------|------|------|-----|
| 1121Z | 1  | E2 | 81   | 3.30  | 83.8  | 0.32 | 8.1  | 0.05 | 1.2 |
| 3089Z | 1  | E1 | 90   | 3.30  | 83.8  | 0.32 | 8.1  | 0.05 | 1.2 |
| 3064Z | 2  | E1 | 185  | 6.00  | 152.4 | 0.59 | 15.0 | 0.05 | 1.2 |
| 1093Z | 4  | E1 | 347  | 6.90  | 175.3 | 0.68 | 17.3 | 0.06 | 1.6 |
| 1094Z | 8  | E1 | 672  | 9.40  | 238.8 | 0.94 | 23.9 | 0.06 | 1.6 |
| 1095Z | 12 | E1 | 997  | 11.30 | 287.0 | 1.13 | 28.7 | 0.08 | 2.1 |
| 1096Z | 24 | E1 | 1971 | 15.60 | 396.2 | 1.56 | 39.6 | 0.08 | 2.1 |

| Part No. | Triads | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|--------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |        |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

18 AWG • Individually Shielded Triads + Overall Shield 100% Beldfoil • Bronze Braid Armor • Double Thermoset Jackets • Type TC

Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets

|        |   |    |     |       |       |      |      |      |     |       |     |
|--------|---|----|-----|-------|-------|------|------|------|-----|-------|-----|
| Z1121Z | 1 | E2 | 81  | 5.57  | 141.6 | 0.46 | 11.8 | 0.05 | 1.2 | 0.055 | 1.4 |
| Z3089Z | 1 | E1 | 90  | 5.57  | 141.6 | 0.46 | 11.8 | 0.05 | 1.2 | 0.055 | 1.4 |
| Z3064Z | 2 | E1 | 185 | 8.81  | 223.9 | 0.73 | 18.7 | 0.05 | 1.2 | 0.055 | 1.4 |
| Z1093Z | 4 | E1 | 347 | 9.89  | 251.3 | 0.82 | 20.9 | 0.06 | 1.6 | 0.055 | 1.4 |
| Z1094Z | 8 | E1 | 672 | 13.01 | 330.5 | 1.08 | 27.5 | 0.06 | 1.6 | 0.055 | 1.4 |

| Part No. | Triads | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|--------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |        |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

18 AWG • Individually Shielded Triads + Overall Shield 100% Beldfoil • Continuous Armor • Double Thermoset Jackets • Type MC

Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets

|        |   |    |     |       |       |      |      |      |     |      |     |
|--------|---|----|-----|-------|-------|------|------|------|-----|------|-----|
| W1121Z | 1 | E2 | 81  | 7.10  | 180.4 | 0.59 | 15.0 | 0.05 | 1.2 | 0.06 | 1.4 |
| W3089Z | 1 | E1 | 90  | 7.10  | 180.4 | 0.59 | 15.0 | 0.05 | 1.2 | 0.06 | 1.4 |
| W3064Z | 2 | E1 | 185 | 10.34 | 262.7 | 0.86 | 21.9 | 0.05 | 1.2 | 0.06 | 1.4 |
| W1093Z | 4 | E1 | 347 | 11.42 | 290.2 | 0.95 | 24.2 | 0.06 | 1.6 | 0.06 | 1.4 |
| W1094Z | 8 | E1 | 672 | 14.54 | 369.4 | 1.21 | 30.8 | 0.06 | 1.6 | 0.06 | 1.4 |



## MarineTuff® UL Instrumentation Cable

600 V Type TC (or MC) Cables, 16 AWG, Shielded, Thermoset Jacket



| Part No.  | Pairs | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |       | Jacket Thickness |     |
|---|-------|------------|--------------------|-------------------|-------|----------|-------|------------------|-----|
|   |       |            | Lbs                | Inch              | mm    | Inch     | mm    | Inch             | mm  |
| <b>16 AWG • Individually Shielded Pairs + Overall Shield 100% Beldfoil • Thermoset Jacket • Type TC</b> |       |            |                    |                   |       |          |       |                  |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • LSZH Jacket</b>                                  |       |            |                    |                   |       |          |       |                  |     |
| <b>1118Z</b>  | 1     | E2         | 105                | 3.50              | 88.9  | 0.34     | 8.64  | 0.05             | 1.2 |
| <b>3090Z</b>  | 1     | E1         | 105                | 3.50              | 88.9  | 0.34     | 8.64  | 0.05             | 1.2 |
| <b>1055Z</b>  | 2     | E1         | 223                | 5.90              | 149.9 | 0.58     | 14.73 | 0.05             | 1.2 |
| <b>1037Z</b>  | 3     | E1         | 290                | 6.20              | 157.5 | 0.62     | 15.75 | 0.05             | 1.2 |
| <b>1039Z</b>  | 4     | E1         | 411                | 6.80              | 172.7 | 0.68     | 17.27 | 0.06             | 1.6 |
| <b>1040Z</b>  | 6     | E1         | 428                | 8.00              | 203.2 | 0.80     | 20.32 | 0.06             | 1.6 |
| <b>1041Z</b>  | 8     | E1         | 786                | 9.00              | 228.6 | 0.90     | 22.86 | 0.06             | 1.6 |
| <b>1042Z</b>  | 12    | E1         | 1161               | 11.00             | 279.4 | 1.10     | 27.94 | 0.09             | 2.2 |
| <b>1043Z</b>  | 16    | E1         | 1537               | 12.30             | 312.4 | 1.22     | 30.99 | 0.09             | 2.2 |
| <b>1044Z</b>  | 20    | E1         | 1912               | 13.60             | 345.4 | 1.36     | 34.54 | 0.09             | 2.2 |
| <b>1045Z</b>  | 24    | E1         | 2287               | 15.20             | 386.1 | 1.51     | 38.35 | 0.09             | 2.2 |
| <b>1046Z</b>  | 36    | E1         | 3413               | 18.10             | 459.7 | 1.80     | 45.72 | 0.09             | 2.2 |
| <b>1047Z</b>  | 50    | E1         | 4726               | 21.20             | 538.5 | 2.12     | 53.85 | 0.12             | 3.0 |

| Part No.   | Pairs | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|--|-------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|  |       |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>16 AWG • Individually Shielded Pairs + Overall Shield 100% Beldfoil • Bronze Braid Armor • Double Thermoset Jackets • Type TC</b> |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets</b>   |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Z1118Z</b>  | 1     | E2         | 105                | 5.81              | 147.7 | 0.48     | 12.3 | 0.05             | 1.2 | 0.06                   | 1.4 |
| <b>Z3090Z</b>  | 1     | E1         | 105                | 5.81              | 147.7 | 0.48     | 12.3 | 0.05             | 1.2 | 0.06                   | 1.4 |
| <b>Z1055Z</b>  | 2     | E1         | 223                | 8.69              | 220.8 | 0.72     | 18.4 | 0.05             | 1.2 | 0.06                   | 1.4 |
| <b>Z1037Z</b>  | 3     | E1         | 290                | 9.17              | 233.0 | 0.76     | 19.4 | 0.05             | 1.2 | 0.06                   | 1.4 |
| <b>Z1039Z</b>  | 4     | E1         | 411                | 9.89              | 251.3 | 0.82     | 20.9 | 0.06             | 1.6 | 0.06                   | 1.4 |
| <b>Z1040Z</b>  | 6     | E1         | 428                | 11.33             | 287.9 | 0.94     | 24.0 | 0.06             | 1.6 | 0.06                   | 1.4 |
| <b>Z1041Z</b>  | 8     | E1         | 786                | 12.53             | 318.3 | 1.04     | 26.5 | 0.06             | 1.6 | 0.06                   | 1.4 |
| <b>Z1042Z</b>  | 12    | E1         | 1161               | 14.93             | 379.3 | 1.24     | 31.6 | 0.09             | 2.2 | 0.06                   | 1.4 |



# MarineTuff® UL Instrumentation Cable

600 V Type TC (or MC) Cables, 16 AWG, Shielded, Thermoset Jacket



| Part No. | Pairs | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|-------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |       |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

**16 AWG • Individually Shielded Pairs + Overall Shield 100% Beldfoil • Continuous Armor • Double Thermoset Jackets • Type MC**

**Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets**

|               |   |    |     |       |       |      |      |      |     |      |     |
|---------------|---|----|-----|-------|-------|------|------|------|-----|------|-----|
| <b>W1118Z</b> | 1 | E2 | 105 | 7.34  | 186.5 | 0.61 | 15.5 | 0.05 | 1.2 | 0.06 | 1.4 |
| <b>W3090Z</b> | 1 | E1 | 105 | 7.34  | 186.5 | 0.61 | 15.5 | 0.05 | 1.2 | 0.06 | 1.4 |
| <b>W1055Z</b> | 2 | E1 | 223 | 10.22 | 259.7 | 0.85 | 21.6 | 0.05 | 1.2 | 0.06 | 1.4 |
| <b>W1037Z</b> | 3 | E1 | 290 | 10.70 | 271.9 | 0.89 | 22.7 | 0.05 | 1.2 | 0.06 | 1.4 |
| <b>W1039Z</b> | 4 | E1 | 411 | 11.42 | 290.2 | 0.95 | 24.2 | 0.06 | 1.6 | 0.06 | 1.4 |
| <b>W1040Z</b> | 6 | E1 | 428 | 12.86 | 326.7 | 1.07 | 27.2 | 0.06 | 1.6 | 0.06 | 1.4 |
| <b>W1041Z</b> | 8 | E1 | 786 | 14.06 | 357.2 | 1.17 | 29.8 | 0.06 | 1.6 | 0.06 | 1.4 |

| Part No. | Triads | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    |
|----------|--------|------------|--------------------|-------------------|----|----------|----|------------------|----|
|          |        |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm |

**16 AWG • Individually Shielded Triads + Overall Shield 100% Beldfoil • Thermoset Jacket • Type TC**

**Flexible Stranded TC Conductors • XLPE Insulation • LSZH Jacket**

|              |    |    |      |       |       |      |      |      |     |
|--------------|----|----|------|-------|-------|------|------|------|-----|
| <b>1119Z</b> | 1  | E2 | 129  | 3.60  | 91.4  | 0.35 | 8.9  | 0.05 | 1.2 |
| <b>3091Z</b> | 1  | E1 | 129  | 3.60  | 91.4  | 0.35 | 8.9  | 0.05 | 1.2 |
| <b>1097Z</b> | 4  | E1 | 554  | 7.40  | 188.0 | 0.74 | 18.8 | 0.06 | 1.6 |
| <b>1098Z</b> | 8  | E1 | 1072 | 10.20 | 259.1 | 1.02 | 25.9 | 0.09 | 2.2 |
| <b>1099Z</b> | 12 | E1 | 1590 | 12.40 | 315.0 | 1.24 | 31.5 | 0.09 | 2.2 |
| <b>3118Z</b> | 16 | E1 | 1771 | 15.10 | 383.5 | 1.51 | 38.4 | 0.09 | 2.2 |
| <b>1100Z</b> | 24 | E1 | 3144 | 17.90 | 454.7 | 1.78 | 45.2 | 0.09 | 2.2 |
| <b>3130Z</b> | 36 | E1 | 3600 | 22.60 | 574.0 | 2.26 | 57.4 | 0.11 | 2.8 |

| Part No. | Triads | Color Code | Pull Tension (Max) | Bend Radius (Min) |    | OD (Nom) |    | Jacket Thickness |    | Outer Jacket Thickness |    |
|----------|--------|------------|--------------------|-------------------|----|----------|----|------------------|----|------------------------|----|
|          |        |            | Lbs                | Inch              | mm | Inch     | mm | Inch             | mm | Inch                   | mm |

**16 AWG • Individually Shielded Triads + Overall Shield 100% Beldfoil • Bronze Braid Armor • Double Thermoset Jackets • Type TC**

**Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets**

|               |   |    |      |       |       |      |      |      |     |      |     |
|---------------|---|----|------|-------|-------|------|------|------|-----|------|-----|
| <b>Z1119Z</b> | 1 | E2 | 129  | 9.77  | 248.0 | 0.38 | 9.8  | 0.05 | 1.2 | 0.06 | 1.4 |
| <b>Z3091Z</b> | 1 | E1 | 129  | 9.77  | 248.0 | 0.38 | 9.8  | 0.05 | 1.2 | 0.06 | 1.4 |
| <b>Z1097Z</b> | 4 | E1 | 554  | 20.11 | 510.8 | 0.79 | 20.1 | 0.06 | 1.6 | 0.06 | 1.4 |
| <b>Z1098Z</b> | 8 | E1 | 1072 | 27.22 | 691.4 | 1.07 | 27.2 | 0.09 | 2.2 | 0.06 | 1.4 |



## MarineTuff® UL Instrumentation Cable

600 V Type TC (or MC) Cables, 16 AWG, Shielded, Thermoset Jacket



| Part No.  | Triads | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|---|--------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|   |        |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>16 AWG • Individually Shielded Triads + Overall Shield 100% Beldfoil • Continuous Armor • Double Thermoset Jackets • Type MC</b> |        |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets</b>  |        |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>W1119Z</b>   | 1      | E2         | 129                | 13.00             | 330.3 | 0.51     | 13.0 | 0.05             | 1.2 | 0.06                   | 1.4 |
| <b>W3091Z</b>   | 1      | E1         | 129                | 13.00             | 330.3 | 0.51     | 13.0 | 0.05             | 1.2 | 0.06                   | 1.4 |
| <b>W1097Z</b>   | 4      | E1         | 554                | 22.91             | 581.9 | 0.90     | 22.9 | 0.06             | 1.6 | 0.06                   | 1.4 |
| <b>W1098Z</b>   | 8      | E1         | 1072               | 30.02             | 762.6 | 1.18     | 30.0 | 0.09             | 2.2 | 0.06                   | 1.4 |



# MarineTuff® UL Instrumentation Cable

600 V Type TC (or MC) Cables, 14 AWG, Shielded, Thermoset Jacket



| Part No.  | Pairs | Color Code | Pull Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |     |
|---|-------|------------|--------------------|-------------------|-------|----------|------|------------------|-----|------------------------|-----|
|   |       |            | Lbs                | Inch              | mm    | Inch     | mm   | Inch             | mm  | Inch                   | mm  |
| <b>14 AWG • Overall Shield 100% Beldfoil • Thermoset Jacket • Type TC</b>   |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • LSZH Jacket</b>  |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>3080Z</b>  | 1     | E1         | 160                | 3.70              | 94.0  | 0.37     | 9.4  | 0.05             | 1.2 | –                      | –   |
| <b>14 AWG • Overall Shield 100% Beldfoil • Bronze Braid Armor • Double Thermoset Jackets • Type TC</b>                              |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets</b>  |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Z3080Z</b>   | 1     | E1         | 160                | 6.17              | 0.6   | 0.51     | 13.1 | 0.05             | 1.2 | 0.06                   | 1.4 |
| <b>14 AWG • Individually Shielded Pairs + Overall Shield 100% Beldfoil • Continuous Armor • Double Thermoset Jackets • Type MC</b>  |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets</b>  |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>W3080Z</b>   | 1     | E1         | 160                | 7.70              | 195.7 | 0.64     | 16.3 | 0.05             | 1.2 | 0.06                   | 1.4 |
| <b>14 AWG • Overall Shield 100% Beldfoil Triads • Thermoset Jacket • Type TC</b>  |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • LSZH Jacket</b>  |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>3081Z</b>  | 1     | E1         | 200                | 3.80              | 96.5  | 0.38     | 9.7  | 0.05             | 1.2 | –                      | –   |
| <b>14 AWG • Overall Shield 100% Beldfoil Triads • Bronze Braid Armor • Double Thermoset Jackets • Type TC</b>                       |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets</b>  |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Z3081Z</b>   | 1     | E1         | 200                | 6.29              | 159.9 | 0.52     | 13.3 | 0.05             | 1.2 | 0.055                  | 1.4 |
| <b>14 AWG • Individually Shielded Triads + Overall Shield 100% Beldfoil • Continuous Armor • Double Thermoset Jackets • Type MC</b> |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets</b>  |       |            |                    |                   |       |          |      |                  |     |                        |     |
| <b>W3081Z</b>   | 1     | E1         | 200                | 7.82              | 198.7 | 0.65     | 16.6 | 0.05             | 1.2 | 0.055                  | 1.4 |



## MarineTuff® UL Instrumentation Cable

600 V Type TC (or MC) Cables, 12 AWG, Shielded,  
Thermoset Jacket



| Part No.   | Pairs | Color Code | Pull Tension (Max) |      | Bend Radius (Min) |      | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |  |
|--|-------|------------|--------------------|------|-------------------|------|----------|------|------------------|------|------------------------|--|
|  |       |            | Lbs                | Inch | mm                | Inch | mm       | Inch | mm               | Inch | mm                     |  |
| <b>12 AWG • Overall Shield 100% Beldfoil • Thermoset Jacket • Type TC</b>  |       |            |                    |      |                   |      |          |      |                  |      |                        |  |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • LSZH Jacket</b>   |       |            |                    |      |                   |      |          |      |                  |      |                        |  |
| <b>3103Z</b>   | 1     | E1         | 253                | 4.10 | 104.1             | 0.41 | 10.4     | 0.05 | 1.2              | –    | –                      |  |
| <b>12 AWG • Overall Shield 100% Beldfoil • Bronze Braid Armor • Double Thermoset Jackets • Type TC</b>                             |       |            |                    |      |                   |      |          |      |                  |      |                        |  |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets</b>   |       |            |                    |      |                   |      |          |      |                  |      |                        |  |
| <b>Z3103Z</b>  | 1     | E1         | 253                | 6.86 | 174.2             | 0.57 | 14.5     | 0.05 | 1.2              | 0.06 | 1.4                    |  |
| <b>14 AWG • Individually Shielded Pairs + Overall Shield 100% Beldfoil • Continuous Armor • Double Thermoset Jackets • Type MC</b> |       |            |                    |      |                   |      |          |      |                  |      |                        |  |
| <b>Flexible Stranded TC Conductors • XLPE Insulation • Double LSZH Jackets</b>   |       |            |                    |      |                   |      |          |      |                  |      |                        |  |
| <b>W3103Z</b>  | 1     | E1         | 253                | 8.18 | 14.6              | 0.68 | 17.3     | 0.05 | 1.2              | 0.06 | 1.4                    |  |



# MarineTuff®

## Variable Frequency Drive (VFD) Cables



It is important to select a motor drive cable that has been properly designed and engineered to address all the key technical issues that such a component faces.

In offshore environments with multiple drives, increased vulnerability to noise exists. This noise emission can sometimes be difficult to track down and eliminate and is likely the single most significant problem associated with VFD systems today. Unless a proper cable shielding design is present to control it, noise emission from a drive system cable can disrupt operations. Moreover, because a longer cable radiates more noise, the length of cable runs must be limited. That, in turn, puts a limitation on your shipboard layout. Choosing well-designed, robust VFD cables ensures motor uptime and reliability of the VFD system and also provides protection for any sensitive instrumentation and adjacent control systems.

- The MarineTuff VFD line features XLP conductors appropriate for 90°C wet/dry demands, Class I and II / Division 2 hazardous location ratings, and HaloarrestXLink™ low smoke zero halogen jackets (LSZH).
- All options are rated 600V UL 1277 TC-ER and 1000V UL Flexible Motor Supply, UL 1309, IEEE 1580 Type P, UL 1685 Vertical Tray Flame tested, RoHS compliant and CE approved.

### Key Attributes

- Thermoset LSZH jacket standard
- Bronze braid armoring available as option
- ABS certified
- 10 year warranty



## MarineTuff® VFD Cable

Classic Foil/Braid Design Thermoset Low Smoke Zero Halogen




### Features:

- Low Smoke Zero Halogen (LSZH) jacketed, Type P insulations
- 300% ground for enhanced system reliability and human safety. Approximately 300% of 1 full-sized conductor in ground potential copper
- Finely stranded tinned copper conductors for ease of cable installation, high frequency performance, vibration, corrosion and heat resistance
- Low capacitance XLP insulation protects motor by reducing magnitude of reflected wave
- Foil/Braid shielding enables noise control, improves common mode current containment and prevents capacitive coupling

### Certifications/Compliance:

- ABS (American Bureau of Shipping)
- IEEE 45 Electrical Installation on Shipboard
- IEEE 1580 Type P insulations IEEE recommended practice for use on shipboard in fixed or floating facilities
- UL 1309 marine shipboard cables
- IEC 60811-2-1 Hydrocarbon Resistant
- IEC 60754-1,-2 (acid gas emissions)
- 600V UL 1277 Type TC-ER
- 1000V UL Flexible Motor Supply
- IEEE 1202/383, CSA FT4 Flame Tests
- IEC 60332-3-22 Cat A Flame Test
- -40°C Cold Bend
- RHW-2/XHHW-2 Rated Conductors (16 AWG XHHW-2 only)
- 90°C Wet/Dry
- Oil Res II
- Sunlight Resistant



### Construction:

1. 16 to 2 AWG - Three Finely-Stranded Tinned Copper (TC) Circuit Conductors with XLP Insulation
2. One Full-Sized Green/Yellow XLP Insulated Ground (Same AWG as Circuit Conductors)
3. One Full-Sized, Tinned, Uninsulated Ground/Drain
4. Overall Duofoil® Shield + 85% TC Braid
5. LSZH Thermoset Jacket



# MarineTuff® VFD Cable

Classic Foil/Braid Design Thermoset Low Smoke Zero Halogen



| Part No.                              | Conductor |           | Pulling Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |      |
|---------------------------------------|-----------|-----------|-----------------------|-------------------|-------|----------|------|------------------|------|------------------------|------|
|                                       | AWG       | Stranding |                       | Lbs               | Inch  | mm       | Inch | mm               | Lbs  | mm                     | Inch |
| <b>16 to 2 AWG • Thermoset Jacket</b> |           |           |                       |                   |       |          |      |                  |      |                        |      |
| 29500X                                | 16        | 26x30     | 128                   | 4.3               | 109.2 | 0.53     | 13.5 | 0.07             | 1.85 | –                      | –    |
| 29501X                                | 14        | 41x30     | 212                   | 4.8               | 121.9 | 0.60     | 15.2 | 0.07             | 1.85 | –                      | –    |
| 29502X                                | 12        | 65x30     | 336                   | 5.2               | 132   | 0.65     | 16.5 | 0.07             | 1.85 | –                      | –    |
| 29503X                                | 10        | 105x30    | 592                   | 5.5               | 139.7 | 0.69     | 17.5 | 0.07             | 1.85 | –                      | –    |
| 29504X                                | 8         | 7x19x29   | 768                   | 7.5               | 190.5 | 0.93     | 23.6 | 0.09             | 2.36 | –                      | –    |
| 29505X                                | 6         | 7x19x27   | 1220                  | 8.0               | 203.2 | 1.02     | 25.9 | 0.09             | 2.36 | –                      | –    |
| 29506X                                | 4         | 7x19x25   | 1940                  | 9.3               | 236.2 | 1.16     | 29.5 | 0.09             | 2.36 | –                      | –    |
| 29507X                                | 2         | 7x19x23   | 3088                  | 10.8              | 273.1 | 1.31     | 33.3 | 0.09             | 2.36 | –                      | –    |

Conductor Color Coding: ICEA Method 4: Black and Numbered, Green/Yellow Ground.

| Part No.   | Conductor |           | Pulling Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |      |
|--|-----------|-----------|-----------------------|-------------------|-------|----------|------|------------------|------|------------------------|------|
|  | AWG       | Stranding |                       | Lbs               | Inch  | mm       | Inch | mm               | Lbs  | mm                     | Inch |
| <b>16 to 2 AWG • Bronze Braid Armor • Double Thermoset Jackets</b> |           |           |                       |                   |       |          |      |                  |      |                        |      |
| Z29500X  | 16        | 26x30     | 128                   | 8.30              | 210.8 | 0.69     | 17.6 | 0.07             | 1.85 | 0.06                   | 1.4  |
| Z29501X  | 14        | 41x30     | 212                   | 9.14              | 232.2 | 0.76     | 19.3 | 0.07             | 1.85 | 0.06                   | 1.4  |
| Z29502X  | 12        | 65x30     | 336                   | 9.74              | 247.4 | 0.81     | 20.6 | 0.07             | 1.85 | 0.06                   | 1.4  |
| Z29503X  | 10        | 105x30    | 592                   | 10.22             | 259.6 | 0.85     | 21.6 | 0.07             | 1.85 | 0.06                   | 1.4  |
| Z29504X  | 8         | 7x19x29   | 768                   | 13.10             | 332.7 | 1.09     | 27.7 | 0.09             | 2.36 | 0.06                   | 1.4  |
| Z29505X  | 6         | 7x19x27   | 1220                  | 14.18             | 360.2 | 1.18     | 30.0 | 0.09             | 2.36 | 0.06                   | 1.4  |

Conductor Color Coding: ICEA Method 4: Black and Numbered, Green/Yellow Ground.

| Part No.   | Conductor |           | Pulling Tension (Max) | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |      | Outer Jacket Thickness |      |
|--|-----------|-----------|-----------------------|-------------------|-------|----------|------|------------------|------|------------------------|------|
|  | AWG       | Stranding |                       | Lbs               | Inch  | mm       | Inch | mm               | Lbs  | mm                     | Inch |
| <b>16 to 2 AWG • Continuous Armor • Double Thermoset Jackets</b> |           |           |                       |                   |       |          |      |                  |      |                        |      |
| W29500X  | 16        | 26x30     | 128                   | 9.62              | 244.4 | 0.80     | 20.4 | 0.07             | 1.85 | 0.06                   | 1.4  |
| W29501X  | 14        | 41x30     | 212                   | 10.46             | 265.8 | 0.87     | 22.1 | 0.07             | 1.85 | 0.06                   | 1.4  |
| W29502X  | 12        | 65x30     | 336                   | 11.06             | 281.0 | 0.92     | 23.4 | 0.07             | 1.85 | 0.06                   | 1.4  |
| W29503X  | 10        | 105x30    | 592                   | 11.54             | 293.2 | 0.96     | 24.4 | 0.07             | 1.85 | 0.06                   | 1.4  |
| W29504X  | 8         | 7x19x29   | 768                   | 14.42             | 366.4 | 1.20     | 30.5 | 0.09             | 2.36 | 0.06                   | 1.4  |
| W29505X  | 6         | 7x19x27   | 1220                  | 15.50             | 393.8 | 1.29     | 32.8 | 0.09             | 2.36 | 0.06                   | 1.4  |

Conductor Color Coding: ICEA Method 4: Black and Numbered, Green/Yellow Ground.

## MarineTuff® VFD Cable

Classic Symmetrical Design Thermoset Low Smoke Zero Halogen




### Features:

- Low Smoke Zero Halogen (LSZH) jacketed, Type P insulations
- 100% Ground - 3 Symmetrical Ground Conductors
- Finely stranded tinned copper conductors for ease of cable installation, high frequency performance, vibration, corrosion and heat resistance
- Low capacitance XLP insulation protects motor by reducing magnitude of reflected wave
- 100% Dual copper tape shielding for enhanced flexibility and noise control

### Certifications/Compliance:

- ABS (American Bureau of Shipping)
- IEEE 45 Electrical Installation on Shipboard
- IEEE 1580 Type P Insulations IEEE recommended practice for use on shipboard in fixed or floating facilities
- UL 1309 marine shipboard cables
- IEC 60811-2-1 Hydrocarbon Resistant
- IEC 60754-1,-2 (acid gas emissions)
- 600V UL 1277 Type TC-ER
- 1000V UL Flexible Motor Supply
- IEEE 1202/383, CSA FT4 Flame Tests
- IEC 60332-3-22 Cat A Flame Test
- -40C Cold Bend
- XHHW-2 Rated Conductors
- 90°C Wet/Dry
- Oil Res II
- Sunlight Resistant



### Construction:

1. 1 to 4/0 AWG - Three Finely-Stranded Tinned Copper (TC) Circuit Conductors with XLP Insulation
2. Three Symmetrical Bare Copper (BC) Uninsulated Grounds (equivalent to 1 full-sized ground)
3. Two Spiral Copper Tape Shields (100% Coverage)
4. LSZH Thermoset Jacket



# MarineTuff® VFD Cable

Classic Symmetrical Design Thermoset Low Smoke  
Zero Halogen



| Part No.                               | Conductor |           | Pulling Tension (Max)<br>Lbs | Bend Radius (Min) |       | OD (Nom) |      | Jacket Thickness |     | Outer Jacket Thickness |    |
|--|-----------|-----------|------------------------------|-------------------|-------|----------|------|------------------|-----|------------------------|----|
|  | AWG       | Stranding |                              | Inch              | mm    | Inch     | mm   | Lbs              | mm  | Inch                   | mm |
| <b>1 to 4/0 AWG • Thermoset Jacket</b> |           |           |                              |                   |       |          |      |                  |     |                        |    |
| <b>29528X</b>                          | 1         | 7X19X22   | 2650                         | 12.00             | 304.8 | 1.20     | 30.5 | 0.08             | 2.1 | –                      | –  |
| <b>29529X</b>                          | 1/0       | 7X19X21   | 3537                         | 12.90             | 327.7 | 1.29     | 32.8 | 0.08             | 2.1 | –                      | –  |
| <b>29530X</b>                          | 2/0       | 7X19X20   | 4200                         | 14.00             | 355.6 | 1.40     | 35.6 | 0.08             | 2.1 | –                      | –  |
| <b>29531X</b>                          | 3/0       | 7X19X19   | 5025                         | 15.20             | 386.1 | 1.52     | 38.6 | 0.08             | 2.1 | –                      | –  |
| <b>29532X</b>                          | 4/0       | 7X19X18   | 6670                         | 16.80             | 426.7 | 1.68     | 42.7 | 0.08             | 2.1 | –                      | –  |

Conductor Color Coding: ICEA Method 4: Black and Numbered, 3 Symmetrical Bare Copper Grounds.



## MarineTuff® Foundation Fieldbus Cables



FOUNDATION Fieldbus is the dominant industrial network in offshore environments. Belden Fieldbus cables are designed to withstand the destructive effects of temperature extremes, humidity/moisture, dust and oil. In harsh environments such as oil and gas extraction ultraviolet radiation from extensive exposure to the sun can shorten cable life. With the high cost of downtime in such remote locations, investing in cable with proven performance and reliability can significantly reduce the likelihood of system failure.

### Key Attributes

- Type P ratings on all 600V insulations and options
- LSZH jackets on all cables and options
- Bronze braid option on all cables
- ABS and DNV certified
- 10 year warranty
- Compliant with Fieldbus Spec IEC 61158-2 (ISA/SP-50)
- Excellent electrical characteristics
- Versions in 18 and 16 AWG stranded tinned copper conductors
- Standard multi-pair cables available in 2 to 12 pairs. Higher pair counts available upon request
- PLTC/ITC-ER, PLTC, and TC-ER versions
- C(UL) CIC Type TC on 600V XLP insulated products
- Suitable for use in Class 1, Div. 2 applications
- RoHS compliant and CE approved



# MarineTuff® FOUNDATION

## Fieldbus Cable

300V and 600V, 18 AWG Paired Cable, Type A,  
Thermoset/Thermoplastic with or without Bronze Armoring

### Featured Options:

- Low Smoke Zero Halogen  
- Both Thermoplastic and Thermoset Options
- Bronze braid armoring
- Additional AWG sizes and pair counts available upon request
- Sun Res
- Oil Res II (Thermoset)

### Certifications/Compliance

- ABS (American Bureau of Shipping)
- DNV (Det Norske Veritas)\*
- IEEE 1580 Type P Insulations - 600V Constructions
- UL 1277 Type TC-ER - 600V Constructions
- PLTC/ITC-ER - 300V Constructions
- NEC: CMG - 300V Constructions
- CEC: CMG FT4 - 300V Constructions
- IEC 60332-3-24 (Cat C)
- FT4/IEEE 1202
- IEC 60332-3-22
- IEC 60754-1 (Jacket)
- IEC 60754-2 (Jacket)



### Construction:

1. 18 or 16 AWG Stranded Tinned Copper Conductors
2. XLP Insulation - 600V  
Polyolefin Insulation - 300V
3. 100% Overall Foil Shield Coverage  
Plus Individually Shielded Pairs on Multi-Pair Constructions
4. LSZH Thermoset or Thermoplastic Jacket

NOTE: Also available on all options, bronze braid armor with LSZH second jacket not pictured





## MarineTuff® FOUNDATION Fieldbus Cable

300V and 600V, 18 AWG Paired Cable, Type A,  
Thermoset/Thermoplastic with or without Bronze Armoring



| Part No.   | AWG | Pairs | OD (Nom) |      | Additional Features/Ratings            |  |
|--|-----|-------|----------|------|--|--|
|  |     |       | Inch     | mm   |  |  |
| <b>300V, 18 AWG Foundation Fieldbus</b>  |     |       |          |      |  |  |
| <b>Stranded (7 x 26) TC Conductors • Polyolefin Insulation • LSZH Jacket • TC Drain Wire • Beldfoil® Shielding</b>   |     |       |          |      |  |  |
| <b>Thermoset Jacket</b>  |     |       |          |      |  |  |
| <b>3076Z</b>   | 18  | 1     | 0.38     | 9.7  | CMG, PLTC-ER, ITC-ER,<br>Direct Burial |  |
| <b>Thermoplastic Jacket</b>  |     |       |          |      |  |  |
| <b>3076T</b>   | 18  | 1     | 0.38     | 9.7  |  |  |
| <b>300V, 18 AWG Foundation Fieldbus, Bronze Armored</b>  |     |       |          |      |  |  |
| <b>Stranded (7 x 26) TC Conductors • Polyolefin Insulation • Double LSZH Jackets • TC Drain Wire • Beldfoil® Shielding</b>                                 |     |       |          |      |  |  |
| <b>Thermoset Jacket</b>  |     |       |          |      |  |  |
| <b>973076Z</b>   | 18  | 1     | 0.52     | 13.3 | CMG, PLTC-ER, ITC-ER,<br>Direct Burial |  |
| <b>Thermoplastic Jacket</b>  |     |       |          |      |  |  |
| <b>773076T</b>   | 18  | 1     | 0.52     | 13.3 |  |  |
| <b>600 V, 18 AWG Foundation Fieldbus</b>   |     |       |          |      |  |  |
| <b>Stranded (7 x 26) TC Conductors • XLP Insulation • LSZH Jacket • TC Drain Wire • Beldfoil® Shielding Note: Cables in this section are not DNV Rated</b> |     |       |          |      |  |  |
| <b>Thermoset Jacket</b>  |     |       |          |      |  |  |
| <b>2118Z</b>   | 18  | 1     | 0.35     | 8.8  | TC-ER, ITC-ER,<br>Direct Burial        |  |
| <b>2119Z</b>   | 18  | 2     | 0.60     | 15.2 |  |  |
| <b>2120Z</b>   | 18  | 5     | 0.75     | 19.0 |  |  |
| <b>2121Z</b>   | 18  | 8     | 0.93     | 23.6 |  |  |
| <b>2122Z</b>   | 18  | 12    | 1.12     | 28.5 |  |  |
| <b>Thermoplastic Jacket</b>  |     |       |          |      |  |  |
| <b>2118T</b>   | 18  | 1     | 0.35     | 8.8  |  |  |
| <b>2119T</b>   | 18  | 2     | 0.60     | 15.2 |  |  |
| <b>2120T</b>   | 18  | 5     | 0.75     | 19.0 |  |  |
| <b>2121T</b>   | 18  | 8     | 0.93     | 23.6 |  |  |
| <b>2122T</b>   | 18  | 12    | 1.12     | 28.5 |  |  |



# MarineTuff® FOUNDATION Fieldbus Cable

600V, 18 AWG Paired Cable, Type A



| Part No. | AWG | Pairs | OD (Nom) |    | Additional Features/Ratings |
|----------|-----|-------|----------|----|-----------------------------|
|          |     |       | Inch     | mm |                             |

## 600V, 18 AWG Foundation Fieldbus - Bronze Armored

Stranded (7x26) TC Conductors • XLP Insulation • Double LSZH Jackets • TC Drain Wire • Individually shielded pairs and overall Beldfoil Shielding

| Thermoset Jacket     |    |   |      |      | TC-ER, ITC-ER, Direct Burial |
|----------------------|----|---|------|------|------------------------------|
| 972118Z              | 18 | 1 | 0.48 | 12.5 |                              |
| 972119Z              | 18 | 2 | 0.75 | 19.3 |                              |
| 972120Z              | 18 | 5 | 0.90 | 23.1 |                              |
| 972121Z              | 18 | 8 | 1.09 | 27.7 |                              |
| Thermoplastic Jacket |    |   |      |      |                              |
| 772118T              | 18 | 1 | 0.49 | 12.5 |                              |
| 772119T              | 18 | 2 | 0.76 | 19.3 |                              |
| 772120T              | 18 | 5 | 0.91 | 23.1 |                              |
| 772121T              | 18 | 8 | 1.09 | 27.7 |                              |



## MarineTuff® FOUNDATION Fieldbus Cable

600V, 16 AWG Paired Cable, Type A



| Part No. | AWG | Pairs | OD (Nom) |    | Additional Features/Ratings |
|----------|-----|-------|----------|----|-----------------------------|
|          |     |       | Inch     | mm |                             |

### 600V, 16 AWG Foundation Fieldbus

Stranded (7x24) TC Conductors • XLP Insulation • LSZH Jacket • TC Drain Wire • Individually shielded pairs and overall Beldfoil Shielding

| Thermoset Jacket     |    |    |      |      | TC-ER, ITC-ER, Direct Burial |
|----------------------|----|----|------|------|------------------------------|
| 2127Z                | 16 | 1  | 0.37 | 9.5  |                              |
| 2128Z                | 16 | 2  | 0.65 | 16.4 |                              |
| 2129Z                | 16 | 5  | 0.81 | 20.6 |                              |
| 2130Z                | 16 | 8  | 1.01 | 25.6 |                              |
| 2131Z                | 16 | 12 | 1.22 | 31.0 |                              |
| Thermoplastic Jacket |    |    |      |      |                              |
| 2127T                | 16 | 1  | 0.37 | 9.5  |                              |
| 2128T                | 16 | 2  | 0.65 | 16.4 |                              |
| 2129T                | 16 | 5  | 0.81 | 20.6 |                              |
| 2130T                | 16 | 8  | 1.01 | 25.6 |                              |
| 2131T                | 16 | 12 | 1.22 | 31.0 |                              |

### 600V, 16 AWG Foundation Fieldbus - Bronze Armored

Stranded (7x24) TC Conductors - XLP Insulation - Double LSZH Jackets - TC Drain Wire - Individually shielded pairs and overall Beldfoil Shielding

| Thermoset Jacket     |    |   |      |      | TC-ER, ITC-ER, Direct Burial |
|----------------------|----|---|------|------|------------------------------|
| 972127Z              | 16 | 1 | 0.52 | 13.2 |                              |
| 972128Z              | 16 | 2 | 0.81 | 20.5 |                              |
| 972129Z              | 16 | 5 | 0.97 | 24.7 |                              |
| 972130Z              | 16 | 8 | 1.17 | 29.7 |                              |
| Thermoplastic Jacket |    |   |      |      |                              |
| 772127T              | 16 | 1 | 0.51 | 13.2 |                              |
| 772128T              | 16 | 2 | 0.80 | 20.5 |                              |
| 772129T              | 16 | 5 | 0.97 | 24.7 |                              |
| 772130T              | 16 | 8 | 1.16 | 29.7 |                              |



## MarineTuff® PROFIBUS-DP Cables



PROFIBUS is one of the largest open industrial fieldbuses in the world. As with most fieldbus systems, PROFIBUS can reduce operating costs, increase productivity, decrease time to market for new products, and improve product quality. And unlike standard 4-20mA controls, PROFIBUS can support up to 32 devices per segment – up to a total of 126 devices, depending on total system current.

The MarineTuff Profibus offering includes a 150-ohm twinax (twisted pair) cable that matches the impedance of your offshore system, allowing for maximum signal transmission. The cable incorporates an overall Beldfoil® shield plus a 65% tinned copper braid for maximum shielding effectiveness. It also carries a UL NEC Type PLTC listing to achieve maximum installation versatility. The stranded option provides additional flexibility during installation and in use. With the additional ABS rating and armoring options, the MarineTuff Profibus line will meet all the demands of your Marine applications.

### Key Attributes

- LSZH jackets on all cable options
- UL NEC Type PLTC
- ABS and DNV certified
- Overall Beldfoil shield plus 65% tinned copper braid
- Optimized for maximum signal transmission
- 10 year warranty



## MarineTuff® PROFIBUS-DP Cable

22 AWG, PLTC, Thermoset/Thermoplastic with or without Bronze Armoring



### Featured Options:

- Low Smoke Zero Halogen jacket – Both Thermoplastic and Thermoset Options
- Multiple armoring options
- Sun Res
- Oil Res II (Thermoset)


### Certifications/Compliance

- ABS (American Bureau of Shipping)
- DNV (Det Norske Veritas)\*
- NEC: PLTC CMG
- CEC: CMG FT4
- FT4/IEEE 1202
- IEC 60332-3-22
- IEC 60754-1 (Jacket)
- IEC 60754-2 (Jacket)

### Construction:

1. 22 AWG Bare Copper Conductors
2. Flame Retardant Foam Polyethylene Insulation
3. Overall Beldfoil® Shield (100% coverage)
4. Tinned Copper Braid Shield (65% coverage)
5. LSZH Thermoset or Thermoplastic Jacket

NOTE: Also available on all options, bronze braid armor with LSZH second jacket not pictured





# MarineTuff® PROFIBUS-DP Cable

22 AWG, PLTC, Thermoset/Thermoplastic with or without Bronze Armoring



| Part No.   | OD (Nom) |      | Additional Features/Ratings |
|--|----------|------|-----------------------------|
|  | Inch     | mm   |                             |
| <b>22 AWG, 300V Single Pair Databus ISA/SP-50 Profibus Cable</b>   |          |      |                             |
| <b>Solid BC Conductors • FRFPE Insulation • Overall Beldfoil® Shielding, plus Overall Tinned Copper Braid (65% coverage) • LSZH Outer Jacket</b>         |          |      |                             |
| <b>Thermoset Jacket</b>  |          |      | PLTC-LS, CMG-LS             |
| <b>3079Z</b>   | 0.43     | 10.9 |                             |
| <b>Thermoplastic Jacket</b>  |          |      |                             |
| <b>3079T</b>   | 0.43     | 10.9 |                             |
| <b>22 AWG, 300V Single Pair DataBus ISA/SP-50 Profibus Cable - with Bronze Armoring</b>  |          |      |                             |
| <b>Solid BC Conductors • FRFPE Insulation • Overall Beldfoil® Shielding, plus Overall Tinned Copper Braid (65% coverage) • Double LSZH Outer Jackets</b> |          |      |                             |
| <b>Thermoset Jacket</b>  |          |      | PLTC-LS, CMG-LS             |
| <b>973079Z</b>   | 0.59     | 15.0 |                             |
| <b>Thermoplastic Jacket</b>  |          |      |                             |
| <b>773079T</b>   | 0.59     | 15.0 |                             |



## MarineTuff®

### RS-485 Cables



As a part of Belden's comprehensive portfolio of Industrial Ethernet cables, the MarineTuff RS-485 provides reliable connections as a standard from the control room to metering and pumping/compressor stations. RS-485 cables provide serial data transmission in offshore industrial environments and are PLTC and CMG rated allowing for installation in 300V power limited cable trays. For plenum installations, MarineTuff RS-485 should be routed through conduit.

With manufacturing in ISO certified manufacturing facilities, Belden's state-of-the-art processes ensure quality in each product. Product consistency is a mainstay of our products.

#### Key Attributes

- LSZH jackets on all cable options
- UL NEC Type PLTC/CMG
- ABS and DNV certified
- High foam density polyethylene insulation (FHDPE)
- Overall Beldfoil shield plus 65% tinned copper braid
- 10 year warranty



# MarineTuff® RS-485 Cable

PLTC/CM, Thermoset/Thermoplastic with or without  
Bronze Armoring



## Featured Options:

- Low Smoke Zero Halogen jacket – both Thermoplastic and Thermoset Options
- Sun Res
- Oil Res II (Thermoset)


## Certifications/Compliance

- ABS (American Bureau of Shipping)
- DNV (Det Norske Veritas)\*
- NEC: CMG, PLTC
- CEC/C(UL): CMG FT4
- FT4/IEEE 1202
- IEC 60332-3-22
- IEC 60754-1 (Jacket)
- IEC 60754-2 (Jacket)

## Construction:

1. 22 AWG Stranded Tinned Copper (TC) Conductors
2. Datalene® Insulation
3. Overall Beldfoil® Shield (100% coverage)
4. Tinned Copper Braid Shield (65% coverage)
5. Stranded Tinned Copper Drain Wire
6. LSZH Thermoset or Thermoplastic Jacket

NOTE: Also available on all options, bronze braid armor with LSZH second jacket not pictured





## MarineTuff® RS-485 Cable

PLTC/CM, Thermoset/Thermoplastic with or without  
Bronze Armoring



| Part No.  | Pairs | OD (Nom) |      | Additional Features/Ratings |  |
|---|-------|----------|------|-----------------------------|--|
|   |       | Inch     | mm   |                             |  |
| <b>RS-485</b>   |       |          |      |                             |  |
| <b>22 AWG (7x30) Stranded TC Conductors • Datalene Insulation • TC Drain Wire Overall Beldfoil Shielding plus an overall tinned copper braid (65% coverage) • LSZH Outer Jacket</b>         |       |          |      |                             |  |
| <b>Thermoset Jacket</b>   |       |          |      |                             |  |
| <b>3105Z</b>  | 1     | 0.40     | 10.2 | <b>CMG-LS, PLTC-LS</b>      |  |
| <b>3107Z</b>  | 2     | 0.44     | 11.2 |                             |  |
| <b>3108Z</b>  | 3     | 0.47     | 11.9 |                             |  |
| <b>3109Z</b>  | 4     | 0.49     | 12.4 |                             |  |
| <b>Thermoplastic Jacket</b>   |       |          |      |                             |  |
| <b>3105T</b>  | 1     | 0.45     | 11.4 |                             |  |
| <b>3107T</b>  | 2     | 0.49     | 12.4 |                             |  |
| <b>3108T</b>  | 3     | 0.52     | 13.2 |                             |  |
| <b>3109T</b>  | 4     | 0.49     | 12.4 |                             |  |
| <b>RS-485 - Bronze Armored</b>  |       |          |      |                             |  |
| <b>22 AWG (7x30) Stranded TC Conductors • Datalene Insulation • TC Drain Wire Overall Beldfoil Shielding plus an overall tinned copper braid (65% coverage) • Double LSZH Outer Jackets</b> |       |          |      |                             |  |
| <b>Thermoset Jacket</b>   |       |          |      |                             |  |
| <b>973105Z</b>  | 1     | 0.56     | 14.3 | <b>CMG-LS, PLTC-LS</b>      |  |
| <b>973107Z</b>  | 2     | 0.60     | 15.3 |                             |  |
| <b>973108Z</b>  | 3     | 0.63     | 16.0 |                             |  |
| <b>973109Z</b>  | 4     | 0.65     | 16.6 |                             |  |
| <b>Thermoplastic Jacket</b>   |       |          |      |                             |  |
| <b>773105T</b>  | 1     | 0.61     | 15.5 |                             |  |
| <b>773107T</b>  | 2     | 0.65     | 16.6 |                             |  |
| <b>773108T</b>  | 3     | 0.68     | 17.3 |                             |  |
| <b>773109T</b>  | 4     | 0.70     | 17.8 |                             |  |



## MarineTuff® ControlNet™



To ensure that Belden's ControlBus™ cables meet the high-speed, time-critical requirements for the operation of ControlNet offshore systems, these low-loss RG-6/U Type coaxial cables incorporate a Duobond Quad Shield for maximum signal integrity and run length. All products are sweep tested across a wide frequency range, ensuring that return loss, impedance and other critical performance features, meet the requirements of the ControlNet physical layer specification. ControlBus cables can be supplied with a bronze braid, aluminum or steel interlocked armor. Belden manufactures variations of the cable for different applications, identification needs, and environments.

### Key Attributes

- Excellent electrical characteristics
- RoHS compliant and CE approved
- ABS and DNV certified
- Low Smoke Zero Halogen (LSZH) jackets on all cables
- Bronze Braid Optional
- 10-Year Warranty



## MarineTuff® ControlNet™ Cable

18 AWG, Duobond®-Quad Shielded Coaxial, Type RG6/U,  
Thermoset/Thermoplastic with or without Bronze Armoring



### Featured Options:

- Low Smoke Zero Halogen Jacket - Both Thermoplastic and Thermoset Options
- Multiple armoring options
- Sun Res
- Oil Res II (Thermoset)


### Certifications/Compliance

- ABS (American Bureau of Shipping)
- DNV (Det Norske Veritas)\*
- NEC: CMG CL2
- CEC: CMG FT4
- FT4/IEEE 1202
- IEC 60332-3-22
- IEC 60754-1 (Jacket)
- IEC 60754-2 (Jacket)

### Construction:

1. Type RG6/U 18 AWG Solid Copper Covered Steel Conductors or 20 AWG Finely Stranded BC Conductor (High Flex)
2. Polyolefin Insulation
3. Quad-Shield Coverage (Foil Braid/Foil Braid)
4. LSZH Thermoset or Thermoplastic Jacket

NOTE: Also available on all options, bronze braid armor with LSZH second jacket not pictured





# MarineTuff® ControlNet™ Cable

18 AWG, Duobond®-Quad Shielded Coaxial, Type RG6/U,  
Thermoset/Thermoplastic with or without Bronze Armoring

| Part No.   | AWG | OD (Nom) |      | Additional Features/Ratings |
|--|-----|----------|------|-----------------------------|
|  |     | Inch     | mm   |                             |
| <b>Solid - Quad Shielded Coaxial, Type RG6/U</b>   |     |          |      |                             |
| <b>18 AWG Solid BC-Covered Steel Conductor • Polyolefin Insulation • Duobond QuadShield • LSZH Jacket</b>  |     |          |      |                             |
| <b>Thermoset Jacket</b>  |     |          |      |                             |
| 3092Z  | 18  | 0.30     | 7.6  | <b>CMG-LS, CL2</b>          |
| <b>Thermoplastic Jacket</b>  |     |          |      |                             |
| 3092T  | 18  | 0.30     | 7.6  |                             |
| <b>Solid - Quad Shielded Coaxial, Type RG6/U - Bronze Armored</b>  |     |          |      |                             |
| <b>18 AWG Solid BC-Covered Steel Conductor • Polyolefin Insulation • Duobond QuadShield • Double LSZH Jackets</b>  |     |          |      |                             |
| <b>Thermoset Jacket</b>  |     |          |      |                             |
| 973092Z  | 18  | 0.44     | 11.3 | <b>CMG-LS, CL2</b>          |
| <b>Thermoplastic Jacket</b>  |     |          |      |                             |
| 773092T  | 18  | 0.44     | 11.3 |                             |
| <b>Stranded - Quad Shielded Coaxial, Type RG6/U</b>  |     |          |      |                             |
| <b>20 AWG Stranded (105x40) BC Conductor • Polyolefin Insulation • Duobond QuadShield • LSZH Jacket Note: Cables in this section are not DNV Rated</b>         |     |          |      |                             |
| <b>Thermoset Jacket</b>  |     |          |      |                             |
| 3092FZ   | 20  | 0.31     | 7.7  | <b>CMG-LS, CL2</b>          |
| <b>Thermoplastic Jacket</b>  |     |          |      |                             |
| 3092FT   | 20  | 0.31     | 7.7  |                             |
| <b>Stranded - Quad Shielded Coaxial, Type RG6/U - Bronze Armored</b>   |     |          |      |                             |
| <b>20 AWG Stranded (105x40) BC Conductor • Polyolefin Insulation • Duobond QuadShield • Double LSZH Jackets Note: Cables in this section are not DNV Rated</b> |     |          |      |                             |
| <b>Thermoset Jacket</b>  |     |          |      |                             |
| 973092F  | 20  | 0.45     | 11.4 | <b>CMG-LS, CL2</b>          |
| <b>Thermoplastic Jacket</b>  |     |          |      |                             |
| 773092F  | 20  | 0.45     | 11.4 |                             |

\*Duobond IV is a four-layer shield: (1) Duobond II Foil, (2) TC Braid (94%), (3) Duofoil® Foil, (4) TC Braid (90%).

BC = Bare Copper • PVC = Polyvinyl Chloride



## MarineTuff® Blue Hose Cables



The needs of real-time, high-throughput applications can be routinely met by the control network and the use of Belden Blue Hose cable. These cables are a robust physical media for the transmission of PLC/DCS signals. Backed by years of research and development, each Belden Blue Hose cable is manufactured to exacting quality standards. Belden Blue Hose cables are designed to give you unprecedented installation flexibility for Data Highway, SY/Net and many other PLC-I/O networks.

### Key Attributes

- LSZH jackets on all cables and options
- Bronze braid options on all cables and options
- ABS and DNV certified
- 10 year warranty



# MarineTuff® Blue Hose Cable

18 AWG, 600V Twinaxial Cable Thermoset/Thermoplastic  
Jackets with or without Bronze Braid Armoring



## Featured Options:

- Low Smoke Zero Halogen jacket – standard on all products
- Sunlight and Oil resistance
- Direct Burial
- Bronze braid armoring
- Sun Res
- Oil Res II (Thermoset)


## Certifications/Compliance

- ABS (American Bureau of Shipping)
- DNV (Det Norske Veritas)\*
- NEC/UL: CMG, TC
- C(UL): CMG
- FT4/IEEE 1202
- IEC 60332-3-22
- IEC 60754-1 (Jacket)
- IEC 60754-2 (Jacket)

## Construction:

1. LSZH Thermoset Jacket
2. 100% Foil Shield Coverage
3. 55% tinned copper braid
4. Drain wire

NOTE: Also available on all options, bronze braid armor with LSZH second jacket not pictured





## MarineTuff® Blue Hose Cable

18 AWG, 600V Twinaxial Cable Thermoset/Thermoplastic Jackets with or without Bronze Braid Armoring



| Part No.  | OD (Nom) |      | Additional Features/Ratings  |
|---|----------|------|------------------------------|
|   | Inch     | mm   |                              |
| <b>18 AWG, 600V Twinaxial Cable</b>   |          |      |                              |
| <b>Stranded TC Conductors (7x26) • Polyolefin Insulation • Overall Beldfoil Shielding • LSZH Outer Jacket</b>         |          |      |                              |
| <b>Thermoset Jacket</b>   |          |      | <b>TC-LS, CMG-LS, ITC-LS</b> |
| <b>3072Z</b>  | 0.42     | 10.6 |                              |
| <b>Thermoplastic Jacket</b>   |          |      |                              |
| <b>3072T</b>  | 0.42     | 10.6 |                              |
| <b>18 AWG, 600V Twinaxial Cable - with Bronze Braid Armor</b>   |          |      |                              |
| <b>Stranded TC Conductors (7x26) • Polyolefin Insulation • Overall Beldfoil Shielding • Double LSZH Outer Jackets</b> |          |      |                              |
| <b>Thermoset Jacket</b>   |          |      | <b>TC-LS, CMG-LS, ITC-LS</b> |
| <b>973072Z</b>  | 0.57     | 14.7 |                              |
| <b>Thermoplastic Jacket</b>   |          |      |                              |
| <b>773072T</b>  | 0.57     | 14.7 |                              |



# MarineTuff®

## DeviceNet™



Widely used for maritime electronics, the MarineTuff DeviceNet cables' rugged design will support your offshore DeviceNet ODVA requirements. These cables provide device designers with the ability to implement desired network behavior of several communication objects into a device while the durable design allows these networks to run in the harshest environments. Whether connecting sensors or switching devices, the MarineTuff DeviceNet cables will offer the reliability you demand.

### Key Attributes

- 600V Class 1 ODVA
- LSZH jackets on all cable options
- ABS and DNV certified
- UL NEC TC-ER
- Overall Beldfoil shield plus 65% tinned copper braid
- XLPE insulation on the power pairs and F-R Polypropylene on the data pairs
- Able to occupy the same tray/conduit as 600V cables
- 10 year warranty

## MarineTuff® DeviceNet™ Cable

16 AWG, 600V Thermoset/Thermoplastic Jackets with or without Bronze Braid Armoring



### Featured Options:

- Low Smoke Zero Halogen jacket – standard on all products
- Multiple armoring options
- Sun Res
- Oil Res II (Thermoset)


### Certifications/Compliance

- ABS (American Bureau of Shipping)
- DNV (Det Norske Veritas)\*
- C(UL) AWM I/II A/B (Thermoset Only)
- NEC: TC-ER
- CEC: FT4
- FT4/IEEE 1202
- IEC 60332-3-22
- IEC 60754-1 (Jacket)
- IEC 60754-2 (Jacket)

### Construction:

1. LSZH Thermoset Jacket
2. 100% Foil Shield Coverage
3. TC Braid Shield (65% coverage)
4. 18 AWG Data
5. 16 AWG Power

NOTE: Also available on all options, bronze braid armor with LSZH second jacket not pictured





# MarineTuff® DeviceNet™ Cable

16 AWG, 600V Thermoset/Thermoplastic Jackets with or without Bronze Braid Armoring



| Part No.  | Pairs | OD (Nom) |      | Additional Features/Ratings       |
|---|-------|----------|------|-----------------------------------|
|   |       | Inch     | mm   |                                   |
| <b>16 AWG, 600V DeviceBus for ODVA DeviceNet</b>  |       |          |      |                                   |
| <b>Stranded (19x) TC Conductors • XLPE Insulation (16 AWG) • PE Insulation (18 AWG) • Overall Beldfoil Shielding plus Overall Tinned Copper Braid (65% coverage) • LSZH Outer Jacket</b>            |       |          |      |                                   |
| <b>Thermoset Jacket</b>   |       |          |      | <b>TC-LS, TC-ER, AWM I/II A/B</b> |
| <b>7896Z</b>  | 2     | 0.64     | 16.2 |                                   |
| <b>Thermoplastic Jacket</b>   |       |          |      | <b>TC-LS, TC-ER</b>               |
| <b>7896T</b>  | 2     | 0.64     | 16.2 |                                   |
| <b>16 AWG, 600V DeviceBus for ODVA DeviceNet</b>  |       |          |      |                                   |
| <b>Stranded (19x) TC Conductors • XLPE Insulation (16 AWG) • PE Insulation (18 AWG) • Overall Beldfoil Shielding plus an overall tinned copper braid (65% coverage) • Double LSZH Outer Jackets</b> |       |          |      |                                   |
| <b>Thermoset Jacket</b>   |       |          |      | <b>TC-LS, TC-ER, AWM I/II A/B</b> |
| <b>977896Z</b>  | 2     | 0.80     | 19.8 |                                   |
| <b>Thermoplastic Jacket</b>   |       |          |      | <b>TC-LS, TC-ER</b>               |
| <b>777896T</b>  | 2     | 0.80     | 19.8 |                                   |

Conductor Color Coding: Data: Blue, White  
Power: Red, Black



## MarineTuff® A/V and Electronic Cable



Delivering high-end audio and video quality in shipboard environments is critical to enhancing shipboard safety and communications as well as crew and consumer experience. Belden's ABS-rated audiovisual and electronic cables enable connectivity for the same wide range of application options available on dry land including audio, video, security, networking and control. Marine A/V cables use standard connectors, with no special installation techniques allowing for a fast and easy installation.

### Products Include

- Electronic Audio, Control, and Instrumentation
- Audio and Speaker Cable
- Coaxial Broadcast AV
- DataTwist Nonbonded-Pair
- Security Composite

### Key Attributes

- ABS certified
- LSZH jackets on all cables and options
- 10 year warranty



# MarineTuff® Electronic Audio, Control and Instrumentation Cable

## Featured Options:


- Low Smoke Zero Halogen jacket – standard on all products
- RS-232 Cable (9451SB)
- Audio/Control Cables
- Multimedia control cable for AMX® and Crestron systems with both RS-485® and power in one cable (1502SB)

## Certifications/Compliance

- ABS Certified
- Compliant with IEEE 45 and applicable sections of IEC 60092-376
- NEC/CEC CMG-LS
- FT4
- RoHS compliant

## Construction:

1. LSZH Thermoplastic Jacket
2. 100% Foil Shield Coverage
3. Drain Wires





## MarineTuff® Electronic Audio, Control and Instrumentation Cable



| Part No.  | AWG | Pairs  | Insulation                    | Shield                                    | OD (Nom) |     | Additional Features/Ratings            |
|---|-----|--------|-------------------------------|---|----------|-----|--|
|   |     |        |                               |   | Inch     | mm  |  |
| <b>Electronic Audio, Control, and Instrumentation Single- and Multi-pair Cables</b> |     |        |                               |   |          |     |  |
| <b>Standard (7x) TC Conductors • Thermoplastic LSZH Jacket</b>                      |     |        |                               |   |          |     |  |
| <b>9451SB*</b>  | 22  | 1      | PP                            | Beldfoil                                  | 0.16     | 4.1 | 300V RMS, NEC/CEC CMG-LS, FT4          |
| <b>8723SB*</b>  | 22  | 2      | PP                            | Individual Beldfoil                       | 0.20     | 5.0 |  |
| <b>8777SB</b>   | 22  | 3      | PP                            | Individual Beldfoil                       | 0.27     | 6.9 | UL AWM Style 2919, NEC/CEC CMG-LS, FT4 |
| <b>Electronic Audio, Control, and Instrumentation Multimedia Control Cable</b>      |     |        |                               |   |          |     |  |
| <b>Standard (7x) TC Conductors • Thermoplastic LSZH Jacket</b>                      |     |        |                               |   |          |     |  |
| <b>1502SB</b>   | 22  | 1 + 2C | FPR (data)<br>F-R PVC (Power) | Beldfoil (data),<br>Unshielded<br>(power) | 0.26     | 6.5 | NEC/CEC CMG-LS, FT4                    |

\* Indicates common part numbers, LSZH, Thermoplastic



# MarineTuff® Audio and Speaker Cable



## Featured Options:


- Low Smoke Zero Halogen thermoplastic jacket – standard on all products
- AES/EBU Audio Cable
- High-strand Speaker Cable

## Certifications/Compliance

- ABS Certified
- Compliant with IEEE 45 and applicable sections of IEC 60092-376
- NEC/CEC CMG-LS
- FT4
- RoHS compliant
- High Flex/High Purity (Fine Stranding) on 1314SB-1317SB

## Construction:

1. LSZH Thermoplastic Jacket
2. Datalene or Polypropylene Insulation
3. 100% Foil Shield Coverage (where applicable)
4. Drain Wires





## MarineTuff® Audio and Speaker Cable



| Part No.   | AWG | Conductors | Insulation | Shield     | OD (Nom) |     | Additional Features/Ratings |
|--|-----|------------|------------|------------|----------|-----|-----------------------------|
|  |     |            |            |            | in/Inch  | mm  |                             |
| <b>AES/EBU Digital Audio Cable</b>   |     |            |            |            |          |     |                             |
| <b>Standard TC Conductors • Thermoplastic LSZH Jacket</b>                                    |     |            |            |            |          |     |                             |
| <b>1350SB*</b>   | 24  | 1 PR       | Datalene   | Beldfoil   | 0.18     | 4.6 | NEC/CEC CMG-LS, FT4         |
| <b>High Strand Speaker Cable for Unshielded Audio and Control; High-Flex and High-Purity</b> |     |            |            |            |          |     |                             |
| <b>Standard TC Conductors • Thermoplastic LSZH Jacket</b>                                    |     |            |            |            |          |     |                             |
| <b>1314SB*</b>   | 14  | 2          | PP         | Unshielded | 0.30     | 7.6 | NEC/CEC CMG-LS, FT4         |
| <b>1315SB</b>  | 14  | 4          | PP         | Unshielded | 0.34     | 8.6 |                             |
| <b>1316SB*</b>   | 12  | 2          | PP         | Unshielded | 0.34     | 8.6 |                             |
| <b>1317SB</b>  | 12  | 4          | PP         | Unshielded | 0.39     | 9.9 |                             |

\* Indicates common part numbers, LSZH, Thermoplastic



# MarineTuff® Coaxial Broadcast AV Cable



## Featured Options:


- Low Smoke Zero Halogen thermoplastic jacket – standard on all products
- CATV, Series
- RG-8 Type Low Loss 50 Ohm Wireless RF Transmission
- RG-6/U Type Digital Low Loss Serial
- RG-11/U Type Low Loss Serial
- Aluminum or Tinned Copper Braid Shielding

## Certifications/Compliance

- ABS Certified
- Compliant with IEEE 45 and applicable sections of IEC 60092-376
- NEC/CEC CMG-LS
- FT4
- RoHS compliant

## Construction:

1. LSZH Thermoplastic Jacket
2. Foam Polyethylene or Foam High-Density Polyethylene Insulation
3. 100% Duobond II® or Duofoil® Shield Coverage
4. 60% or 95% Braid Shield Coverage





## MarineTuff® Coaxial Broadcast AV Cable



| Part No.  | AWG | Pairs | Insulation | Shield                             | OD (Nom) |      | Additional Features/Ratings                 |
|---|-----|-------|------------|------------------------------------|----------|------|---|
|   |     |       |            |                                    | Inch     | mm   |   |
| <b>Broadband Coaxial; CATV Series 6</b>   |     |       |            |                                    |          |      |   |
| <b>Thermoplastic LSZH Jacket</b>  |     |       |            |                                    |          |      |   |
| <b>9116SB*</b>  | 18  | Coax  | Foam PE    | Duobond®II + Aluminum Braid Shield | 0.27     | 7.0  | NEC/CEC CMG-LS, FT4                         |
| <b>Low Loss 50 Ohm Wireless RF Transmission Cable; RG-8 Type</b>                                |     |       |            |                                    |          |      |   |
| <b>Thermoplastic LSZH Jacket</b>  |     |       |            |                                    |          |      |   |
| <b>7810SB</b>   | 10  | Coax  | Foam HDPE  | Duobond®II + TC Braid              | 0.41     | 10.3 | RF400, NEC/CEC CMG-LS, FT4                  |
| <b>Precision Video Cable for Analog and Digital; Low Loss Serial Digital Coax; RG-6/U Type</b>  |     |       |            |                                    |          |      |   |
| <b>Thermoplastic LSZH Jacket</b>  |     |       |            |                                    |          |      |   |
| <b>1694SB*</b>  | 18  | Coax  | Foam HDPE  | Duofoil® + TC Braid                | 0.27     | 7.0  | SDI/HDTV Digital Video, NEC/CEC CMG-LS, FT4 |
| <b>Precision Video Cable for Analog and Digital; Low Loss Serial Digital Coax; RG-11/U Type</b> |     |       |            |                                    |          |      |   |
| <b>Thermoplastic LSZH Jacket</b>  |     |       |            |                                    |          |      |   |
| <b>7731SB</b>   | 14  | Coax  | Foam HDPE  | Duofoil® + TC Braid                | 0.40     | 10.2 | SDI/HDTV Digital Video, NEC/CEC CMG-LS, FT4 |

\* Indicates common part numbers, LSZH, Thermoplastic



# MarineTuff® DataTwist® Nonbonded Pair



## Featured Options:


- Low Smoke Zero Halogen thermoplastic jacket – standard on all products
- Category 5e or Category 6
- Multimedia control cable for AMX® and Crestron systems with both RS-485® and power in one cable (1502SB)
- Shielded or Unshielded (depending on construction)
- RJ-45 Compatible

## Certifications/Compliance

- ABS Certified
- TIA/EIA-568-B.2 or B.2.1
- Compliant with IEEE 45 and applicable sections of IEC 60092-376
- NEC/CEC CMG-LS
- FT4
- RoHS compliant

## Construction:

1. LSZH Thermoplastic Jacket
2. 100% Foil Shield Coverage (for shielded)
3. Drain Wire (for shielded)
4. Rip Cord (for unshielded)





## MarineTuff® DataTwist Nonbonded Pair



| Part No.  | AWG | Pairs | Insulation | Shield              | OD (Nom) |     | Additional Features/Ratings |
|---|-----|-------|------------|---------------------|----------|-----|-----------------------------|
|   |     |       |            |                     | Inch     | mm  |                             |
| <b>Category 5e; TIA/EIA-568-B.2</b>                       |     |       |            |                     |          |     |                             |
| <b>Solid BC Conductors • Thermoplastic LSZH Jacket</b>    |     |       |            |                     |          |     |                             |
| <b>1300SB*</b>  | 24  | 4     | PO         | Beldfoil            | 0.26     | 6.6 | NEC/CEC CMG-LS, FT4         |
| <b>1633ESB*</b>   | 24  | 4     | PO         | Beldfoil + TC Braid | 0.25     | 6.3 |                             |
| <b>1318SB</b>   | 24  | 4     | PO         | Unshielded          | 0.29     | 7.4 |                             |
| <b>Category 6; TIA/EIA-568-B.2.1</b>                      |     |       |            |                     |          |     |                             |
| <b>Standard TC Conductors • Thermoplastic LSZH Jacket</b> |     |       |            |                     |          |     |                             |
| <b>1319SB*</b>  | 23  | 4     | PO         | Unshielded          | 0.29     | 7.4 | NEC/CEC CMG-LS, FT4         |

\* Indicates common part numbers, LSZH, Thermoplastic



# MarineTuff® Security Composite Cable



## Featured Options:

- Low Smoke Zero Halogen thermoplastic jacket – standard
- RG-6 Coax Plus Twisted Pair
- CCTV Plus Audio or Pan/Tilt/Zoom CCTV Control Applications

## Certifications/Compliance

- ABS Certified
- NEC/CEC CMG-LS
- FT4
- RoHS compliant

## Construction:

1. LSZH Thermoplastic Jacket





## MarineTuff® Security Composite Cable



| Part No.  | AWG                    | Conductors | Insulation               | Shield                               | OD (Nom)  |            | Additional Features/Ratings |
|---|------------------------|------------|--------------------------|--------------------------------------|-----------|------------|-----------------------------|
|   |                        |            |                          |                                      | Inch      | mm         |                             |
| <b>CCTV plus Audio or Pan/Tilt/Zoom CCTV Control Applications</b> |                        |            |                          |                                      |           |            |                             |
| <b>RG6 Coax plus Twisted Pair - Siamese Construction</b>          |                        |            |                          |                                      |           |            |                             |
| <b>1306SB*</b>  | 18 (Coax)<br>18 (Pair) | 1PR + Coax | FPE (Coax),<br>PO (Pair) | BC Braid (Coax)<br>Unshielded (Pair) | .28 x .51 | 7.0 x 13.1 | NEC/CEC CMG-LS, FT4         |

\* Indicates common part numbers, LSZH, Thermoplastic



# MarineTuff® Part Number Index

| Part Number | Page No            |
|-------------|--------------------|
| 1037Z       | <a href="#">38</a> |
| 1038Z       | <a href="#">36</a> |
| 1039Z       | <a href="#">38</a> |
| 1040Z       | <a href="#">38</a> |
| 1041Z       | <a href="#">38</a> |
| 1042Z       | <a href="#">38</a> |
| 1043Z       | <a href="#">38</a> |
| 1044Z       | <a href="#">38</a> |
| 1045Z       | <a href="#">38</a> |
| 1046Z       | <a href="#">38</a> |
| 1047Z       | <a href="#">38</a> |
| 1048Z       | <a href="#">36</a> |
| 1049Z       | <a href="#">36</a> |
| 1050Z       | <a href="#">36</a> |
| 1051Z       | <a href="#">36</a> |
| 1052Z       | <a href="#">36</a> |
| 1053Z       | <a href="#">36</a> |
| 1054Z       | <a href="#">36</a> |
| 1055Z       | <a href="#">38</a> |
| 1093Z       | <a href="#">37</a> |
| 1094Z       | <a href="#">37</a> |
| 1095Z       | <a href="#">37</a> |
| 1096Z       | <a href="#">37</a> |
| 1097Z       | <a href="#">39</a> |
| 1098Z       | <a href="#">39</a> |
| 1099Z       | <a href="#">39</a> |
| 1100Z       | <a href="#">39</a> |
| 1118Z       | <a href="#">38</a> |
| 1119Z       | <a href="#">39</a> |
| 1120Z       | <a href="#">36</a> |
| 1121Z       | <a href="#">37</a> |
| 1300SB      | <a href="#">76</a> |
| 1306SB      | <a href="#">78</a> |
| 1314SB      | <a href="#">72</a> |
| 1315SB      | <a href="#">72</a> |
| 1316SB      | <a href="#">72</a> |
| 1317SB      | <a href="#">72</a> |
| 1318SB      | <a href="#">76</a> |
| 1319SB      | <a href="#">76</a> |
| 1350SB      | <a href="#">72</a> |
| 1502SB      | <a href="#">70</a> |
| 1633ESB     | <a href="#">76</a> |
| 1694SB      | <a href="#">74</a> |
| 2118T       | <a href="#">50</a> |

| Part Number | Page No            |
|-------------|--------------------|
| 2118Z       | <a href="#">50</a> |
| 2119T       | <a href="#">50</a> |
| 2119Z       | <a href="#">50</a> |
| 2120T       | <a href="#">50</a> |
| 2120Z       | <a href="#">50</a> |
| 2121T       | <a href="#">50</a> |
| 2121Z       | <a href="#">50</a> |
| 2122T       | <a href="#">50</a> |
| 2122Z       | <a href="#">50</a> |
| 2127T       | <a href="#">52</a> |
| 2127Z       | <a href="#">52</a> |
| 2128T       | <a href="#">52</a> |
| 2128Z       | <a href="#">52</a> |
| 2129T       | <a href="#">52</a> |
| 2129Z       | <a href="#">52</a> |
| 2130T       | <a href="#">52</a> |
| 2130Z       | <a href="#">52</a> |
| 2131T       | <a href="#">52</a> |
| 2131Z       | <a href="#">52</a> |
| 3064Z       | <a href="#">37</a> |
| 3072T       | <a href="#">64</a> |
| 3072Z       | <a href="#">64</a> |
| 3076T       | <a href="#">50</a> |
| 3076Z       | <a href="#">50</a> |
| 3079T       | <a href="#">55</a> |
| 3079Z       | <a href="#">55</a> |
| 3080Z       | <a href="#">41</a> |
| 3081Z       | <a href="#">41</a> |
| 3088Z       | <a href="#">36</a> |
| 3089Z       | <a href="#">37</a> |
| 3090Z       | <a href="#">38</a> |
| 3091Z       | <a href="#">39</a> |
| 3092FT      | <a href="#">61</a> |
| 3092FZ      | <a href="#">61</a> |
| 3092T       | <a href="#">61</a> |
| 3092Z       | <a href="#">61</a> |
| 3103Z       | <a href="#">42</a> |
| 3105T       | <a href="#">58</a> |
| 3105Z       | <a href="#">58</a> |
| 3107T       | <a href="#">58</a> |
| 3107Z       | <a href="#">58</a> |
| 3108T       | <a href="#">58</a> |
| 3108Z       | <a href="#">58</a> |
| 3109T       | <a href="#">58</a> |

| Part Number | Page No            |
|-------------|--------------------|
| 3109Z       | <a href="#">58</a> |
| 3118Z       | <a href="#">39</a> |
| 3130Z       | <a href="#">39</a> |
| 7731SB      | <a href="#">74</a> |
| 7810SB      | <a href="#">74</a> |
| 7896T       | <a href="#">67</a> |
| 7896Z       | <a href="#">67</a> |
| 7940T       | <a href="#">12</a> |
| 7940Z       | <a href="#">12</a> |
| 7953T       | <a href="#">12</a> |
| 7953Z       | <a href="#">12</a> |
| 8723SB      | <a href="#">70</a> |
| 8777SB      | <a href="#">70</a> |
| 9116SB      | <a href="#">74</a> |
| 9451SB      | <a href="#">70</a> |
| 27080Z      | <a href="#">21</a> |
| 27109Z      | <a href="#">24</a> |
| 27138Z      | <a href="#">27</a> |
| 27325Z      | <a href="#">15</a> |
| 27325ZS     | <a href="#">17</a> |
| 27337Z      | <a href="#">18</a> |
| 27337ZS     | <a href="#">20</a> |
| 27636Z      | <a href="#">21</a> |
| 27641Z      | <a href="#">24</a> |
| 27643Z      | <a href="#">27</a> |
| 27916Z      | <a href="#">15</a> |
| 27917Z      | <a href="#">18</a> |
| 28081Z      | <a href="#">21</a> |
| 28081ZS     | <a href="#">23</a> |
| 28082Z      | <a href="#">21</a> |
| 28082ZS     | <a href="#">23</a> |
| 28083Z      | <a href="#">21</a> |
| 28084Z      | <a href="#">21</a> |
| 28085Z      | <a href="#">21</a> |
| 28086Z      | <a href="#">21</a> |
| 28087Z      | <a href="#">21</a> |
| 28088Z      | <a href="#">21</a> |
| 28089Z      | <a href="#">21</a> |
| 28090Z      | <a href="#">21</a> |
| 28091Z      | <a href="#">21</a> |
| 28092Z      | <a href="#">21</a> |
| 28093Z      | <a href="#">21</a> |
| 28094Z      | <a href="#">21</a> |
| 28095Z      | <a href="#">21</a> |

| Part Number | Page No            |
|-------------|--------------------|
| 28096Z      | <a href="#">21</a> |
| 28097Z      | <a href="#">21</a> |
| 28098Z      | <a href="#">21</a> |
| 28099Z      | <a href="#">21</a> |
| 28100Z      | <a href="#">21</a> |
| 28101Z      | <a href="#">21</a> |
| 28102Z      | <a href="#">21</a> |
| 28103Z      | <a href="#">21</a> |
| 28104Z      | <a href="#">21</a> |
| 28105Z      | <a href="#">21</a> |
| 28106Z      | <a href="#">21</a> |
| 28107Z      | <a href="#">21</a> |
| 28108Z      | <a href="#">21</a> |
| 28110Z      | <a href="#">24</a> |
| 28111Z      | <a href="#">24</a> |
| 28112Z      | <a href="#">24</a> |
| 28113Z      | <a href="#">24</a> |
| 28114Z      | <a href="#">24</a> |
| 28115Z      | <a href="#">24</a> |
| 28116Z      | <a href="#">24</a> |
| 28117Z      | <a href="#">24</a> |
| 28118Z      | <a href="#">24</a> |
| 28119Z      | <a href="#">24</a> |
| 28120Z      | <a href="#">24</a> |
| 28121Z      | <a href="#">24</a> |
| 28122Z      | <a href="#">24</a> |
| 28123Z      | <a href="#">24</a> |
| 28124Z      | <a href="#">24</a> |
| 28125Z      | <a href="#">24</a> |
| 28126Z      | <a href="#">24</a> |
| 28127Z      | <a href="#">24</a> |
| 28128Z      | <a href="#">24</a> |
| 28129Z      | <a href="#">24</a> |
| 28130Z      | <a href="#">24</a> |
| 28131Z      | <a href="#">24</a> |
| 28132Z      | <a href="#">24</a> |
| 28133Z      | <a href="#">24</a> |
| 28134Z      | <a href="#">24</a> |
| 28135Z      | <a href="#">24</a> |
| 28136Z      | <a href="#">24</a> |
| 28137Z      | <a href="#">24</a> |
| 28139Z      | <a href="#">27</a> |
| 28140Z      | <a href="#">27</a> |
| 28141Z      | <a href="#">27</a> |



## MarineTuff® Part Number Index

| Part Number | Page No            |
|-------------|--------------------|-------------|--------------------|-------------|--------------------|-------------|--------------------|
| 28142Z      | <a href="#">27</a> | 28336Z      | <a href="#">15</a> | 29505X      | <a href="#">45</a> | 973109Z     | <a href="#">58</a> |
| 28143Z      | <a href="#">27</a> | 28338Z      | <a href="#">18</a> | 29506X      | <a href="#">45</a> | 977896Z     | <a href="#">67</a> |
| 28144Z      | <a href="#">27</a> | 28339Z      | <a href="#">18</a> | 29507X      | <a href="#">45</a> | 977940Z     | <a href="#">12</a> |
| 28145Z      | <a href="#">27</a> | 28340Z      | <a href="#">18</a> | 29528X      | <a href="#">47</a> | 977953Z     | <a href="#">12</a> |
| 28146Z      | <a href="#">27</a> | 28341Z      | <a href="#">18</a> | 29529X      | <a href="#">47</a> | FD1B002LB   | <a href="#">9</a>  |
| 28147Z      | <a href="#">27</a> | 28600Z      | <a href="#">15</a> | 29530X      | <a href="#">47</a> | FD1B004LB   | <a href="#">9</a>  |
| 28148Z      | <a href="#">27</a> | 28601Z      | <a href="#">15</a> | 29531X      | <a href="#">47</a> | FD1B006LB   | <a href="#">9</a>  |
| 28149Z      | <a href="#">29</a> | 28602Z      | <a href="#">15</a> | 29532X      | <a href="#">47</a> | FD1B010LB   | <a href="#">9</a>  |
| 28150Z      | <a href="#">29</a> | 28603Z      | <a href="#">15</a> | 772118T     | <a href="#">51</a> | FD1B012LB   | <a href="#">9</a>  |
| 28151Z      | <a href="#">29</a> | 28604Z      | <a href="#">15</a> | 772119T     | <a href="#">51</a> | FD1L006LF   | <a href="#">8</a>  |
| 28152Z      | <a href="#">30</a> | 28605Z      | <a href="#">15</a> | 772120T     | <a href="#">51</a> | FD1L012LG   | <a href="#">8</a>  |
| 28153Z      | <a href="#">30</a> | 28606Z      | <a href="#">15</a> | 772121T     | <a href="#">51</a> | FD1L024LG   | <a href="#">8</a>  |
| 28154Z      | <a href="#">30</a> | 28607Z      | <a href="#">15</a> | 772127T     | <a href="#">52</a> | FD1L036LG   | <a href="#">8</a>  |
| 28155Z      | <a href="#">31</a> | 28608Z      | <a href="#">15</a> | 772128T     | <a href="#">52</a> | FD1L048LG   | <a href="#">8</a>  |
| 28156Z      | <a href="#">31</a> | 28609Z      | <a href="#">15</a> | 772129T     | <a href="#">52</a> | FD3B002LB   | <a href="#">9</a>  |
| 28157Z      | <a href="#">31</a> | 28610Z      | <a href="#">15</a> | 772130T     | <a href="#">52</a> | FD3B004LB   | <a href="#">9</a>  |
| 28158Z      | <a href="#">32</a> | 28611Z      | <a href="#">15</a> | 773072T     | <a href="#">64</a> | FD3B006LB   | <a href="#">9</a>  |
| 28159Z      | <a href="#">32</a> | 28612Z      | <a href="#">15</a> | 773076T     | <a href="#">50</a> | FD3B010LB   | <a href="#">9</a>  |
| 28161Z      | <a href="#">33</a> | 28613Z      | <a href="#">15</a> | 773079T     | <a href="#">55</a> | FD3B012LB   | <a href="#">9</a>  |
| 28167Z      | <a href="#">33</a> | 28614Z      | <a href="#">15</a> | 773092F     | <a href="#">61</a> | FD3L006LF   | <a href="#">8</a>  |
| 28168Z      | <a href="#">33</a> | 28615Z      | <a href="#">18</a> | 773092T     | <a href="#">61</a> | FD3L012LG   | <a href="#">8</a>  |
| 28169Z      | <a href="#">33</a> | 28616Z      | <a href="#">18</a> | 773105T     | <a href="#">58</a> | FD3L024LG   | <a href="#">8</a>  |
| 28170Z      | <a href="#">33</a> | 28617Z      | <a href="#">18</a> | 773107T     | <a href="#">58</a> | FD3L036LG   | <a href="#">8</a>  |
| 28171Z      | <a href="#">33</a> | 28618Z      | <a href="#">18</a> | 773108T     | <a href="#">58</a> | FD3L048LG   | <a href="#">8</a>  |
| 28172Z      | <a href="#">33</a> | 28619Z      | <a href="#">18</a> | 773109T     | <a href="#">58</a> | FD4B002LB   | <a href="#">9</a>  |
| 28173Z      | <a href="#">34</a> | 28620Z      | <a href="#">18</a> | 777896T     | <a href="#">67</a> | FD4B004LB   | <a href="#">9</a>  |
| 28174Z      | <a href="#">34</a> | 28621Z      | <a href="#">18</a> | 777940T     | <a href="#">12</a> | FD4B006LB   | <a href="#">9</a>  |
| 28175Z      | <a href="#">34</a> | 28622Z      | <a href="#">18</a> | 777953T     | <a href="#">12</a> | FD4B010LB   | <a href="#">9</a>  |
| 28176Z      | <a href="#">34</a> | 28623Z      | <a href="#">18</a> | 972118Z     | <a href="#">51</a> | FD4B012LB   | <a href="#">9</a>  |
| 28177Z      | <a href="#">34</a> | 28624Z      | <a href="#">18</a> | 972119Z     | <a href="#">51</a> | FD4L006LF   | <a href="#">8</a>  |
| 28178Z      | <a href="#">34</a> | 28625Z      | <a href="#">18</a> | 972120Z     | <a href="#">51</a> | FD4L012LG   | <a href="#">8</a>  |
| 28323Z      | <a href="#">18</a> | 28626Z      | <a href="#">18</a> | 972121Z     | <a href="#">51</a> | FD4L024LG   | <a href="#">8</a>  |
| 28324Z      | <a href="#">18</a> | 28627Z      | <a href="#">18</a> | 972127Z     | <a href="#">52</a> | FD4L036LG   | <a href="#">8</a>  |
| 28326Z      | <a href="#">15</a> | 28628Z      | <a href="#">18</a> | 972128Z     | <a href="#">52</a> | FD4L048LG   | <a href="#">8</a>  |
| 28326ZS     | <a href="#">17</a> | 28629Z      | <a href="#">21</a> | 972129Z     | <a href="#">52</a> | FDSB002LB   | <a href="#">9</a>  |
| 28327Z      | <a href="#">15</a> | 28630Z      | <a href="#">24</a> | 972130Z     | <a href="#">52</a> | FDSB004LB   | <a href="#">9</a>  |
| 28328Z      | <a href="#">15</a> | 28632Z      | <a href="#">15</a> | 973072Z     | <a href="#">64</a> | FDSB006LB   | <a href="#">9</a>  |
| 28329Z      | <a href="#">15</a> | 28634Z      | <a href="#">24</a> | 973076Z     | <a href="#">50</a> | FDSB010LB   | <a href="#">9</a>  |
| 28330Z      | <a href="#">18</a> | 28912Z      | <a href="#">21</a> | 973079Z     | <a href="#">55</a> | FDSB012LB   | <a href="#">9</a>  |
| 28331Z      | <a href="#">18</a> | 29500X      | <a href="#">45</a> | 973092F     | <a href="#">61</a> | FDSL006LF   | <a href="#">8</a>  |
| 28331ZS     | <a href="#">20</a> | 29501X      | <a href="#">45</a> | 973092Z     | <a href="#">61</a> | FDSL012LG   | <a href="#">8</a>  |
| 28334Z      | <a href="#">15</a> | 29502X      | <a href="#">45</a> | 973105Z     | <a href="#">58</a> | FDSL024LG   | <a href="#">8</a>  |
| 28334ZS     | <a href="#">17</a> | 29503X      | <a href="#">45</a> | 973107Z     | <a href="#">58</a> | FDSL036LG   | <a href="#">8</a>  |
| 28335Z      | <a href="#">15</a> | 29504X      | <a href="#">45</a> | 973108Z     | <a href="#">58</a> | FDSL048LG   | <a href="#">8</a>  |



# MarineTuff® Part Number Index

| Part Number | Page No            |
|-------------|--------------------|
| W1037Z      | <a href="#">39</a> |
| W1039Z      | <a href="#">39</a> |
| W1040Z      | <a href="#">39</a> |
| W1041Z      | <a href="#">39</a> |
| W1048Z      | <a href="#">36</a> |
| W1049Z      | <a href="#">36</a> |
| W1050Z      | <a href="#">36</a> |
| W1051Z      | <a href="#">36</a> |
| W1055Z      | <a href="#">39</a> |
| W1093Z      | <a href="#">37</a> |
| W1094Z      | <a href="#">37</a> |
| W1097Z      | <a href="#">40</a> |
| W1098Z      | <a href="#">40</a> |
| W1118Z      | <a href="#">39</a> |
| W1119Z      | <a href="#">40</a> |
| W1120Z      | <a href="#">36</a> |
| W1121Z      | <a href="#">37</a> |
| W3064Z      | <a href="#">37</a> |
| W3080Z      | <a href="#">41</a> |
| W3081Z      | <a href="#">41</a> |
| W3088Z      | <a href="#">36</a> |
| W3089Z      | <a href="#">37</a> |
| W3090Z      | <a href="#">39</a> |
| W3091Z      | <a href="#">40</a> |
| W3103Z      | <a href="#">42</a> |
| W27080Z     | <a href="#">23</a> |
| W27109Z     | <a href="#">26</a> |
| W27138Z     | <a href="#">28</a> |
| W27325Z     | <a href="#">16</a> |
| W27337Z     | <a href="#">19</a> |
| W27636Z     | <a href="#">23</a> |
| W27641Z     | <a href="#">26</a> |
| W27643Z     | <a href="#">28</a> |
| W27916Z     | <a href="#">16</a> |
| W27917Z     | <a href="#">19</a> |
| W28081Z     | <a href="#">23</a> |
| W28082Z     | <a href="#">23</a> |
| W28083Z     | <a href="#">23</a> |
| W28084Z     | <a href="#">23</a> |
| W28085Z     | <a href="#">23</a> |
| W28086Z     | <a href="#">23</a> |
| W28087Z     | <a href="#">23</a> |
| W28088Z     | <a href="#">23</a> |
| W28089Z     | <a href="#">23</a> |

| Part Number | Page No            |
|-------------|--------------------|
| W28090Z     | <a href="#">23</a> |
| W28091Z     | <a href="#">23</a> |
| W28092Z     | <a href="#">23</a> |
| W28093Z     | <a href="#">23</a> |
| W28094Z     | <a href="#">23</a> |
| W28095Z     | <a href="#">23</a> |
| W28096Z     | <a href="#">23</a> |
| W28097Z     | <a href="#">23</a> |
| W28098Z     | <a href="#">23</a> |
| W28099Z     | <a href="#">23</a> |
| W28100Z     | <a href="#">23</a> |
| W28101Z     | <a href="#">23</a> |
| W28102Z     | <a href="#">23</a> |
| W28103Z     | <a href="#">23</a> |
| W28104Z     | <a href="#">23</a> |
| W28105Z     | <a href="#">23</a> |
| W28106Z     | <a href="#">23</a> |
| W28107Z     | <a href="#">23</a> |
| W28108Z     | <a href="#">23</a> |
| W28110Z     | <a href="#">26</a> |
| W28111Z     | <a href="#">26</a> |
| W28112Z     | <a href="#">26</a> |
| W28113Z     | <a href="#">26</a> |
| W28114Z     | <a href="#">26</a> |
| W28115Z     | <a href="#">26</a> |
| W28116Z     | <a href="#">26</a> |
| W28117Z     | <a href="#">26</a> |
| W28118Z     | <a href="#">26</a> |
| W28119Z     | <a href="#">26</a> |
| W28120Z     | <a href="#">26</a> |
| W28121Z     | <a href="#">26</a> |
| W28122Z     | <a href="#">26</a> |
| W28123Z     | <a href="#">26</a> |
| W28124Z     | <a href="#">26</a> |
| W28125Z     | <a href="#">26</a> |
| W28126Z     | <a href="#">26</a> |
| W28127Z     | <a href="#">26</a> |
| W28128Z     | <a href="#">26</a> |
| W28129Z     | <a href="#">26</a> |
| W28130Z     | <a href="#">26</a> |
| W28139Z     | <a href="#">28</a> |
| W28140Z     | <a href="#">28</a> |
| W28141Z     | <a href="#">28</a> |
| W28142Z     | <a href="#">28</a> |

| Part Number | Page No            |
|-------------|--------------------|
| W28143Z     | <a href="#">28</a> |
| W28144Z     | <a href="#">28</a> |
| W28145Z     | <a href="#">28</a> |
| W28146Z     | <a href="#">28</a> |
| W28147Z     | <a href="#">28</a> |
| W28148Z     | <a href="#">28</a> |
| W28149Z     | <a href="#">29</a> |
| W28150Z     | <a href="#">29</a> |
| W28151Z     | <a href="#">29</a> |
| W28152Z     | <a href="#">30</a> |
| W28153Z     | <a href="#">30</a> |
| W28154Z     | <a href="#">30</a> |
| W28155Z     | <a href="#">31</a> |
| W28156Z     | <a href="#">31</a> |
| W28157Z     | <a href="#">31</a> |
| W28158Z     | <a href="#">32</a> |
| W28159Z     | <a href="#">32</a> |
| W28323Z     | <a href="#">19</a> |
| W28324Z     | <a href="#">20</a> |
| W28326Z     | <a href="#">16</a> |
| W28327Z     | <a href="#">16</a> |
| W28328Z     | <a href="#">16</a> |
| W28329Z     | <a href="#">16</a> |
| W28330Z     | <a href="#">19</a> |
| W28331Z     | <a href="#">19</a> |
| W28334Z     | <a href="#">16</a> |
| W28335Z     | <a href="#">16</a> |
| W28336Z     | <a href="#">16</a> |
| W28338Z     | <a href="#">19</a> |
| W28339Z     | <a href="#">19</a> |
| W28340Z     | <a href="#">19</a> |
| W28341Z     | <a href="#">19</a> |
| W28600Z     | <a href="#">16</a> |
| W28601Z     | <a href="#">16</a> |
| W28602Z     | <a href="#">16</a> |
| W28603Z     | <a href="#">16</a> |
| W28604Z     | <a href="#">16</a> |
| W28605Z     | <a href="#">16</a> |
| W28606Z     | <a href="#">16</a> |
| W28607Z     | <a href="#">16</a> |
| W28608Z     | <a href="#">17</a> |
| W28609Z     | <a href="#">17</a> |
| W28610Z     | <a href="#">17</a> |
| W28611Z     | <a href="#">17</a> |

| Part Number | Page No            |
|-------------|--------------------|
| W28612Z     | <a href="#">17</a> |
| W28613Z     | <a href="#">17</a> |
| W28615Z     | <a href="#">19</a> |
| W28616Z     | <a href="#">19</a> |
| W28617Z     | <a href="#">19</a> |
| W28618Z     | <a href="#">19</a> |
| W28619Z     | <a href="#">19</a> |
| W28620Z     | <a href="#">19</a> |
| W28621Z     | <a href="#">19</a> |
| W28622Z     | <a href="#">19</a> |
| W28623Z     | <a href="#">19</a> |
| W28624Z     | <a href="#">19</a> |
| W28626Z     | <a href="#">20</a> |
| W28627Z     | <a href="#">20</a> |
| W29500X     | <a href="#">45</a> |
| W29501X     | <a href="#">45</a> |
| W29502X     | <a href="#">45</a> |
| W29503X     | <a href="#">45</a> |
| W29504X     | <a href="#">45</a> |
| W29505X     | <a href="#">45</a> |
| Z1037Z      | <a href="#">38</a> |
| Z1039Z      | <a href="#">38</a> |
| Z1040Z      | <a href="#">38</a> |
| Z1041Z      | <a href="#">38</a> |
| Z1042Z      | <a href="#">38</a> |
| Z1048Z      | <a href="#">36</a> |
| Z1049Z      | <a href="#">36</a> |
| Z1050Z      | <a href="#">36</a> |
| Z1051Z      | <a href="#">36</a> |
| Z1055Z      | <a href="#">38</a> |
| Z1093Z      | <a href="#">37</a> |
| Z1094Z      | <a href="#">37</a> |
| Z1097Z      | <a href="#">39</a> |
| Z1098Z      | <a href="#">39</a> |
| Z1118Z      | <a href="#">38</a> |
| Z1119Z      | <a href="#">39</a> |
| Z1120Z      | <a href="#">36</a> |
| Z1121Z      | <a href="#">37</a> |
| Z3064Z      | <a href="#">37</a> |
| Z3080Z      | <a href="#">41</a> |
| Z3081Z      | <a href="#">41</a> |
| Z3088Z      | <a href="#">36</a> |
| Z3089Z      | <a href="#">37</a> |
| Z3090Z      | <a href="#">38</a> |



## MarineTuff® Part Number Index

| Part Number | Page No            |
|-------------|--------------------|-------------|--------------------|-------------|--------------------|-------------|--------------------|
| Z3091Z      | <a href="#">39</a> | Z28102Z     | <a href="#">22</a> | Z28143Z     | <a href="#">27</a> | Z28601Z     | <a href="#">15</a> |
| Z3103Z      | <a href="#">42</a> | Z28103Z     | <a href="#">22</a> | Z28144Z     | <a href="#">27</a> | Z28602Z     | <a href="#">16</a> |
| Z27080Z     | <a href="#">22</a> | Z28104Z     | <a href="#">22</a> | Z28145Z     | <a href="#">27</a> | Z28603Z     | <a href="#">16</a> |
| Z27109Z     | <a href="#">25</a> | Z28105Z     | <a href="#">22</a> | Z28146Z     | <a href="#">27</a> | Z28604Z     | <a href="#">16</a> |
| Z27138Z     | <a href="#">27</a> | Z28106Z     | <a href="#">22</a> | Z28147Z     | <a href="#">27</a> | Z28605Z     | <a href="#">16</a> |
| Z27325Z     | <a href="#">15</a> | Z28107Z     | <a href="#">22</a> | Z28148Z     | <a href="#">27</a> | Z28606Z     | <a href="#">16</a> |
| Z27337Z     | <a href="#">18</a> | Z28108Z     | <a href="#">22</a> | Z28149Z     | <a href="#">29</a> | Z28607Z     | <a href="#">16</a> |
| Z27636Z     | <a href="#">22</a> | Z28110Z     | <a href="#">25</a> | Z28150Z     | <a href="#">29</a> | Z28608Z     | <a href="#">16</a> |
| Z27641Z     | <a href="#">25</a> | Z28111Z     | <a href="#">25</a> | Z28151Z     | <a href="#">29</a> | Z28609Z     | <a href="#">16</a> |
| Z27643Z     | <a href="#">27</a> | Z28112Z     | <a href="#">25</a> | Z28152Z     | <a href="#">30</a> | Z28610Z     | <a href="#">16</a> |
| Z27916Z     | <a href="#">15</a> | Z28113Z     | <a href="#">25</a> | Z28153Z     | <a href="#">30</a> | Z28611Z     | <a href="#">16</a> |
| Z27917Z     | <a href="#">18</a> | Z28114Z     | <a href="#">25</a> | Z28154Z     | <a href="#">30</a> | Z28612Z     | <a href="#">16</a> |
| Z28081Z     | <a href="#">22</a> | Z28115Z     | <a href="#">25</a> | Z28155Z     | <a href="#">31</a> | Z28613Z     | <a href="#">16</a> |
| Z28082Z     | <a href="#">22</a> | Z28116Z     | <a href="#">25</a> | Z28156Z     | <a href="#">31</a> | Z28614Z     | <a href="#">16</a> |
| Z28083Z     | <a href="#">22</a> | Z28117Z     | <a href="#">25</a> | Z28157Z     | <a href="#">31</a> | Z28615Z     | <a href="#">18</a> |
| Z28084Z     | <a href="#">22</a> | Z28118Z     | <a href="#">25</a> | Z28158Z     | <a href="#">32</a> | Z28616Z     | <a href="#">18</a> |
| Z28085Z     | <a href="#">22</a> | Z28119Z     | <a href="#">25</a> | Z28159Z     | <a href="#">32</a> | Z28617Z     | <a href="#">18</a> |
| Z28086Z     | <a href="#">22</a> | Z28120Z     | <a href="#">25</a> | Z28323Z     | <a href="#">18</a> | Z28618Z     | <a href="#">19</a> |
| Z28087Z     | <a href="#">22</a> | Z28121Z     | <a href="#">25</a> | Z28324Z     | <a href="#">19</a> | Z28619Z     | <a href="#">19</a> |
| Z28088Z     | <a href="#">22</a> | Z28122Z     | <a href="#">25</a> | Z28326Z     | <a href="#">15</a> | Z28620Z     | <a href="#">19</a> |
| Z28089Z     | <a href="#">22</a> | Z28123Z     | <a href="#">25</a> | Z28327Z     | <a href="#">15</a> | Z28621Z     | <a href="#">19</a> |
| Z28090Z     | <a href="#">22</a> | Z28124Z     | <a href="#">25</a> | Z28328Z     | <a href="#">16</a> | Z28622Z     | <a href="#">19</a> |
| Z28091Z     | <a href="#">22</a> | Z28125Z     | <a href="#">25</a> | Z28329Z     | <a href="#">16</a> | Z28623Z     | <a href="#">19</a> |
| Z28092Z     | <a href="#">22</a> | Z28126Z     | <a href="#">25</a> | Z28330Z     | <a href="#">19</a> | Z28624Z     | <a href="#">19</a> |
| Z28093Z     | <a href="#">22</a> | Z28127Z     | <a href="#">25</a> | Z28331Z     | <a href="#">18</a> | Z28625Z     | <a href="#">19</a> |
| Z28094Z     | <a href="#">22</a> | Z28128Z     | <a href="#">25</a> | Z28334Z     | <a href="#">15</a> | Z28626Z     | <a href="#">19</a> |
| Z28095Z     | <a href="#">22</a> | Z28129Z     | <a href="#">25</a> | Z28335Z     | <a href="#">15</a> | Z28627Z     | <a href="#">19</a> |
| Z28096Z     | <a href="#">22</a> | Z28130Z     | <a href="#">25</a> | Z28336Z     | <a href="#">15</a> | Z29500X     | <a href="#">45</a> |
| Z28097Z     | <a href="#">22</a> | Z28131Z     | <a href="#">25</a> | Z28338Z     | <a href="#">18</a> | Z29501X     | <a href="#">45</a> |
| Z28098Z     | <a href="#">22</a> | Z28139Z     | <a href="#">27</a> | Z28339Z     | <a href="#">18</a> | Z29502X     | <a href="#">45</a> |
| Z28099Z     | <a href="#">22</a> | Z28140Z     | <a href="#">27</a> | Z28340Z     | <a href="#">18</a> | Z29503X     | <a href="#">45</a> |
| Z28100Z     | <a href="#">22</a> | Z28141Z     | <a href="#">27</a> | Z28341Z     | <a href="#">19</a> | Z29504X     | <a href="#">45</a> |
| Z28101Z     | <a href="#">22</a> | Z28142Z     | <a href="#">27</a> | Z28600Z     | <a href="#">15</a> | Z29505X     | <a href="#">45</a> |





## About Belden

Belden Inc., a global leader in high quality, end-to-end signal transmission solutions, delivers a comprehensive product portfolio designed to meet the mission-critical network infrastructure needs of industrial, enterprise and broadcast markets. With innovative solutions targeted at reliable and secure transmission of rapidly growing amounts of data, audio and video needed for today's applications, Belden is at the center of the global transformation to a connected world. Founded in 1902, the company is headquartered in St. Louis, USA, and has manufacturing capabilities in North and South America, Europe and Asia.

For more information, visit us at:  
[www.belden.com](http://www.belden.com)  
[www.beldensolutions.com](http://www.beldensolutions.com)  
follow us on Twitter @BeldenIND